

SIMATIC S7-1200, CPU 1212FC, COMPACT CPU, DC/DC/RLY,  
ONBOARD I/O: 8 DI 24V DC; 6 DO RELAY 2A; 2 AI 0 - 10V DC,  
POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA  
MEMORY 100 KB



### General information

Product type designation	CPU 1212FC DC/DC/relay
Firmware version	V4.2
Engineering with	
<ul style="list-style-type: none"> <li>Programming package</li> </ul>	STEP 7 V14 or higher

### Supply voltage

Rated value (DC)	
<ul style="list-style-type: none"> <li>24 V DC</li> </ul>	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

### Input current

$I^2t$	0.5 A <sup>2</sup> ·s
--------	-----------------------

### Output current

for backplane bus (5 V DC), max.	1 000 mA; Max. 5 V DC for SM and CM
----------------------------------	-------------------------------------

### Encoder supply

24 V encoder supply	
<ul style="list-style-type: none"> <li>24 V</li> </ul>	Permissible range: 20.4V to 28.8V

Power loss	
Power loss, typ.	9 W
Memory	
Work memory	
<ul style="list-style-type: none"> <li>integrated</li> </ul>	100 kbyte
<ul style="list-style-type: none"> <li>expandable</li> </ul>	No
Load memory	
<ul style="list-style-type: none"> <li>integrated</li> </ul>	2 Mbyte
<ul style="list-style-type: none"> <li>Plug-in (SIMATIC Memory Card), max.</li> </ul>	with SIMATIC memory card
Backup	
<ul style="list-style-type: none"> <li>present</li> </ul>	Yes
<ul style="list-style-type: none"> <li>maintenance-free</li> </ul>	Yes
<ul style="list-style-type: none"> <li>without battery</li> </ul>	Yes
CPU processing times	
for bit operations, typ.	0.08 $\mu$ s; / instruction
for word operations, typ.	1.7 $\mu$ s; / instruction
for floating point arithmetic, typ.	2.5 $\mu$ s; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
OB	
<ul style="list-style-type: none"> <li>Number, max.</li> </ul>	Limited only by RAM for code
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	10 kbyte
Flag	
<ul style="list-style-type: none"> <li>Number, max.</li> </ul>	4 kbyte; Size of bit memory address area
Local data	
<ul style="list-style-type: none"> <li>per priority class, max.</li> </ul>	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB
Address area	
I/O address area	
<ul style="list-style-type: none"> <li>Inputs</li> </ul>	1 024 byte
<ul style="list-style-type: none"> <li>Outputs</li> </ul>	1 024 byte
Process image	
<ul style="list-style-type: none"> <li>Inputs, adjustable</li> </ul>	1 kbyte
<ul style="list-style-type: none"> <li>Outputs, adjustable</li> </ul>	1 kbyte
Hardware configuration	
Number of modules per system, max.	3 comm. modules, 1 signal board, 2 signal modules

Time of day	
Clock	
<ul style="list-style-type: none"> <li>• Hardware clock (real-time)</li> <li>• Backup time</li> <li>• Deviation per day, max.</li> </ul>	Yes 480 h; Typical 60 s/month at 25 °C
Digital inputs	
Number of digital inputs	8; Integrated
<ul style="list-style-type: none"> <li>• of which inputs usable for technological functions</li> </ul>	4; HSC (High Speed Counting)
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	8
Input voltage	
<ul style="list-style-type: none"> <li>• Rated value (DC)</li> <li>• for signal "0"</li> <li>• for signal "1"</li> </ul>	24 V 5 V DC at 1 mA 15 V DC at 2.5 mA
Input current	
<ul style="list-style-type: none"> <li>• for signal "1", typ.</li> </ul>	1 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— parameterizable	Yes
Digital outputs	
Number of digital outputs	6
Switching capacity of the outputs	
<ul style="list-style-type: none"> <li>• with resistive load, max.</li> <li>• on lamp load, max.</li> </ul>	2 A 30 W with DC, 200 W with AC
Output delay with resistive load	
<ul style="list-style-type: none"> <li>• "0" to "1", max.</li> <li>• "1" to "0", max.</li> </ul>	10 ms; max. 10 ms; max.
Cable length	
<ul style="list-style-type: none"> <li>• shielded, max.</li> <li>• unshielded, max.</li> </ul>	500 m 150 m
Analog inputs	
Number of analog inputs	2
Input ranges	
<ul style="list-style-type: none"> <li>• Voltage</li> </ul>	Yes

<b>Input ranges (rated values), voltages</b>	
• 0 to +10 V	Yes
• Input resistance (0 to 10 V)	≥100k ohms
<b>Cable length</b>	
• shielded, max.	100 m; twisted and shielded
<b>Analog outputs</b>	
Number of analog outputs	0
<b>Analog value generation for the inputs</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	10 bit
• Integration time, parameterizable	Yes
• Conversion time (per channel)	625 μs
<b>Encoder</b>	
<b>Connectable encoders</b>	
• 2-wire sensor	Yes
<b>1. Interface</b>	
Interface type	PROFINET
Physics	Ethernet
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
<b>Interface types</b>	
• Number of ports	1
• integrated switch	Yes
<b>Functionality</b>	
• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes
• Web server	Yes
<b>PROFINET IO Controller</b>	
• Transmission rate, max.	100 Mbit/s
<b>Services</b>	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	No
— MRP	No

— MRPD	No
— PROFINergy	No
— Prioritized startup	Yes
— Number of IO devices with prioritized startup, max.	16
— Number of connectable IO Devices, max.	16
— Number of connectable IO Devices for RT, max.	16
— of which in line, max.	16
— Activation/deactivation of IO Devices	Yes
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— Updating time	The minimum value of the update time also depends on the communication component set for PROFINET IO, on the number of IO devices and the quantity of configured user data.

### PROFINET IO Device

#### Services

— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	No
— MRP	No
— MRPD	No
— PROFINergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2

#### Protocols

Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 required
AS-Interface	Yes; CM 1243-2 required

#### Protocols (Ethernet)

• TCP/IP	Yes
• DHCP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes

#### Open IE communication

• TCP/IP	
— Data length, max.	8 kbyte
• ISO-on-TCP (RFC1006)	Yes

— Data length, max.	8 kbyte
• UDP	
— Data length, max.	1 472 byte
<b>Further protocols</b>	
• MODBUS	Yes
<b>Communication functions</b>	
<b>S7 communication</b>	
• supported	Yes
• as server	Yes
• as client	Yes
• User data per job, max.	See online help (S7 communication, user data size)
<b>Web server</b>	
• supported	Yes
<b>Test commissioning functions</b>	
<b>Status/control</b>	
• Status/control variable	Yes
<b>Forcing</b>	
• Forcing	Yes
<b>Diagnostic buffer</b>	
• present	Yes
<b>Traces</b>	
• Number of configurable Traces	2
• Memory size per trace, max.	512 kbyte
<b>Integrated Functions</b>	
Number of counters	4
Counting frequency (counter) max.	100 kHz
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction interface	Up to 4 with SB 1222
PID controller	Yes
Number of pulse outputs	4
<b>Potential separation</b>	
<b>Potential separation digital inputs</b>	
• Potential separation digital inputs	500V AC for 1 minute
• between the channels, in groups of	1
<b>Potential separation digital outputs</b>	
• Potential separation digital outputs	Relays
• between the channels	No
• between the channels, in groups of	1

<b>Permissible potential difference</b>	
between different circuits	500 V DC between 24 V DC and 5 V DC
<b>EMC</b>	
<b>Interference immunity against discharge of static electricity</b>	
• Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes
— Test voltage at air discharge	8 kV
— Test voltage at contact discharge	6 kV
<b>Interference immunity to cable-borne interference</b>	
• Interference immunity on supply lines acc. to IEC 61000-4-4	Yes
• Interference immunity on signal cables acc. to IEC 61000-4-4	Yes
<b>Interference immunity against voltage surge</b>	
• on the supply lines acc. to IEC 61000-4-5	Yes
<b>Interference immunity against conducted variable disturbance induced by high-frequency fields</b>	
• Interference immunity against high-frequency radiation acc. to IEC 61000-4-6	Yes
<b>Emission of radio interference acc. to EN 55 011</b>	
• Limit class A, for use in industrial areas	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
<b>Degree and class of protection</b>	
Degree of protection acc. to EN 60529	
• IP20	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes
<b>Highest safety class achievable in safety mode</b>	
• Performance level according to ISO 13849-1	PLe
• SIL acc. to IEC 61508	SIL 3
<b>Ambient conditions</b>	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	0 °C

• max.	55 °C
• horizontal installation, min.	0 °C
• horizontal installation, max.	55 °C
• vertical installation, min.	0 °C
• vertical installation, max.	45 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 139 hPa
• permissible operating height	-1000 to 2000 m
<b>Relative humidity</b>	
• Operation, max.	95 %; no condensation
<b>Vibrations</b>	
• Operation, tested according to IEC 60068-2-6	Yes
<b>Pollutant concentrations</b>	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
<b>Configuration</b>	
<b>Programming</b>	
Programming language	
— LAD	Yes; incl. failsafe
— FBD	Yes; incl. failsafe
— SCL	Yes
<b>Know-how protection</b>	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
<b>Cycle time monitoring</b>	
• adjustable	Yes
<b>Dimensions</b>	
Width	90 mm
Height	100 mm
Depth	75 mm
<b>last modified:</b>	10/13/2017