

### Product type designation



Figure similar

### SCALANCE X307-3LD

SCALANCE X307-3LD, MANAGED PLUS IE SWITCH, 3 X 1000MBIT/S SM SC 7 X 10/100MBIT/S RJ45 PORTS, LED-DIAGNOSTICS, FAULT SIGNAL CONTACT WITH SELECT/SET BUTTON, PROFINET-IO DEVICE, NETWORK-MANAGEMENT, INTEGRATED REDUNDANCY MANAGER, OFFICE FEATURES (RSTP, VLAN, IGMP,..) C-PLUG IN SCOPE OF SUPPLY

### Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
---------------	------------------------------------

### Interfaces

Number of electrical/optical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment / maximum</li> </ul>	10
Number of electrical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	7
Type of electrical connection	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	RJ45 port
Number of optical interfaces	
<ul style="list-style-type: none"> <li>for fiber optic cable / at 1000 Mbit/s</li> </ul>	3
Design of the optical interface	
<ul style="list-style-type: none"> <li>for fiber optic cable / at 1000 Mbit/s</li> </ul>	SC port (singlemode up to 10 km)
Connectable optical power relative to 1 mW	
<ul style="list-style-type: none"> <li>of the transmitter output</li> <li>of the receiver input / maximum</li> </ul>	-9.5 ... -3 -3 dB
Optical sensitivity relating to 1 mW / of the receiver input / minimum	-21 dB
Damping ratio / of the FOC transmission link / minimum necessary	0 dB
Range / at the optical interface / depending on the optical fiber used	0 ... 10 km

### Interfaces / for communication / integrated

Number of 100 Mbit/s SC ports / for multimode	0
Number of 1000 Mbit/s LC ports / for multimode	0

### Interfaces / others

Number of electrical connections	
• for signaling contact	1
• for power supply	1
• for redundant voltage supply	2
Type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes

### Signal-Inputs/outputs

Operating voltage / of the signaling contacts	
• for DC / Rated value	24 V
Operating current / of the signaling contacts	
• for DC / maximum	0.1 A

### Supply voltage, current consumption, power loss

Type of voltage supply / redundant power supply unit	No
Type of voltage / of the supply voltage	DC
Supply voltage	
• external	24 V
• external	18 ... 32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	F 3 A / 32 V
Consumed current / maximum	0.4 A
Active power loss	
• for DC / at 24 V	9.6 W

### Permitted ambient conditions

Ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP30

### Design, dimensions and weight

Design	compact
Width	120 mm
Height	125 mm

Depth	123 mm
Net weight	1.4 kg
Mounting type	When used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted.
<ul style="list-style-type: none"> <li>• 19-inch installation</li> <li>• 35 mm DIN rail mounting</li> <li>• wall mounting</li> <li>• S7-300 rail mounting</li> <li>• S7-1500 rail mounting</li> </ul>	<p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p>

### Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3\text{ s}</math>	100
Cascading in cases of star topology	Any (depending only on signal propagation time)

### Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> <li>• CLI</li> <li>• web-based management</li> <li>• MIB support</li> <li>• TRAPs via email</li> <li>• Configuration with STEP 7</li> <li>• RMON</li> <li>• Port mirroring</li> <li>• multiport mirroring</li> <li>• CoS</li> <li>• PROFINET IO diagnosis</li> <li>• switch-managed</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Protocol / is supported	
<ul style="list-style-type: none"> <li>• Telnet</li> <li>• HTTP</li> <li>• HTTPS</li> <li>• TFTP</li> <li>• FTP</li> <li>• BOOTP</li> <li>• GMRP</li> <li>• DCP</li> <li>• LLDP</li> <li>• IGMP (snooping/querier)</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> <li>• I&amp;M1 – higher-level designation/location designation</li> </ul>	<p>Yes</p> <p>Yes</p>

Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

### Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes

### Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
Number of VLANs / maximum	255
Number of VLANs - dynamic / maximum	255
Protocol / is supported / GVRP	Yes

### Product functions / DHCP

Product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

### Product functions / Redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes

<ul style="list-style-type: none"> <li>• redundancy procedure MSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Passive listening</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• STP/RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• MSTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• RSTP big network support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LACP</li> </ul>	Yes

### Product functions / Security

Product function	
<ul style="list-style-type: none"> <li>• ACL - MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• ACL - port/MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 802.1x (radius)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Broadcast/Multicast/Unicast Limiter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• broadcast blocking</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes

### Product functions / Time

Product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 1588 profile default</li> </ul>	No

### Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> <li>• for FM</li> </ul>	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
<ul style="list-style-type: none"> <li>• for hazardous zone</li> </ul>	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> <li>• for hazardous zone / from CSA and UL</li> </ul>	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-2:2005
Certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> <li>• CE marking</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes

<ul style="list-style-type: none"> <li>• Railway application in accordance with EN 50155</li> </ul>	No
<b>Marine classification association</b> <ul style="list-style-type: none"> <li>• American Bureau of Shipping Europe Ltd. (ABS)</li> <li>• Bureau Veritas (BV)</li> <li>• Det Norske Veritas (DNV)</li> <li>• Germanische Lloyd (GL)</li> <li>• Lloyds Register of Shipping (LRS)</li> <li>• Nippon Kaiji Kyokai (NK)</li> <li>• Polski Rejestr Statkow (PRS)</li> </ul>	Yes Yes Yes Yes Yes Yes No
MTBF / at 40 °C	20 y

### Further Information / Internet Links

<b>Internet-Link</b> <ul style="list-style-type: none"> <li>• to website: Selector SIMATIC NET SELECTION TOOL</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAx Download Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
---	---

### Security information

<b>Security information</b>	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a> . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a> . (V3.4)
-----------------------------	---

**last modified:** 16.03.2015