


www.vishay.com

Vishay Semiconductors

# Optocoupler Phototransistor Output, SOP-4, 100 mil Pitch, Mini-Flat Package



#### **DESCRIPTION**

The SFH690ABT, SFH690AT, SFH690BT, SFH690CT, SFH690DT family has a GaAs infrared emitting diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a 4 pin 100 mil lead pitch miniflat package. It features a high current transfer ratio, low coupling capacitance, and high isolation voltage.

The coupling devices are designed for signal transmission between two electrically separated circuits. The SFH690 series is available only on tape and reel. There are 2000 parts per reel. Marking for SFH690AT is 690A; SFH690BT is 690B; SFH690CT is 690C; SFH690DT is 690D; SFH690ABT will be marked as 690A or 690B.

#### **FEATURES**

- SOP (small outline package)
- Isolation test voltage, 3750 V<sub>RMS</sub> (1 s)
- High collector emitter breakdown voltage,
   V<sub>CEO</sub> = 70 V
- Low saturation voltage
- · Fast switching times
- Temperature stable
- Low coupling capacitance
- End-stackable, 0.100" (2.54 mm) spacing
- Material categorization: For definitions of compliance please see <a href="https://www.vishav.com/doc?99912"><u>www.vishav.com/doc?99912</u></a>



## **APPLICATIONS**

- High density mounting or space sensitive PCBs
- PLCs
- Telecommunication

#### **AGENCY APPROVALS**

- UL1577, file no. E52744 system code U
- cUL tested to CSA 22.2 bulletin 5A
- BSI EN 60950; EN 60065
- DIN EN 60747-5-5 (VDE 0885-5) available with option 1
- CQC GB4943.1-2011 and GB8898-2011 (suitable for installation altitude below 2000 m)

ORDERING INFORMATION								
S F H 6 9 0 x x - X 0 0 1 T  PART NUMBER CTR BIN PACKAGE OPTION TAPE AND REEL								
AGENCY CERTIFIED/PACKAGE			CTR (%)					
UL, cUL, BSI	50 to 300	50 to 150	100 to 300	100 to 200	200 to 400			
SOP-4, 100 mil pitch	SFH690ABT	SFH690AT3 <sup>(1)</sup> , SFH690AT <sup>(2)</sup>	SFH690BT3 <sup>(1)</sup> , SFH690BT <sup>(2)</sup>	SFH690CT	SFH690DT			
VDE, UL, cUL, BSI	50 to 300	50 to 150	100 to 300	100 to 200	200 to 400			
SOP-4, 100 mil pitch	-	-	SFH690B-X001T	SFH690C-X001T	SFH690D-X001T			

## Notes

- (1) Product is rotated 180° in tape and reel cavity
- (2) Also available in tubes, do not put "T" to the end



www.vishay.com

Vishay Semiconductors

ABSOLUTE MAXIMUM RATING	<b>S</b> ( $T_{amb} = 25  ^{\circ}C$ , unless otherwis	se specified)		
PARAMETER	TEST CONDITION	SYMBOL	SYMBOL VALUE	
INPUT				
Reverse voltage		$V_R$	6	V
DC forward current		I <sub>F</sub>	50	mA
Surge forward current	t <sub>p</sub> ≤ 10 μs	I <sub>FSM</sub>	2.5	Α
Power dissipation		P <sub>diss</sub>	80	mW
OUTPUT				
Collector emitter voltage		V <sub>CEO</sub>	70	V
Emitter collector voltage		V <sub>ECO</sub>	7	V
0.11.1		I <sub>C</sub>	50	mA
Collector current	t <sub>p</sub> ≤ 1 ms	Ic	100	mA
Power dissipation		P <sub>diss</sub>	150	mW
COUPLER				
Isolation test voltage between emitter and detector (1 s)		V <sub>ISO</sub>	3750	V <sub>RMS</sub>
Isolation resistance	V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 25 °C	R <sub>IO</sub>	≥ 10 <sup>12</sup>	Ω
isolation resistance	V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 100 °C	R <sub>IO</sub>	≥ 10 <sup>11</sup>	Ω
Storage temperature range		T <sub>stg</sub>	- 55 to + 150	°C
Ambient temperature range		T <sub>amb</sub>	- 55 to + 100	°C
Soldering temperature (1)	max. 10 s dip soldering distance to seating plane ≥ 1.5 mm	T <sub>sld</sub>	260	°C

### Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
  implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
  maximum ratings for extended periods of the time can adversely affect reliability.
- (3) Refer to reflow profile for soldering conditions for surface mounted devices.




Fig. 1 - Permissible Power Dissipation vs. Ambient Temperature



www.vishay.com

## Vishay Semiconductors

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT		
INPUT								
Forward voltage	I <sub>F</sub> = 5 mA	$V_{F}$		1.15	1.4	V		
Reverse current	V <sub>R</sub> = 6 V	I <sub>R</sub>		0.01	10	μΑ		
Capacitance	V <sub>R</sub> = 0 V, f = 1 MHz	Co		14		pF		
Thermal resistance		R <sub>thJA</sub>		750		K/W		
OUTPUT								
Collector emitter leakage current	V <sub>CE</sub> = 20 V	I <sub>CEO</sub>			100	nA		
Collector emitter capacitance	V <sub>CE</sub> = 5 V, f = 1 MHz	C <sub>CE</sub>		2.8		pF		
Thermal resistance		R <sub>thJA</sub>		500		K/W		
COUPLER	<u> </u>							
Collector emitter saturation voltage	$I_F = 10 \text{ mA}, I_C = 2 \text{ mA}$	V <sub>CEsat</sub>		0.1	0.3	V		
Coupling capacitance	f = 1 MHz	C <sub>C</sub>		0.3		pF		

#### Note

• Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
I <sub>O</sub> /I <sub>F</sub>	I <sub>F</sub> = 5 mA, V <sub>CE</sub> = 5 V	SFH690ABT	CTR	50		300	%
		SFH690AT	CTR	50		150	%
		SFH690BT	CTR	100		300	%
		SFH690CT	CTR	100		200	%
		SFH690DT	CTR	200		400	%

<b>SWITCHING CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Rise time	$I_C = 2 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 100 \Omega$	t <sub>r</sub>		3		μs	
Fall time	$I_C$ = 2 mA, $V_{CC}$ = 5 V, $R_L$ = 100 $\Omega$	t <sub>f</sub>		4		μs	
Turn-on time	$I_C = 2 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 100 \Omega$	t <sub>on</sub>		5		μs	
Turn-off time	$I_C = 2 \text{ mA}, V_{CC} = 5 \text{ V}, R_1 = 100 \Omega$	t <sub>off</sub>		3		μs	




Fig. 2 - Switching Operation (without Saturation)



www.vishay.com

## Vishay Semiconductors

SAFETY AND INSULATION RATINGS								
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT		
Climatic classification (according to IEC 68 part 1)				55/100/21				
Comparative tracking index		CTI	175		399			
V <sub>IOTM</sub>			6000			V		
V <sub>IORM</sub>			707			V		
P <sub>SO</sub>					350	mW		
I <sub>SI</sub>					150	mA		
T <sub>SI</sub>					175	°C		
Creepage distance			5			mm		
Clearance distance			5			mm		
Insulation thickness			0.4			mm		

#### Note

## TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 3 - Forward Voltage vs. Forward Current




Fig. 4 - Collector Current vs. Collector Emitter Voltage (NS)




Fig. 5 - Leakage Current vs. Ambient Temperature




Fig. 6 - Collector Current vs. Collector Emitter Voltage (sat)

<sup>•</sup> As per IEC 60747-5-5, §7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.



www.vishay.com

Vishay Semiconductors




Fig. 7 - Normalized Current Transfer Ratio (sat) vs.
Ambient Temperature




Fig. 8 - Normalized Current Transfer Ratio (NS) vs. Ambient Temperature




Fig. 9 - Normalized CTR (NS) vs. Forward Current




Fig. 10 - Normalized CTR (sat) vs. Forward Current




Fig. 11 - F<sub>CTR</sub> vs. Phase Angle




Fig. 12 - F<sub>CTR</sub> vs. Collector Current

www.vishay.com

Vishay Semiconductors







Fig. 13 - Switching Time vs. Load Resistance


## **PACKAGE DIMENSIONS** in millimeters







## **PACKAGE MARKING** (example of SFH690AT)



#### Notes

i178037

- Only option 1 is reflected in the package marking with the characters "X1"
- Tape and reel suffix (T) is not part of the package marking



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000