

MG 100S Kit 2

Product no.: 100-1055-ESDN



Benefits

- › High Gasfilter volume
- › Electronic filter control with filter alarm
- › Variable speed setting
- › Minimized foot print
- › Switching power supply 100 – 240 V for global use
- › Optimized filter lifetime
- › The MG 100S kit 2 will be delivered with 2 pcs. flexible extrctation arm 1,5 meter, and 2 pcs. funnel nozzle. To make installation easier, the MG 100S can be suspended at the work table with special table mounting set (780-3001-ESD). The fume extraction unit is suitable for applications with a high demand of gases. Variable speed and alarm function for filter exchange can be set via the remote control.

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	460 x 210 x 610
Dimensions L x W x H (inches)	18, 11 x 8, 26 x 24, 15
Weight (approx.) in kg	15
Voltage	110 - 240 V, 50/60 Hz
Power	100 W
Noise level (distance 1 m) dB(A)	< 52
Max. vacuum	---
Capacity m³/h	140
Pre-filter	---
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-2 workstations
RS232 interface (remote control)	1 x RS232 (TTL)
USB port	---
WX-compatible	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE