




Part Number : [511930600](#)

Product Description : HMC Rectangular Industrial Female Housing, Multi-Module Type, 6 Circuits

Series Number : 51193

Status : Planned for Obsolescence

Product Category : I/O Connectors



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Planned for Obsolescence
Category	I/O Connectors
Series	51193
Description	HMC Rectangular Industrial Female Housing, Multi-Module Type, 6 Circuits
Application	Panel-Mount
Component Type	Housing
Product Family	HMC Heavy Duty Rectangular Connectors
Product Name	HMC
Type	N/A
UPC	800753934634

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	N/A
Shielded	No
Voltage - Maximum	250V AC / 300V DC

Physical

Boot Color	N/A
Breakaway	No
Circuits (Loaded)	N/A
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	2808.300/mg
Number of Rows	2

Orientation	Vertical
Packaging Type	Bag
Panel Mount	N/A
PCB Locator	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Ports	1
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	N/A
Waterproof / Dustproof	No

This document was generated on Sep 26, 2023