



1 Gbit (128 Mbyte), 512 Mbit (64 Mbyte), 256 Mbit (32 Mbyte), 128 Mbit (16 Mbyte), 3.0V GL-S Flash Memory

General Description

The Cypress S29GL01G/512/256/128S are MirrorBit[®] Eclipse[™] flash products fabricated on 65 nm process technology. These devices offer a fast page access time as fast as 15 ns with a corresponding random access time as fast as 90 ns. They feature a Write Buffer that allows a maximum of 256 words/512 bytes to be programmed in one operation, resulting in faster effective programming time than standard programming algorithms. This makes these devices ideal for today's embedded applications that require higher density, better performance and lower power consumption.

Distinctive Characteristics

- CMOS 3.0 Volt Core with Versatile I/O
- 65-nm MirrorBit Eclipse Technology
- Single supply (V_{CC}) for read / program / erase (2.7V to 3.6V)
- Versatile I/O Feature
 - Wide I/O voltage range (V_{IO}): 1.65V to V_{CC}
- x16 data bus
- Asynchronous 32-byte Page read
- 512-byte Programming Buffer
 - Programming in Page multiples, up to a maximum of 512
- Single word and multiple program on same word options
- Sector Erase
 - Uniform 128-kbyte sectors
- Suspend and Resume commands for Program and Erase operations
- Status Register, Data Polling, and Ready/Busy pin methods to determine device status

- Advanced Sector Protection (ASP)
 - Volatile and non-volatile protection methods for each
- Separate 1024-byte One Time Program (OTP) array with two lockable regions
- Common Flash Interface (CFI) parameter table
- Temperature Range
 - Industrial (-40 °C to +85 °C)
 - In-Cabin (-40 °C to +105 °C)
- 100,000 erase cycles for any sector typical
- 20-year data retention typical
- Packaging Options
 - 56-pin TSOP
 - 64-ball LAA Fortified BGA, 13 mm × 11 mm
 - 64-ball LAE Fortified BGA, 9 mm × 9 mm
 - 56-ball VBU Fortified BGA, 9 mm × 7 mm

Performance Summary

	Maximum Read Access Times					
Density	Voltage Range	Random Access Time (t _{ACC})	Page Access Time (t _{PACC})	CE# Access Time (t _{CE})	OE# Access Time (t _{OE})	
128 Mb	Full V _{CC} = V _{IO}	90	15	90	25	
120 1010	VersatileIO V _{IO}	100	25	100	35	
256 Mb	Full V _{CC} = V _{IO}	90	15	90	25	
250 IVID	VersatileIO V _{IO}	100	25	100	35	
512 Mb	Full V _{CC} = V _{IO}	100	15	100	25	
312 1010	VersatilelO V _{IO}	110	25	110	35	
1 Gb	Full V _{CC} = V _{IO}	100	15	100	25	
i Gb	VersatileIO V _{IO}	110	25	110	35	



Typical Program and Erase Rates		
Buffer Programming (512 bytes)	1.5 MB/s	
Sector Erase (128 kbytes)	477 kB/s	

Maximum Current Consumption		
Active Read at 5 MHz, 30 pF	60 mA	
Program	100 mA	
Erase	100 mA	
Standby	100 μΑ	



Contents


1.	Product Overview	. 4
Soft	ware Interface	
2.1 2.2 2.3 2.4 2.5 2.6	Address Space Maps Flash Memory Array Device ID and CFI (ID-CFI) ASO Status Register ASO Data Polling Status ASO Secure Silicon Region ASO Sector Protection Control.	. 7 . 8 . 9 10
3.1 3.2 3.3 3.4	Data Protection Device Protection Methods Command Protection Secure Silicon Region (OTP) Sector Protection Methods	12 12
4. 4.1 4.2	Read Operations Asynchronous Read Page Mode Read	18 18 18
5.1 5.2 5.3 5.4 5.5 5.6	Embedded Operations Embedded Algorithm Controller (EAC) Program and Erase Summary Command Set Status Monitoring Error Types and Clearing Procedures Embedded Algorithm Performance Table	19 20 21 31
6. 6.1 6.2	Software Interface Reference	52
Har	dware Interface	
7. 7.1 7.2 7.3 7.4 7.5	Signal Descriptions Address and Data Configuration Input/Output Summary Versatile I/O Feature Ready/Busy# (RY/BY#) Hardware Reset	61 61 62 62 62
Ω	Signal Protocols	63

8.1 8.2 8.3 8.4 8.5	Interface States	62 64 64
9.	Electrical Specifications	66
9.1	Absolute Maximum Ratings	
9.2 9.3	Latchup Characteristics	
9.3	Operating Ranges DC Characteristics	
9.5	Capacitance Characteristics	
10.	Timing Specifications	
	Key to Switching Waveforms	
10.2	AC Test Conditions	72
	Power-On Reset (POR) and Warm Reset	
10.4	AC Characteristics	
11.	Physical Interface	
	56-Pin TSOP	
	64-Ball FBGA56-Ball FBGA	
		32
12.	Special Handling Instructions for FBGA Package	94
13.	Ordering Information	
14.	Other Resources	97
14.1	Links to Software	
	Links to Application Notes	
	Specification Bulletins	
14.4	Contacting Cypress	
15.	Revision History	
	ument History Pages, Solutions, and Legal Information	
	Worldwide Sales and Design Support	
	Products	
	PSoC® Solutions	102
	Cypress Developer Community	
	Lochnical Support	711



1. Product Overview

The GL-S family consists of 128-Mbit to 1Gbit, 3.0V core, Versatile I/O, non-volatile, flash memory devices. These devices have a 16-bit (word) wide data bus and use only word boundary addresses. All read accesses provide 16 bits of data on each bus transfer cycle. All writes take 16 bits of data from each bus transfer cycle.



Noto

The GL-S family combines the best features of eXecute In Place (XIP) and Data Storage flash memories. This family has the fast random access of XIP flash along with the high density and fast program speed of Data Storage flash.

Read access to any random location takes 90 ns to 120 ns depending on device density and I/O power supply voltage. Each random (initial) access reads an entire 32-byte aligned group of data called a Page. Other words within the same Page may be read by changing only the low order 4 bits of word address. Each access within the same Page takes 15 ns to 30 ns. This is called Page Mode read. Changing any of the higher word address bits will select a different Page and begin a new initial access. All read accesses are asynchronous.

^{**} A_{MAX} GL01GS = A25, A_{MAX} GL512S = A24, A_{MAX} GL256S = A23, A_{MAX} GL128S = A22



Table 1.1 S29GL-S Address Map

Туре	Count	Addresses
Address within Page	16	A3 - A0
Address within Write Buffer	256	A7 - A0
Page	4096	A15 - A4
Write-Buffer-Line	256	A15 - A8
	1024 (1 Gb)	
Sector	512 (512 Mb)	A _{MAX} - A16
J Geoloi	256 (256 Mb)	AMAX - ATO
	128 (128 Mb)	

The device control logic is subdivided into two parallel operating sections, the Host Interface Controller (HIC) and the Embedded Algorithm Controller (EAC). HIC monitors signal levels on the device inputs and drives outputs as needed to complete read and write data transfers with the host system. HIC delivers data from the currently entered address map on read transfers; places write transfer address and data information into the EAC command memory; notifies the EAC of power transition, hardware reset, and write transfers. The EAC looks in the command memory, after a write transfer, for legal command sequences and performs the related Embedded Algorithms.

Changing the non-volatile data in the memory array requires a complex sequence of operations that are called Embedded Algorithms (EA). The algorithms are managed entirely by the device internal EAC. The main algorithms perform programming and erase of the main array data. The host system writes command codes to the flash device address space. The EAC receives the commands, performs all the necessary steps to complete the command, and provides status information during the progress of an EA.

The erased state of each memory bit is a logic 1. Programming changes a logic 1 (High) to a logic 0 (Low). Only an Erase operation is able to change a 0 to a 1. An erase operation must be performed on an entire 128-kbyte aligned and length group of data call a Sector. When shipped from Cypress all Sectors are erased.

Programming is done via a 512-byte Write Buffer. It is possible to write from 1 to 256 words, anywhere within the Write Buffer before starting a programming operation. Within the flash memory array, each 512-byte aligned group of 512 bytes is called a Line. A programming operation transfers volatile data from the Write Buffer to a non-volatile memory array Line. The operation is called Write Buffer Programming.

The Write Buffer is filled with 1's after reset or the completion of any operation using the Write Buffer. Any locations not written to a 0 by a Write to Buffer command are by default still filled with 1's. Any 1's in the Write Buffer do not affect data in the memory array during a programming operation.

As each Page of data that was loaded into the Write Buffer is transferred to a memory array Line.

Sectors may be individually protected from program and erase operations by the Advanced Sector Protection (ASP) feature set. ASP provides several, hardware and software controlled, volatile and non-volatile, methods to select which sectors are protected from program and erase operations.



Software Interface

2. Address Space Maps

There are several separate address spaces that may appear within the address range of the flash memory device. One address space is visible (entered) at any given time.

- Flash Memory Array: the main non-volatile memory array used for storage of data that may be randomly accessed by asynchronous read operations.
- ID/CFI: a memory array used for Cypress factory programmed device characteristics information. This area contains the Device Identification (ID) and Common Flash Interface (CFI) information tables.
- Secure Silicon Region (SSR): a One Time Programmable (OTP) non-volatile memory array used for Cypress factory programmed permanent data, and customer programmable permanent data.
- Lock Register: an OTP non-volatile word used to configure the ASP features and lock the SSR.
- Persistent Protection Bits (PPB): a non-volatile flash memory array with one bit for each Sector. When programmed, each bit protects the related Sector from erasure and programming.
- PPB Lock: a volatile register bit used to enable or disable programming and erasure of the PPB bits.
- Password: an OTP non-volatile array used to store a 64-bit password used to enable changing the state of the PPB Lock Bit when using Password Mode sector protection.
- Dynamic Protection Bits (DYB): a volatile array with one bit for each Sector. When set, each bit protects the related Sector from erasure and programming.
- Status Register: a volatile register used to display Embedded Algorithm status.
- Data Polling Status: a volatile register used as an alternate, legacy software compatible, way to display Embedded Algorithm status.

The main Flash Memory Array is the primary and default address space but, it may be overlaid by one other address space, at any one time. Each alternate address space is called an Address Space Overlay (ASO).

Each ASO replaces (overlays) the entire flash device address range. Any address range not defined by a particular ASO address map, is reserved for future use. All read accesses outside of an ASO address map returns non-valid (undefined) data. The locations will display actively driven data but the meaning of whatever 1's or 0's appear are not defined.

There are four device operating modes that determine what appears in the flash device address space at any given time:

- Read Mode
- Data Polling Mode
- Status Register (SR) Mode
- Address Space Overlay (ASO) Mode

In Read Mode the entire Flash Memory Array may be directly read by the host system memory controller. The memory device Embedded Algorithm Controller (EAC), puts the device in Read mode during Power-on, after a Hardware Reset, after a Command Reset, or after an Embedded Algorithm (EA) is suspended. Read accesses and command writes are accepted in read mode. A subset of commands are accepted in read mode when an EA is suspended.

While in any mode, the Status Register read command may be issued to cause the Status Register ASO to appear at every word address in the device address space. In this Status Register ASO Mode, the device interface waits for a read access and, any write access is ignored. The next read access to the device accesses the content of the status register, exits the Status Register ASO, and returns to the previous (calling) mode in which the Status Register read command was received.

In EA mode the EAC is performing an Embedded Algorithm, such as programming or erasing a non-volatile memory array. While in EA mode, none of the main Flash Memory Array is readable because the entire flash device address space is replaced by the Data Polling Status ASO. Data Polling Status will appear at every word location in the device address space.

While in EA mode, only a Program / Erase suspend command or the Status Register Read command will be accepted. All other commands are ignored. Thus, no other ASO may be entered from the EA mode.



When an Embedded Algorithm is suspended, the Data Polling ASO is visible until the device has suspended the EA. When the EA is suspended the Data Polling ASO is exited and Flash Array data is available. The Data Polling ASO is reentered when the suspended EA is resumed, until the EA is again suspended or finished. When an Embedded Algorithm is completed, the Data Polling ASO is exited and the device goes to the previous (calling) mode (from which the Embedded Algorithm was started).

In ASO mode, one of the remaining overlay address spaces is entered (overlaid on the main Flash Array address map). Only one ASO may be entered at any one time. Commands to the device affect the currently entered ASO. Only certain commands are valid for each ASO. These are listed in the Table 6.1 on page 52, in each ASO related section of the table.

The following ASOs have non-volatile data that may be programmed to change 1's to 0's:

- Secure Silicon Region
- Lock Register
- Persistent Protection Bits (PPB)
- Password
- Only the PPB ASO has non-volatile data that may be erased to change 0's to 1's

When a program or erase command is issued while one of the non-volatile ASOs is entered, the EA operates on the ASO. The ASO is not readable while the EA is active. When the EA is completed the ASO remains entered and is again readable. Suspend and Resume commands are ignored during an EA operating on any of these ASOs.

2.1 Flash Memory Array

The S29GL-S family has uniform sector architecture with a sector size of 128 kB. Table 2.1 to Table 2.4 shows the sector architecture of the four devices.

Table 2.1 S29GL01GS Sector and Memory Address Map

Sector Size (kbyte)	Sector Count	Sector Range	Address Range (16-Bit)	Notes
		SA00	0000000h-000FFFFh	Sector Starting Address
128	1024	:	:	-
		SA1023	3FF0000h-3FFFFFh	Sector Ending Address

Table 2.2 S29GL512S Sector and Memory Address Map

Sector Size (kbyte)	Sector Count	Sector Range	Address Range (16-Bit)	Notes
		SA00	0000000h-000FFFFh	Sector Starting Address
128	512	:	:	_
		SA511	1FF0000h-1FFFFFh	Sector Ending Address

Table 2.3 S29GL256S Sector and Memory Address Map

Sector Size (kbyte)	Sector Count	Sector Range	Address Range (16-Bit)	Notes
		SA00	0000000h-000FFFFh	Sector Starting Address
128	256	:	:	-
		SA255	0FF0000h-0FFFFFh	Sector Ending Address



Table 2.4 S29GL128S Sector and Memory Address Map

Sector Size (kbyte)	Sector Count	Sector Range	Address Range (16-Bit)	Notes
		SA00	0000000h-000FFFFh	Sector Starting Address
128	128	:	:	_
		SA127	07F0000h-07FFFFh	Sector Ending Address

Note: These tables have been condensed to show sector related information for an entire device on a single page Sectors and their address ranges that are not explicitly listed (such as SA001-SA510) have sectors starting and ending addresses that form the same pattern as all other sectors of that size. For example, all 128 kB sectors have the pattern XXX0000h-XXXFFFFh.

2.2 Device ID and CFI (ID-CFI) ASO

There are two traditional methods for systems to identify the type of flash memory installed in the system. One has traditionally been called Autoselect and is now referred to as Device Identification (ID). The other method is called Common Flash Interface (CFI).

For ID, a command is used to enable an address space overlay where up to 16 word locations can be read to get JEDEC manufacturer identification (ID), device ID, and some configuration and protection status information from the flash memory. The system can use the manufacturer and device IDs to select the appropriate driver software to use with the flash device.

CFI also uses a command to enable an address space overlay where an extendable table of standard information about how the flash memory is organized and operates can be read. With this method the driver software does not have to be written with the specifics of each possible memory device in mind. Instead the driver software is written in a more general way to handle many different devices but adjusts the driver behavior based on the information in the CFI table.

Traditionally these two address spaces have used separate commands and were separate overlays. However, the mapping of these two address spaces are non-overlapping and so can be combined in to a single address space and appear together in a single overlay. Either of the traditional commands used to access (enter) the Autoselect (ID) or CFI overlay will cause the now combined ID-CFI address map to appear. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements.

The ID-CFI address map appears within, and overlays the Flash Array data of, the sector selected by the address used in the ID-CFI enter command. While the ID-CFI ASO is entered the content of all other sectors is undefined.

The ID-CFI address map starts at location 0 of the selected sector. Locations above the maximum defined address of the ID-CFI ASO to the maximum address of the selected sector have undefined data. The ID-CFI enter commands use the same address and data values used on previous generation memories to access the JEDEC Manufacturer ID (Autoselect) and Common Flash Interface (CFI) information, respectively.

Table 2.5 ID-CFI Address Map Overview

Word Address	Description	Read / Write
(SA) + 0000h to 000Fh	Device ID (traditional Autoselect values)	Read Only
(SA) + 0010h to 0079h	CFI data structure	Read Only
(SA) + 0080h to FFFFh	Undefined	Read Only

For the complete address map see Table 6.2 on page 56.



2.2.1 Device ID

The Joint Electron Device Engineering Council (JEDEC) standard JEP106T defines the manufacturer ID for a compliant memory. Common industry usage defined a method and format for reading the manufacturer ID and a device specific ID from a memory device. The manufacturer and device ID information is primarily intended for programming equipment to automatically match a device with the corresponding programming algorithm. Cypress has added additional fields within this 32-byte address space.

The original industry format was structured to work with any memory data bus width e. g. x8, x16, x32. The ID code values are traditionally byte wide but are located at bus width address boundaries such that incrementing the device address inputs will read successive byte, word, or double word locations with the ID codes always located in the least significant byte location of the data bus. Because the device data bus is word wide each code byte is located in the lower half of each word location. The original industry format made the high order byte always 0. Cypress has modified the format to use both bytes in some words of the address space. For the detail description of the Device ID address map see Table 6.2 on page 56.

2.2.2 Common Flash Memory Interface

The JEDEC Common Flash Interface (CFI) specification (JESD68.01) defines a standardized data structure that may be read from a flash memory device, which allows vendor-specified software algorithms to be used for entire families of devices. The data structure contains information for system configuration such as various electrical and timing parameters, and special functions supported by the device. Software support can then be device-independent, Device ID-independent, and forward-and-backward-compatible for entire Flash device families.

The system can read CFI information at the addresses within the selected sector as shown in Device ID and Common Flash Interface (ID-CFI) ASO Map on page 56.

Like the Device ID information, CFI information is structured to work with any memory data bus width e. g. x8, x16, x32. The code values are always byte wide but are located at data bus width address boundaries such that incrementing the device address reads successive byte, word, or double word locations with the codes always located in the least significant byte location of the data bus. Because the data bus is word wide each code byte is located in the lower half of each word location and the high order byte is always 0.

For further information, please refer to the *Cypress CFI Specification, Version 1.4* (or later), and the *JEDEC publications JEP137-A* and *JESD68.01*. Please contact JEDEC (www.jedec.org) for their standards and the Cypress CFI Specification may be found at the Cypress Web site www.cypress.com/spansionappnotes at the time of this document's publication) or by contacting a local Cypress sales office listed on the web site.

2.3 Status Register ASO

The Status Register ASO contains a single word of registered volatile status for Embedded Algorithms. When the Status Register read command is issued, the current status is captured (by the rising edge of WE#) into the register and the ASO is entered. The Status Register content appears on all word locations. The first read access exits the Status Register ASO (with the rising edge of CE# or OE#) and returns to the address space map in use when the Status Register read command was issued. Write commands will not exit the Status Register ASO state.

Page 10 of 102



2.4 Data Polling Status ASO

The Data Polling Status ASO contains a single word of volatile memory indicating the progress of an EA. The Data Polling Status ASO is entered immediately following the last write cycle of any command sequence that initiates an EA. Commands that initiate an EA are:

- Word Program
- Program Buffer to Flash
- Chip Erase
- Sector Erase
- Erase Resume / Program Resume
- Program Resume Enhanced Method
- Blank Check
- Lock Register Program
- Password Program
- PPB Program
- All PPB Erase

The Data Polling Status word appears at all word locations in the device address space. When an EA is completed the Data Polling Status ASO is exited and the device address space returns to the address map mode where the EA was started.

2.5 Secure Silicon Region ASO

The Secure Silicon Region (SSR) provides an extra flash memory area that can be programmed once and permanently protected from further changes i. e. it is a One Time Program (OTP) area. The SSR is

1024 bytes in length. It consists of 512 bytes for Factory Locked Secure Silicon Region and 512 bytes for Customer Locked Secure Silicon Region.

The sector address supplied during the Secure Silicon Entry command selects the Flash Memory Array sector that is overlaid by the Secure Silicon Region address map. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. The SSR is overlaid starting at location 0 in the selected sector. Use of the sector 0 address is recommended for future compatibility. While the SSR ASO is entered the content of all other sectors is undefined. Locations above the maximum defined address of the SSR ASO to the maximum address of the selected sector have undefined data.

Table 2.6 Secure Silicon Region

Word Address Range	Content	Size
(SA) + 0000h to 00FFh	Factory Locked Secure Silicon Region	512 bytes
(SA) + 0100h to 01FFh	Customer Locked Secure Silicon Region	512 bytes
(SA) + 0200h to FFFFh	Undefined	127 kbytes



2.6 Sector Protection Control

2.6.1 Lock Register ASO

The Lock register ASO contains a single word of OTP memory. When the ASO is entered the Lock Register appears at all word locations in the device address space. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. However, it is recommended to read or program the Lock Register only at location 0 of the device address space for future compatibility.

2.6.2 Persistent Protection Bits (PPB) ASO

The PPB ASO contains one bit of a Flash Memory Array for each Sector in the device. When the PPB ASO is entered, the PPB bit for a sector appears in the Least Significant Bit (LSB) of each address in the sector. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. Reading any address in a sector displays data where the LSB indicates the non-volatile protection status for that sector. However, it is recommended to read or program the PPB only at address 0 of the sector for future compatibility. If the bit is 0 the sector is protected against programming and erase operations. If the bit is 1 the sector is not protected by the PPB. The sector may be protected by other features of ASP.

2.6.3 PPB LOCK ASO

The PPB Lock ASO contains a single bit of volatile memory. The bit controls whether the bits in the PPB ASO may be programmed or erased. If the bit is 0 the PPB ASO is protected against programming and erase operations. If the bit is 1 the PPB ASO is not protected. When the PPB Lock ASO is entered the PPB Lock bit appears in the Least Significant Bit (LSB) of each address in the device address space. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. However, it is recommended to read or program the PPB Lock only at address 0 of the device for future compatibility.

2.6.4 Password ASO

The Password ASO contains four words of OTP memory. When the ASO is entered the Password appears starting at address 0 in the device address space. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. All locations above the forth word are undefined.

2.6.5 Dynamic Protection Bits (DYB) ASO

The DYB ASO contains one bit of a volatile memory array for each Sector in the device. When the DYB ASO is entered, the DYB bit for a sector appears in the Least Significant Bit (LSB) of each address in the sector. See Figure 10.16, ASO Entry Timing on page 84 for ASO Entry timing requirements. Reading any address in a sector displays data where the LSB indicates the non-volatile protection status for that sector. However, it is recommended to read, set, or clear the DYB only at address 0 of the sector for future compatibility. If the bit is 0 the sector is protected against programming and erase operations. If the bit is 1 the sector is not protected by the DYB. The sector may be protected by other features of ASP.



3. Data Protection

The device offers several features to prevent malicious or accidental modification of any sector via hardware means.

3.1 Device Protection Methods

3.1.1 Power-Up Write Inhibit

RESET#, CE#, WE#, and, OE# are ignored during Power-On Reset (POR). During POR, the device can not be selected, will not accept commands on the rising edge of WE#, and does not drive outputs. The Host Interface Controller (HIC) and Embedded Algorithm Controller (EAC) are reset to their standby states, ready for reading array data, during POR. CE# or OE# must go to V_{IH} before the end of POR (t_{VCS}).

At the end of POR the device conditions are:

- all internal configuration information is loaded,
- the device is in read mode,
- the Status Register is at default value,
- all bits in the DYB ASO are set to un-protect all sectors,
- the Write Buffer is loaded with all 1's,
- the EAC is in the standby state.

3.1.2 Low V_{CC} Write Inhibit

When V_{CC} is less than V_{LKO} , the HIC does not accept any write cycles and the EAC resets. This protects data during V_{CC} power-up and power-down. The system must provide the proper signals to the control pins to prevent unintentional writes when V_{CC} is greater than V_{LKO} .

3.2 Command Protection

Embedded Algorithms are initiated by writing command sequences into the EAC command memory. The command memory array is not readable by the host system and has no ASO. Each host interface write is a command or part of a command sequence to the device. The EAC examines the address and data in each write transfer to determine if the write is part of a legal command sequence. When a legal command sequence is complete the EAC will initiate the appropriate EA.

Writing incorrect address or data values, or writing them in an improper sequence, will generally result in the EAC returning to its Standby state. However, such an improper command sequence may place the device in an unknown state, in which case the system must write the reset command, or possibly provide a hardware reset by driving the RESET# signal Low, to return the EAC to its Standby state, ready for random read.

The address provided in each write may contain a bit pattern used to help identify the write as a command to the device. The upper portion of the address may also select the sector address on which the command operation is to be performed. The Sector Address (SA) includes A_{MAX} through A16 flash address bits (system byte address signals a_{max} through a17). A command bit pattern is located in A10 to A0 flash address bits (system byte address signals a11 through a1).

The data in each write may be: a bit pattern used to help identify the write as a command, a code that identifies the command operation to be performed, or supply information needed to perform the operation. See Table 6.1 on page 52 for a listing of all commands accepted by the device.

3.3 Secure Silicon Region (OTP)

The Secure Silicon Region (SSR) provides an extra flash memory area that can be programmed once and permanently protected from further changes i. e. it is a One Time Program (OTP) area. The SSR is 1024 bytes in length. It consists of 512 bytes for Factory Locked Secure Silicon Region and 512 bytes for Customer Locked Secure Silicon Region.

3.4 Sector Protection Methods

3.4.1 Write Protect Signal

If WP# = V_{IL} , the lowest or highest address sector is protected from program or erase operations independent of any other ASP configuration. Whether it is the lowest or highest sector depends on the device ordering option (model) selected. If WP# = V_{IH} , the



lowest or highest address sector is not protected by the WP# signal but it may be protected by other aspects of ASP configuration. WP# has an internal pull-up; when unconnected, WP# is at V_{IH} .

3.4.2 ASP

Advanced Sector Protection (ASP) is a set of independent hardware and software methods used to disable or enable programming or erase operations, individually, in any or all sectors. This section describes the various methods of protecting data stored in the memory array. An overview of these methods is shown in Figure 3.1.




Figure 3.1 Advanced Sector Protection Overview

Every main flash array sector has a non-volatile (PPB) and a volatile (DYB) protection bit associated with it. When either bit is 0, the sector is protected from program and erase operations.

The PPB bits are protected from program and erase when the PPB Lock bit is 0. There are two methods for managing the state of the PPB Lock bit, Persistent Protection and Password Protection.

The Persistent Protection method sets the PPB Lock to 1 during POR or Hardware Reset so that the PPB bits are unprotected by a device reset. There is a command to clear the PPB Lock bit to 0 to protect the PPB bits. There is no command in the Persistent Protection method to set the PPB Lock bit therefore the PPB Lock bit will remain at 0 until the next power-off or hardware reset. The Persistent Protection method allows boot code the option of changing sector protection by programming or erasing the PPB, then protecting the PPB from further change for the remainder of normal system operation by clearing the PPB Lock bit. This is sometimes called Boot-code controlled sector protection.



The Password method clears the PPB Lock bit to 0 during POR or Hardware Reset to protect the PPB. A 64-bit password may be permanently programmed and hidden for the password method. A command can be used to provide a password for comparison with the hidden password. If the password matches the PPB Lock bit is set to 1 to unprotect the PPB. A command can be used to clear the PPB Lock bit to 0.

The selection of the PPB Lock management method is made by programming OTP bits in the Lock Register so as to permanently select the method used.

The Lock Register also contains OTP bits, for protecting the SSR.

The PPB bits are erased so that all main flash array sectors are unprotected when shipped from Cypress. The Secured Silicon Region can be factory protected or left unprotected depending on the ordering option (model) ordered.

3.4.3 PPB Lock

The Persistent Protection Bit Lock is a volatile bit for protecting all PPB bits. When cleared to 0, it locks all PPBs and when set to 1, it allows the PPBs to be changed. There is only one PPB Lock Bit per device.

The PPB Lock command is used to clear the bit to 0. The PPB Lock Bit must be cleared to 0 only after all the PPBs are configured to the desired settings.

In Persistent Protection mode, the PPB Lock is set to 1 during POR or a hardware reset. When cleared, no software command sequence can set the PPB Lock, only another hardware reset or power-up can set the PPB Lock bit.

In the Password Protection mode, the PPB Lock is cleared to 0 during POR or a hardware reset. The PPB Lock can only set to 1 by the Password Unlock command sequence. The PPB Lock can be cleared by the PPB Lock Bit Clear command.

3.4.4 Persistent Protection Bits (PPB)

The Persistent Protection Bits (PPB) are located in a separate nonvolatile flash array. One of the PPB bits is assigned to each sector. When a PPB is 0 its related sector is protected from program and erase operations. The PPB are programmed individually but must be erased as a group, similar to the way individual words may be programmed in the main array but an entire sector must be erased at the same time. Preprogramming and verification prior to erasure are handled by the EAC.

Programming a PPB bit requires the typical word programming time. During a PPB bit programming operation or PPB bit erasing, Data polling Status DQ6 Toggle Bit I will toggle until the operation is complete. Erasing all the PPBs requires typical sector erase time.

If the PPB Lock is 0, the PPB Program or erase commands do not execute and time-out without programming or erasing the PPB.

The protection state of a PPB for a given sector can be verified by executing a PPB Status Read command when entered in the PPB ASO.

3.4.5 Dynamic Protection Bits (DYB)

Dynamic Protection Bits are volatile and unique for each sector and can be individually modified. DYBs only control protection for sectors that have their PPBs erased. By issuing the DYB Set or Clear command sequences, the DYB are set to 0 or cleared to 1, thus placing each sector in the protected or unprotected state respectively, if the PPB for the Sector is 1. This feature allows software to easily protect sectors against inadvertent changes, yet does not prevent the easy removal of protection when changes are needed.

The DYB can be set to 0 or cleared to 1 as often as needed.



3.4.6 Sector Protection States Summary

Each sector can be in one of the following protection states:

- Unlocked The sector is unprotected and protection can be changed by a simple command. The protection state defaults to unprotected after a power cycle or hardware reset.
- Dynamically Locked A sector is protected and protection can be changed by a simple command. The protection state is not saved across a power cycle or hardware reset.
- Persistently Locked A sector is protected and protection can only be changed if the PPB Lock Bit is set to 1. The protection state is non-volatile and saved across a power cycle or hardware reset. Changing the protection state requires programming or erase of the PPB bits.

Table 3.1 Sector Protection States

Protection Bit Values			Sector State		
PPB Lock	PPB	DYB	Sector State		
1	1	1	Unprotected - PPB and DYB are changeable		
1	1	0	Protected - PPB and DYB are changeable		
1	0	1	Protected - PPB and DYB are changeable		
1	0	0	Protected - PPB and DYB are changeable		
0	1	1	Unprotected - PPB not changeable, DYB is changeable		
0	1	0	Protected - PPB not changeable, DYB is changeable		
0	0	1	Protected - PPB not changeable, DYB is changeable		
0	0	0	Protected - PPB not changeable, DYB is changeable		

3.4.7 Lock Register

The Lock Register holds the non-volatile OTP bits for controlling protection of the SSR, and determining the PPB Lock bit management method (protection mode).

Table 3.2 Lock Register

Bit	Default Value	Name
15-9	1	Reserved
8	0	Reserved
7	X	Reserved
6	1	SSR Region 1 (Customer) Lock Bit
5	1	Reserved
4	1	Reserved
3	1	Reserved
2	1	Password Protection Mode Lock Bit
1	1	Persistent Protection Mode Lock Bit
0	0	SSR Region 0 (Factory) Lock Bit

The Secure Silicon Region (SSR) protection bits must be used with caution, as once locked, there is no procedure available for unlocking the protected portion of the Secure Silicon Region and none of the bits in the protected Secure Silicon Region memory space can be modified in any way. Once the Secure Silicon Region area is protected, any further attempts to program in the area will fail with status indicating the area being programmed is protected. The Region 0 Indicator Bit is located in the Lock Register at bit location 0 and Region 1 in bit location 6.



As shipped from the factory, all devices default to the Persistent Protection method, with all sectors unprotected, when power is applied. The device programmer or host system can then choose which sector protection method to use. Programming either of the following two, one-time programmable, non-volatile bits, locks the part permanently in that mode:

- Persistent Protection Mode Lock Bit (DQ1)
- Password Protection Mode Lock Bit (DQ2)

If both lock bits are selected to be programmed at the same time, the operation will abort. Once the Password Mode Lock Bit is programmed, the Persistent Mode Lock Bit is permanently disabled and no changes to the protection scheme are allowed. Similarly, if the Persistent Mode Lock Bit is programmed, the Password Mode is permanently disabled.

If the password mode is to be chosen, the password must be programmed prior to setting the corresponding lock register bit. Setting the Password Protection Mode Lock Bit is programmed, a power cycle, hardware reset, or PPB Lock Bit Set command is required to set the PPB Lock bit to 0 to protect the PPB array.

The programming time of the Lock Register is the same as the typical word programming time. During a Lock Register programming EA, Data polling Status DQ6 Toggle Bit I will toggle until the programming has completed. The system can also determine the status of the lock register programming by reading the Status Register. See Status Register on page 31 for information on these status bits.

The user is not required to program DQ2 or DQ1, and DQ6 or DQ0 bits at the same time. This allows the user to lock the SSR before or after choosing the device protection scheme. When programming the Lock Bits, the Reserved Bits must be 1 (masked).

3.4.8 Persistent Protection Mode

The Persistent Protection method sets the PPB Lock to 1 during POR or Hardware Reset so that the PPB bits are unprotected by a device reset. There is a command to clear the PPB Lock bit to 0 to protect the PPB. There is no command in the Persistent Protection method to set the PPB Lock bit to 1 therefore the PPB Lock bit will remain at 0 until the next power-off or hardware reset.

3.4.9 Password Protection Mode

3.4.9.1 PPB Password Protection Mode

PPB Password Protection Mode allows an even higher level of security than the Persistent Sector Protection Mode, by requiring a 64-bit password for setting the PPB Lock. In addition to this password requirement, after power up and reset, the PPB Lock is cleared to 0 to ensure protection at power-up. Successful execution of the Password Unlock command by entering the entire password sets the PPB Lock to 1, allowing for sector PPB modifications.

Password Protection Notes:

- The Password Program Command is only capable of programming 0's.
- The password is all 1's when shipped from Cypress. It is located in its own memory space and is accessible through the use of the Password Program and Password Read commands.
- All 64-bit password combinations are valid as a password.
- Once the Password is programmed and verified, the Password Mode Locking Bit must be set in order to prevent reading or modification of the password.
- The Password Mode Lock Bit, once programmed, prevents reading the 64-bit password on the data bus and further password programming. All further program and read commands to the password region are disabled (data is read as 1's) and these commands are ignored. There is no means to verify what the password is after the Password Protection Mode Lock Bit is programmed. Password verification is only allowed before selecting the Password Protection mode.
- The Password Mode Lock Bit is not erasable.
- The exact password must be entered in order for the unlocking function to occur.
- The addresses can be loaded in any order but all 4 words are required for a successful match to occur.



- The Sector Addresses and Word Line Addresses are compared while the password address/data are loaded. If the Sector Address don't match than the error will be reported at the end of that write cycle. The status register will return to the ready state with the Program Status Bit set to 1, Program Status Register Bit set to 1, and Write Buffer Abort Status Bit set to 1 indicating a failed programming operation. It is a failure to change the state of the PPB Lock bit because it is still protected by the lack of a valid password. The data polling status will remain active, with DQ7 set to the complement of the DQ7 bit in the last word of the password unlock command, and DQ6 toggling. RY/BY# will remain low.
- The specific address and data are compared after the Program Buffer To Flash command has been given. If they don't match to the internal set value than the status register will return to the ready state with the Program Status Bit set to 1 and Program Status Register Bit set to 1 indicating a failed programming operation. It is a failure to change the state of the PPB Lock bit because it is still protected by the lack of a valid password. The data polling status will remain active, with DQ7 set to the complement of the DQ7 bit in the last word of the password unlock command, and DQ6 toggling. RY/BY# will remain low.
- The device requires approximately 100 µs for setting the PPB Lock after the valid 64-bit password is given to the device.
- The Password Unlock command cannot be accepted any faster than once every 100 μs ± 20 μs. This makes it take an unreasonably long time (58 million years) for a hacker to run through all the 64-bit combinations in an attempt to correctly match a password. The EA status checking methods may be used to determine when the EAC is ready to accept a new password command.
- If the password is lost after setting the Password Mode Lock Bit, there is no way to clear the PPB Lock.

Document Number: 001-98285 Rev. *J Page 17 of 102



4. Read Operations

4.1 Asynchronous Read

Each read access may be made to any location in the memory (random access). Each random access is self-timed with the same latency from CE# or address to valid data (t_{ACC} or t_{CE}).

4.2 Page Mode Read

Each random read accesses an entire 32-byte Page in parallel. Subsequent reads within the same Page have faster read access speed. The Page is selected by the higher address bits $(A_{MAX}-A4)$, while the specific word of that page is selected by the least significant address bits A3-A0. The higher address bits are kept constant and only A3-A0 changed to select a different word in the same Page. This is an asynchronous access with data appearing on DQ15-DQ0 when CE# remains Low, OE# remains Low, and the asynchronous Page access time (t_{PACC}) is satisfied. If CE# goes High and returns Low for a subsequent access, a random read access is performed and time is required (t_{ACC}) or t_{CE} .

Document Number: 001-98285 Rev. *J Page 18 of 102



5. Embedded Operations

5.1 Embedded Algorithm Controller (EAC)

The EAC takes commands from the host system for programming and erasing the flash memory array and performs all the complex operations needed to change the non-volatile memory state. This frees the host system from any need to manage the program and erase processes.

There are four EAC operation categories:

- Standby (Read Mode)
- Address Space Switching
- Embedded Algorithms (EA)
- Advanced Sector Protection (ASP) Management

5.1.1 EAC Standby

In the standby mode current consumption is greatly reduced. The EAC enters its standby mode when no command is being processed and no Embedded Algorithm is in progress. If the device is deselected

(CE# = High) during an Embedded Algorithm, the device still draws active current until the operation is completed (I_{CC3}). I_{CC4} in DC Characteristics on page 69 represents the standby current specification when both the Host Interface and EAC are in their Standby state.

5.1.2 Address Space Switching

Writing specific address and data sequences (command sequences) switch the memory device address space from the main flash array to one of the Address Space Overlays (ASO).

Embedded Algorithms operate on the information visible in the currently active (entered) ASO. The system continues to have access to the ASO until the system issues an ASO Exit command, performs a Hardware RESET, or until power is removed from the device. An ASO Exit Command switches from an ASO back to the main flash array address space. The commands accepted when a particular ASO is entered are listed between the ASO enter and exit commands in the command definitions table. See Command Summary on page 52 for address and data requirements for all command sequences.

5.1.3 Embedded Algorithms (EA)

Changing the non-volatile data in the memory array requires a complex sequence of operations that are called Embedded Algorithms (EA). The algorithms are managed entirely by the device internal Embedded Algorithm Controller (EAC). The main algorithms perform programming and erasing of the main array data and the ASO's. The host system writes command codes to the flash device address space. The EAC receives the commands, performs all the necessary steps to complete the command, and provides status information during the progress of an EA.



5.2 Program and Erase Summary

Flash data bits are erased in parallel in a large group called a sector. The Erase operation places each data bit in the sector in the logical 1 state (High). Flash data bits may be individually programmed from the erased 1 state to the programmed logical 0 (low) state. A data bit of 0 cannot be programmed back to a 1. A succeeding read shows that the data is still 0. Only erase operations can convert a 0 to a 1. Programming the same word location more than once with different 0 bits will result in the logical AND of the previous data and the new data being programmed.

The duration of program and erase operations is shown in Embedded Algorithm Performance Table on page 40.

Program and erase operations may be suspended.

- An erase operation may be suspended to allow either programming or reading of another sector (not in the erase sector). No other erase operation can be started during an erase suspend.
- A program operation may be suspended to allow reading of another location (not in the Line being programmed).
- No other program or erase operation may be started during a suspended program operation program or erase commands will be ignored during a suspended program operation.
- After an intervening program operation or read access is complete the suspended erase or program operation may be resumed. The resume can happen at any time after the suspend assuming the device is not in the process of executing another command.
- Program and Erase operations may be interrupted as often as necessary but in order for a program or erase operation to progress to completion there must be some periods of time between resume and the next suspend commands greater than or equal to t_{PRS} or t_{ERS} in Embedded Algorithm Performance Table on page 40.
- When an Embedded Algorithm (EA) is complete, the EAC returns to the operation state and address space from which the EA was started (Erase Suspend or EAC Standby).

The system can determine the status of a program or erase operation by reading the Status Register or using Data Polling Status. Refer to Status Register on page 31 for information on these status bits. Refer to Data Polling Status on page 32 for more information.

Any commands written to the device during the Embedded Program Algorithm are ignored except the Program Suspend, and Status Read command.

Any commands written to the device during the Embedded Erase Algorithm are ignored except Erase Suspend and Status Read command.

A hardware reset immediately terminates any in progress program / erase operation and returns to read mode after t_{RPH} time. The terminated operation should be reinitiated once the device has returned to the idle state, to ensure data integrity.

For performance and reliability reasons reading and programming is internally done on full 32-byte Pages.

I_{CC3} in DC Characteristics on page 69 represents the active current specification for a write (Embedded Algorithm) operation.

5.2.1 Program Granularity

The S29GL-S supports two methods of programming, Word or Write Buffer Programming. Each Page can be programmed by either method. Pages programmed by different methods may be mixed within a Line for the Industrial Temperature version (-40°C to +85°C). For the In-Cabin version (-40°C to +105°C) the device will only support one programming operation on each 32-byte page between erase operations and Single Word Programming command is not supported.

Word programming examines the data word supplied by the command and programs 0's in the addressed memory array word to match the 0's in the command data word.

Write Buffer Programming examines the write buffer and programs 0's in the addressed memory array Pages to match the 0's in the write buffer. The write buffer does not need to be completely filled with data. It is allowed to program as little as a single bit, several bits, a single word, a few words, a Page, multiple Pages, or the entire buffer as one programming operation. Use of the write buffer method reduces host system overhead in writing program commands and reduces memory device internal overhead in programming operations to make Write Buffer Programming more efficient and thus faster than programming individual words with the Word Programming command.



5.2.2 Incremental Programming

The same word location may be programmed more than once, by either the Word or Write Buffer Programming methods, to incrementally change 1's to 0's.

5.3 Command Set

5.3.1 Program Methods

5.3.1.1 Word Programming

Word programming is used to program a single word anywhere in the main Flash Memory Array.

The Word Programming command is a four-write-cycle sequence. The program command sequence is initiated by writing two unlock write cycles, followed by the program set up command. The program address and data are written next, which in turn initiate the Embedded Word Program algorithm. The system is not required to provide further controls or timing. The device automatically generates the program pulses and verifies the programmed cell margin internally. When the Embedded Word Program algorithm is complete, the EAC then returns to its standby mode.

The system can determine the status of the program operation by using Data Polling Status, reading the Status Register, or monitoring the RY/BY# output. See Status Register on page 31 for information on these status bits. See Data Polling Status on page 32 for information on these status bits. See Figure 5.1 on page 21 for a diagram of the programming operation.

Any commands other than Program Suspend written to the device during the Embedded Program algorithm are ignored. Note that a hardware reset (RESET# = V_{IL}) immediately terminates the programming operation and returns the device to read mode after t_{RPH} time. To ensure data integrity, the Program command sequence should be reinitiated once the device has completed the hardware reset operation.

A modified version of the Word Programming command, without unlock write cycles, is used for programming when entered into the Lock Register, Password, and PPB ASOs. The same command is used to change volatile bits when entered in to the PPB Lock, and DYB ASOs. See Table 6.1 on page 52 for program command sequences.




Figure 5.1 Word Program Operation



5.3.1.2 Write Buffer Programming

A write buffer is used to program data within a 512-byte address range aligned on a 512-byte boundary (Line). Thus, a full Write Buffer Programming operation must be aligned on a Line boundary. Programming operations of less than a full 512 bytes may start on any word boundary but may not cross a Line boundary. At the start of a Write Buffer programming operation all bit locations in the buffer are all 1's (FFFFh words) thus any locations not loaded will retain the existing data. See Product Overview on page 4 for information on address map.

Write Buffer Programming allows up to 512 bytes to be programmed in one operation. It is possible to program from 1 bit up to 512 bytes in each Write Buffer Programming operation. It is recommended that a multiple of Pages be written and each Page written only once. For the very best performance, programming should be done in full Lines of 512 bytes aligned on 512-byte boundaries.

Write Buffer Programming is supported only in the main flash array or the SSR ASO.

The Write Buffer Programming operation is initiated by first writing two unlock cycles. This is followed by a third write cycle of the Write to Buffer command with the Sector Address (SA), in which programming is to occur. Next, the system writes the number of word locations minus 1. This tells the device how many write buffer addresses are loaded with data and therefore when to expect the Program Buffer to flash confirm command. The Sector Address must match in the Write to Buffer command and the Write Word Count command. The Sector to be programmed must be unlocked (unprotected).

The system then writes the starting address / data combination. This starting address is the first address / data pair to be programmed, and selects the write-buffer-Line address. The Sector address must match the Write to Buffer Sector Address or the operation will abort and return to the initiating state. All subsequent address / data pairs must be in sequential order. All write buffer addresses must be within the same Line. If the system attempts to load data outside this range, the operation will abort and return to the initiating state.

The counter decrements for each data load operation. Note that while counting down the data writes, every write is considered to be data being loaded into the write buffer. No commands are possible during the write buffer loading period. The only way to stop loading the write buffer is to write with an address that is outside the Line of the programming operation. This invalid address will immediately abort the Write to Buffer command.

Once the specified number of write buffer locations has been loaded, the system must then write the Program Buffer to Flash command at the Sector Address. The device then goes busy. The Embedded Program algorithm automatically programs and verifies the data for the correct data pattern. The system is not required to provide any controls or timings during these operations. If an incorrect number of write buffer locations have been loaded the operation will abort and return to the initiating state. The abort occurs when anything other than the Program Buffer to Flash is written when that command is expected at the end of the word count.

The write-buffer embedded programming operation can be suspended using the Program Suspend command. When the Embedded Program algorithm is complete, the EAC then returns to the EAC standby or Erase Suspend standby state where the programming operation was started.

The system can determine the status of the program operation by using Data Polling Status, reading the Status Register, or monitoring the RY/BY# output. See Status Register on page 31 for information on these status bits. See Data Polling Status on page 32 for information on these status bits. See Figure 5.2 on page 23 for a diagram of the programming operation.

The Write Buffer Programming Sequence will be Aborted under the following conditions:

- Load a Word Count value greater than the buffer size (255).
- Write an address that is outside the Line provided in the Write to Buffer command.
- The Program Buffer to Flash command is not issued after the Write Word Count number of data words is loaded.

When any of the conditions that cause an abort of write buffer command occur the abort will happen immediately after the offending condition, and will indicate a Program Fail in the Status Register at bit location 4 (PSB = 1) due to Write Buffer Abort bit location 3 (WBASB = 1). The next successful program operation will clear the failure status or a Clear Status Register may be issued to clear the PSB status bit.

The Write Buffer Programming Sequence can be stopped by the following: Hardware Reset or Power cycle. However, these using either of these methods may leave the area being programmed in an intermediate state with invalid or unstable data values. In this case the same area will need to be reprogrammed with the same data or erased to ensure data values are properly programmed or erased.

Document Number: 001-98285 Rev. *J Page 22 of 102






Figure 5.2 Write Buffer Programming Operation with Data Polling Status

Notes:

- 1. DQ7 should be rechecked even if DQ5 = 1 because DQ7 may change simultaneously with DQ5.
- If this flowchart location was reached because DQ5 = 1, then the device FAILED. If this flowchart location was reached because DQ1 = 1, then the Write Buffer operation was ABORTED. In either case the proper RESET command must be written to the device to return the device to READ mode. Write-Buffer-Programming-Abort-Rest if DQ1 = 1, either Software RESET or Write-Buffer-Programming-Abort-Reset if DQ5 = 1.
- 3. See Table 6.1, Command Definitions on page 52 for the command sequence as required for Write Buffer Programming.
- 4. When Sector Address is specified, any address in the selected sector is acceptable. However, when loading Write-Buffer address locations with data, all addresses MUST fall within the selected Write-Buffer Page.






Figure 5.3 Write Buffer Programming Operation with Status Register

Notes.

- 1. See Table 6.1, Command Definitions on page 52 for the command sequence as required for Write Buffer Programming.
- 2. When Sector Address is specified, any address in the selected sector is acceptable. However, when loading Write-Buffer address locations with data, all addresses MUST fall within the selected Write-Buffer Page.



Table 5.1 Write Buffer Programming Command Sequence

Sequence	Address	Data	Comment
Issue Unlock Command 1	555/AAA	AA	
Issue Unlock Command 2	2AA/555	55	
Issue Write to Buffer Command at Sector Address	SA	0025h	
Issue Number of Locations at Sector Address	SA	WC	WC = number of words to program - 1
Example: WC of 0 = 1 words to pgm			
WC of 1 = 2 words to pgm			
Load Starting Address / Data pair	Starting Address	PD	Selects Write-Buffer-Page and loads first Address/Data Pair.
Load next Address / Data pair	WBL	PD	All addresses MUST be within the selected write-buffer- page boundaries, and have to be loaded in sequential order.
Load LAST Address/Data pair	WBL	PD	All addresses MUST be within the selected write-buffer- page boundaries, and have to be loaded in sequential order.
Issue Write Buffer Program Confirm at Sector Address	SA	0029h	This command MUST follow the last write buffer location loaded, or the operation will ABORT.
Device goes busy.			

Legend:

SA = Sector Address (Non-Sector Address bits are don't care. Any address within the Sector is sufficient.)

WBL = Write Buffer Location (MUST be within the boundaries of the Write-Buffer-Line specified by the Starting Address.)

WC =Word Count

PD = Program Data

5.3.2 Program Suspend / Program Resume Commands

The Program Suspend command allows the system to interrupt an embedded programming operation so that data can read from any non-suspended Line. When the Program Suspend command is written during a programming process, the device halts the programming operation within t_{PSL} (program suspend latency) and updates the status bits. Addresses are don't-cares when writing the Program Suspend command.

There are two commands available for program suspend. The legacy combined Erase / Program suspend command (B0h command code) and the separate Program Suspend command (51h command code). There are also two commands for Program resume. The legacy combined Erase / Program resume command (30h command code) and the separate Program Resume command (50h command code). It is recommended to use the separate program suspend and resume commands for programming and use the legacy combined command only for erase suspend and resume.

After the programming operation has been suspended, the system can read array data from any non-suspended Line. The Program Suspend command may also be issued during a programming operation while an erase is suspended. In this case, data may be read from any addresses not in Erase Suspend or Program Suspend.

After the Program Resume command is written, the device reverts to programming and the status bits are updated. The system can determine the status of the program operation by reading the Status Register or using Data Polling. Refer to Status Register on page 31 for information on these status bits. Refer to Data Polling Status on page 32 for more information.

Accesses and commands that are valid during Program Suspend are:

- Read to any other non-erase-suspended sector
- Read to any other non-program-suspended Line
- Status Read command
- Exit ASO or Command Set Exit
- Program Resume command



The system must write the Program Resume command to exit the Program Suspend mode and continue the programming operation. Further writes of the Program Resume command are ignored. Another Program Suspend command can be written after the device has resumed programming.

Program operations can be interrupted as often as necessary but in order for a program operation to progress to completion there must be some periods of time between resume and the next suspend command greater than or equal to t_{PRS} in Embedded Algorithm Controller (EAC) on page 19.

Program suspend and resume is not supported while entered in an ASO. While in program suspend entry into ASO is not supported.

5.3.3 Blank Check

The Blank Check command will confirm if the selected main flash array sector is erased. The Blank Check command does not allow for reads to the array during the Blank Check. Reads to the array while this command is executing will return unknown data.

To initiate a Blank Check on a Sector, write 33h to address 555h in the Sector, while the EAC is in the standby state

The Blank Check command may not be written while the device is actively programming or erasing or suspended.

Use the Status Register read to confirm if the device is still busy and when complete if the sector is blank or not. Bit 7 of the Status Register will show if the device is performing a Blank Check (similar to an erase operation). Bit 5 of the Status Register will be cleared to 0 if the sector is erased and set to 1 if not erased.

As soon as any bit is found to not be erased, the device will halt the operation and report the results.

Once the Blank Check is completed, the EAC will return to the Standby State.

5.3.4 Erase Methods

5.3.4.1 Chip Erase

The chip erase function erases the entire main Flash Memory Array. The device does not require the system to preprogram prior to erase. The Embedded Erase algorithm automatically programs and verifies the entire memory for an all 0 data pattern prior to electrical erase. After a successful chip erase, all locations within the device contain FFFFh. The system is not required to provide any controls or timings during these operations. The chip erase command sequence is initiated by writing two unlock cycles, followed by a set up command. Two additional unlock write cycles are then followed by the chip erase command, which in turn invokes the Embedded Erase algorithm. When WE# goes high, at the end of the 6th cycle, the RY/BY# goes low.

When the Embedded Erase algorithm is complete, the EAC returns to the standby state. Note that while the Embedded Erase operation is in progress, the system can not read data from the device. The system can determine the status of the erase operation by reading RY/BY#, the Status Register or using Data Polling. Refer to Status Register on page 31 for information on these status bits. Refer to Data Polling Status on page 32 for more information.

Once the chip erase operation has begun, only a Status Read, Hardware RESET or Power cycle are valid. All other commands are ignored. However, a Hardware Reset or Power Cycle immediately terminates the erase operation and returns to read mode after t_{RPH} time. If a chip erase operation is terminated, the chip erase command sequence must be reinitiated once the device has returned to the idle state to ensure data integrity.

See Table 5.4 on page 40, Asynchronous Write Operations on page 79 and Alternate CE# Controlled Write Operations on page 85 for parameters and timing diagrams.

Sectors protected by the ASP DYB and PPB lock bits will not be erased. See ASP on page 13. If a sector is protected during chip erase, chip erase will skip the protected sector and continue with next sector erase. The status register erase status bit and sector lock bit are not set to 1 by a failed erase on a protected sector.



5.3.4.2 Sector Erase

The sector erase function erases one sector in the memory array. The device does not require the system to preprogram prior to erase. The Embedded Erase algorithm automatically programs and verifies the entire sector for an all 0 data pattern prior to electrical erase. After a successful sector erase, all locations within the erased sector contain FFFFh. The system is not required to provide any controls or timings during these operations. The sector erase command sequence is initiated by writing two unlock cycles, followed by a set up command. Two additional unlock write cycles are then followed by the address of the sector to be erased, and the sector erase command. When WE# goes high, at the end of the 6th cycle, the RY/BY# goes low.

The system can determine the status of the erase operation by reading the Status Register or using Data Polling. Refer to Status Register on page 31 for information on these status bits. Refer to Data Polling Status on page 32 for more information.

Once the sector erase operation has begun, the Status Register Read and Erase Suspend commands are valid. All other commands are ignored. However, note that a hardware reset immediately terminates the erase operation and returns to read mode after t_{RPH} time. If a sector erase operation is terminated, the sector erase command sequence must be reinitiated once the device has reset operation to ensure data integrity.

See Embedded Algorithm Controller (EAC) on page 19 for parameters and timing diagrams.

Sectors protected by the ASP DYB and PPB lock bits will not be erased. See ASP on page 13.




Figure 5.4 Sector Erase Operation



5.3.5 Erase Suspend / Erase Resume

The Erase Suspend command allows the system to interrupt a sector erase operation and then read data from, or program data to, the main flash array. This command is valid only during sector erase or program operation. The Erase Suspend command is ignored if written during the chip erase operation.

When the Erase Suspend command is written during the sector erase operation, the device requires a maximum of t_{ESL} (erase suspend latency) to suspend the erase operation and update the status bits.

After the erase operation has been suspended, the part enters the erase-suspend mode. The system can read data from or program data to the main flash array. Reading at any address within erase-suspended sectors produces undetermined data. The system can determine if a sector is actively erasing or is erase-suspended by reading the Status Register or using Data Polling. Refer to Status Register on page 31 for information on these status bits. Refer to Data Polling Status on page 32 for more information.

After an erase-suspended program operation is complete, the EAC returns to the erase-suspend state. The system can determine the status of the program operation by reading the Status Register, just as in the standard program operation.

If a program failure occurs during erase suspend the Clear or Reset commands will return the device to the erase suspended state. Erase will need to be resumed and completed before again trying to program the memory array.

Accesses and commands that are valid during Erase Suspend are:

- Read to any other non-suspended sector
- Program to any other non-suspended sector
- Status Register Read
- Status Register Clear
- Enter DYB ASO
- DYB Set
- DYB Clear
- DYB Status Read
- Exit ASO or Command Set Exit
- Erase Resume command

To resume the sector erase operation, the system must write the Erase Resume command. The device will revert to erasing and the status bits will be updated. Further writes of the Resume command are ignored. Another Erase Suspend command can be written after the chip has resumed erasing.

Erase suspend and resume is not supported while entered in an ASO. While in erase suspend entry into ASO is not supported.



5.3.6 ASO Entry and Exit

5.3.6.1 ID-CFI ASO

The system can access the ID-CFI ASO by issuing the ID-CFI Entry command sequence during Read Mode. This entry command uses the Sector Address (SA) in the command to determine which sector will be overlaid and which sector's protection state is reported in word location 2h. See the detail description Table 6.2 on page 56.

The ID-CFI ASO allows the following activities:

- Read ID-CFI ASO, using the same SA as used in the entry command.
- Read Sector Protection State at Sector Address (SA) + 2h. Location 2h provides volatile information on the current state of sector protection for the sector addressed. Bit 0 of the word at location 2h shows the logical NAND of the PPB and DYB bits related to the addressed sector such that if the sector is protected by either the PPB=0 or the DYB=0 bit for that sector the state shown is protected. (1= Sector protected, 0= Sector unprotected). This protection state is shown only for the SA selected when entering ID-CFI ASO. Reading other SA provides undefined data. To read a different SA protection state ASO exit command must be used and then enter ID-CFI ASO again with the new SA.
- ASO Exit

The following is a C source code example of using the CFI Entry and Exit functions. Refer to the *Cypress Low Level Driver User's Guide* (available on www.cypress.com) for general information on Cypress flash memory software development guidelines.

```
/* Example: CFI Entry command */
*( (UINT16 *)base_addr + 0x55 ) = 0x0098; /* write CFI entry command */
/* Example: CFI Exit command */
*( (UINT16 *)base addr + 0x000 ) = 0x00F0; /* write cfi exit command */
```

5.3.6.2 Status Register ASO

The Status Register ASO contains a single word of registered volatile status for Embedded Algorithms. When the Status Register read command is issued, the current status is captured (by the rising edge of WE#) into the register and the ASO is entered. The Status Register content appears on all word locations. The first read access exits the Status Register ASO (with the rising edge of CE# or OE#) and returns to the address space map in use when the Status Register read command was issued. Write commands will not exit the Status Register ASO state.

5.3.6.3 Secure Silicon Region ASO

The system can access the Secure Silicon Region by issuing the Secure Silicon Region Entry command sequence during Read Mode. This entry command uses the Sector Address (SA) in the command to determine which sector will be overlaid.

The Secure Silicon Region ASO allows the following activities:

- Read Secure Silicon Regions.
- Programming the customer Secure Silicon Region is allowed using the Word or Write Buffer Programming commands.
- ASO Exit using legacy Secure Silicon Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.



5.3.6.4 Lock Register ASO

The system can access the Lock Register by issuing the Lock Register entry command sequence during Read Mode. This entry command does not use a sector address from the entry command. The Lock Register appears at word location 0 in the device address space. All other locations in the device address space are undefined.

The Lock Register ASO allows the following activities:

- Read Lock Register, using device address location 0.
- Program the customer Lock Register using a modified Word Programming command.
- ASO Exit using legacy Command Set Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.

5.3.6.5 Password ASO

The system can access the Password ASO by issuing the Password entry command sequence during Read Mode. This entry command does not use a sector address from the entry command. The Password appears at word locations 0 to 3 in the device address space. All other locations in the device address space are undefined.

The Password ASO allows the following activities:

- Read Password, using device address location 0 to 3.
- Program the Password using a modified Word Programming command.
- Unlock the PPB Lock bit with the Password Unlock command.
- ASO Exit using legacy Command Set Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.

5.3.6.6 PPB ASO

The system can access the PPB ASO by issuing the PPB entry command sequence during Read Mode. This entry command does not use a sector address from the entry command. The PPB bit for a sector appears in bit 0 of all word locations in the sector.

The PPB ASO allows the following activities:

- Read PPB protection status of a sector in bit 0 of any word in the sector.
- Program the PPB bit using a modified Word Programming command.
- Erase all PPB bits with the PPB erase command.
- ASO Exit using legacy Command Set Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.

5.3.6.7 PPB Lock ASO

The system can access the PPB Lock ASO by issuing the PPB Lock entry command sequence during Read Mode. This entry command does not use a sector address from the entry command. The global PPB Lock bit appears in bit 0 of all word locations in the device.

The PPB Lock ASO allows the following activities:

- Read PPB Lock protection status in bit 0 of any word in the device address space.
- Set the PPB Lock bit using a modified Word Programming command.
- ASO Exit using legacy Command Set Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.



5.3.6.8 DYB ASO

The system can access the DYB ASO by issuing the DYB entry command sequence during Read Mode. This entry command does not use a sector address from the entry command. The DYB bit for a sector appears in bit 0 of all word locations in the sector.

The DYB ASO allows the following activities:

- Read DYB protection status of a sector in bit 0 of any word in the sector.
- Set the DYB bit using a modified Word Programming command.
- Clear the DYB bit using a modified Word Programming command.
- ASO Exit using legacy Command Set Exit command for backward software compatibility.
- ASO Exit using the common exit command for all ASO alternative for a consistent exit method.

5.3.6.9 Software (Command) Reset / ASO exit

Software reset is part of the command set (See Table 6.1, Command Definitions on page 52) that also returns the EAC to standby state and must be used for the following conditions:

- Exit ID/CFI mode
- Clear timeout bit (DQ5) for data polling when timeout occurs

Software Reset does not affect EA mode. Reset commands are ignored once programming or erasure has begun, until the operation is complete. Software Reset does not affect outputs; it serves primarily to return to Read Mode from an ASO mode or from a failed program or erase operation.

Software Reset may cause a return to Read Mode from undefined states that might result from invalid command sequences. However, a Hardware Reset may be required to return to normal operation from some undefined states.

There is no software reset latency requirement. The reset command is executed during the t_{WPH} period.

5.4 Status Monitoring

There are three methods for monitoring EA status. Previous generations of the S29GL flash family used the methods called Data Polling and Ready/Busy# (RY/BY#) Signal. These methods are still supported by the S29GL-S family. One additional method is reading the Status Register.

5.4.1 Status Register

The status of program and erase operations is provided by a single 16-bit status register. The status is receiver by writing the Status Register Read command followed by a read access. When the Status Register read command is issued, the current status is captured (by the rising edge of WE#) into the register and the ASO is entered. The contents of the status register is aliased (overlaid) on the full memory address space. Any valid read (CE# and OE# low) access while in the Status Register ASO will exit the ASO (with the rising edge of CE# or OE# for t_{CEPH}/t_{OEPH} time) and return to the address space map in use when the Status Register Read command was issued.

The status register contains bits related to the results - success or failure - of the most recently completed Embedded Algorithms (EA):

- Erase Status (bit 5).
- Program Status (bit 4),
- Write Buffer Abort (bit 3),
- Sector Locked Status (bit 1),
- RFU (bit 0).

and, bits related to the current state of any in process EA:

- Device Busy (bit 7),
- Erase Suspended (bit 6),
- Program Suspended (bit 2),



The current state bits indicate whether an EA is in process, suspended, or completed.

The upper 8 bits (bits 15:8) are reserved. These have undefined High or Low value that can change from one status read to another. These bits should be treated as don't care and ignored by any software reading status.

The Soft Reset Command will clear to 0 bits [5, 4, 1, 0] of the status register if Status Register bit 3 =0. It will not affect the current state bits. The Clear Status Register Command will clear to 0 the results related bits of the status register but will not affect the current state bits.

Table 5.2 Status Register

Bit #	15:8	7	6	5	4	3	2	1	0
Bit Description	Reserved	Device Ready Bit	Erase Suspend Status Bit	Erase Status Bit	Program Status Bit	Write Buffer Abort Status Bit	Program Suspend Status Bit	Sector Lock Status Bit	Reserved
Bit Name		DRB	ESSB	ESB	PSB	WBASB	PSSB	SLSB	
Reset Status	Х	1	0	0	0	0	0	0	0
Busy Status	Invalid	0	Invalid	Invalid	Invalid	Invalid	Invalid	Invalid	Invalid
Ready Status	Х	1	0=No Erase in Suspension 1=Erase in Suspension	0=Erase successful 1=Erase fail	0=Program successful 1=Program fail	0=Program not aborted 1=Program aborted during Write to Buffer command	0=No Program in suspension 1=Program in suspension	0=Sector not locked during operation 1=Sector locked error	х

Notes:

- 1. Bits 15 thru 8, and 0 are reserved for future use and may display as 0 or 1. These bits should be ignored (masked) when checking status.
- 2. Bit 7 is 1 when there is no Embedded Algorithm in progress in the device.
- 3. Bits 6 thru 1 are valid only if Bit 7 is 1.
- 4. All bits are put in their reset status by cold reset or warm reset.
- 5. Bits 5, 4, 3, and 1 are cleared to 0 by the Clear Status Register command or Reset command.
- 6. Upon issuing the Erase Suspend Command, the user must continue to read status until DRB becomes 1.
- 7. ESSB is cleared to 0 by the Erase Resume Command.
- 8. ESB reflects success or failure of the most recent erase operation.
- 9. PSB reflects success or failure of the most recent program operation.
- 10. During erase suspend, programming to the suspended sector, will cause program failure and set the Program status bit to 1.
- 11. Upon issuing the Program Suspend Command, the user must continue to read status until DRB becomes 1.
- 12. PSSB is cleared to 0 by the Program Resume Command.
- 13. SLSB indicates that a program or erase operation failed because the sector was locked.
- 14. SLSB reflects the status of the most recent program or erase operation.

5.4.2 Data Polling Status

During an active Embedded Algorithm the EAC switches to the Data Polling ASO to display EA status to any read access. A single word of status information is aliased in all locations of the device address space. In the status word there are several bits to determine the status of an EA. These are referred to as DQ bits as they appear on the data bus during a read access while an EA is in progress. DQ bits 15 to 8, DQ4, and DQ0 are reserved and provide undefined data. Status monitoring software must mask the reserved bits and treat them as don't care. Table 5.3 on page 36 and the following subsections describe the functions of the remaining bits.



5.4.2.1 DQ7: Data# Polling

The Data# Polling bit, DQ7, indicates to the host system whether an Embedded Algorithm is in progress or has completed. Data# Polling is valid after the rising edge of the final WE# pulse in the program or erase command sequence. Note that the Data# Polling is valid only for the last word being programmed in the write-buffer-page during Write Buffer Programming. Reading Data# Polling status on any word other than the last word to be programmed in the write-buffer-page will return false status information.

During the Embedded Program algorithm, the device outputs on DQ7 the complement of the data bit programmed to DQ7. This DQ7 status also applies to programming during Erase Suspend. When the Embedded Program algorithm is complete, the device outputs the data bit programmed to bit 7 of the last word programmed. In case of a Program Suspend, the device allows only reading array data. If a program address falls within a protected sector, Data# Polling on DQ7 is active for approximately 20 μ s, then the device returns to reading array data.

During the Embedded Erase or Blank Check algorithms, Data# Polling produces a 0 on DQ7. When the algorithm is complete, or if the device enters the Erase Suspend mode, Data# Polling produces a 1 on DQ7. This is analogous to the complement / true datum output described for the Embedded Program algorithm: the erase function changes all the bits in a sector to 1; prior to this, the device outputs the complement or '0'. The system must provide an address within the sector selected for erasure to read valid status information on DQ7.

After an erase command sequence is written, if the sector selected for erasing is protected, Data# Polling on DQ7 is active for approximately 100 µs, then the device returns to reading array data.

When the system detects DQ7 has changed from the complement to true data, it can read valid data at DQ15-DQ0 on the following read cycles. This is because DQ7 may change asynchronously with DQ6-DQ0 while Output Enable (OE#) is asserted Low. This is illustrated in Figure 10.17 on page 84. Table 5.3 on page 36 shows the outputs for Data# polling on DQ7. Figure 5.2 on page 23 shows the Data# polling algorithm use in Write Buffer Programming.

Valid DQ7 data polling status may only be read from:

- the address of the last word loaded into the Write Buffer for a Write Buffer programming operation;
- the location of a single word programming operation;
- or a location in a sector being erased or blank checked;
- or a location in any sector during chip erase.

Read DQ7-DQ0

No

No

DQ5 = 1?

Yes

Read DQ7 -DQ0

PASS

PASS

Figure 5.5 Data# Polling Algorithm

Note:

1. DQ7 should be rechecked even if DQ5 = 1 because DQ7 may change simultaneously with DQ5.



5.4.2.2 DQ6: Toggle Bit I

Toggle Bit I on DQ6 indicates whether an Embedded Program or Erase algorithm is in progress or complete, or whether the device has entered the Program Suspend or Erase Suspend mode. Toggle Bit I may be read at any address, and is valid after the rising edge of the final WE# pulse in the command sequence (prior to the program or erase operation).

During an Embedded Program or Erase algorithm operation, successive read cycles to any address cause DQ6 to toggle. (The system may use either OE# or CE# to control the read cycles). When the operation is complete, DQ6 stops toggling.

After an erase command sequence is written, if the sector selected for erasing is protected, DQ6 toggles for approximately 100 µs, then the EAC returns to standby (Read Mode). If the selected sector is not protected, the Embedded Erase algorithm erases the unprotected sector.

The system can use DQ6 and DQ2 together to determine whether a sector is actively erasing or erase-suspended. When the device is actively erasing (that is, the Embedded Erase algorithm is in progress), DQ6 toggles. When the device enters the Program Suspend mode or Erase Suspend mode, DQ6 stops toggling. However, the system must also use DQ2 to determine which sectors are erasing, or erase-suspended. Alternatively, the system can use DQ7 (see DQ7: Data# Polling on page 33).

DQ6 also toggles during the erase-suspend-program mode, and stops toggling once the Embedded Program algorithm is complete.

Table 5.3 on page 36 shows the outputs for Toggle Bit I on DQ6. Figure 5.6 on page 35 shows the toggle bit algorithm in flowchart form, and the Reading Toggle Bits DQ6/DQ2 on page 35 explains the algorithm. Figure 5.6 on page 35 shows the toggle bit timing diagrams. Figure 5.2 on page 23 shows the differences between DQ2 and DQ6 in graphical form. See also DQ2: Toggle Bit II on page 34.

5.4.2.3 DQ3: Sector Erase Timer

After writing a sector erase command sequence, the system may read DQ3 to determine whether or not erasure has begun. See Sector Erase on page 27 for more details.

After the sector erase command is written, the system should read the status of DQ7 (Data# Polling) or DQ6 (Toggle Bit I) to ensure that the device has accepted the command sequence, and then read DQ3. If DQ3 is 1, the Embedded Erase algorithm has begun; all further commands (except Erase Suspend) are ignored until the erase operation is complete. Table 5.3 on page 36 shows the status of DQ3 relative to the other status bits.

5.4.2.4 DQ2: Toggle Bit II

Toggle Bit II on DQ2, when used with DQ6, indicates whether a particular sector is actively erasing (that is, the Embedded Erase algorithm is in progress), or whether that sector is erase-suspended. Toggle Bit II is valid after the rising edge of the final WE# pulse in the command sequence.

DQ2 toggles when the system reads at addresses within the sector selected for erasure. (The system may use either OE# or CE# to control the read cycles). But DQ2 cannot distinguish whether the sector is actively erasing or is erase-suspended. DQ6, by comparison, indicates whether the device is actively erasing, or is in Erase Suspend, but cannot distinguish if the sector is selected for erasure. Thus, both status bits are required for sector and mode information. Refer to Table 5.3 on page 36 to compare outputs for DQ2 and DQ6. Figure 5.5 on page 33 shows the toggle bit algorithm in flowchart form, and the Reading Toggle Bits DQ6/DQ2 on page 35 explains the algorithm. See also Figure 5.6 on page 35 shows the toggle bit timing diagram. Figure 5.2 on page 23 shows the differences between DQ2 and DQ6 in graphical form.



5.4.2.5 Reading Toggle Bits DQ6/DQ2

Refer to Figure 5.5 on page 33 for the following discussion. Whenever the system initially begins reading toggle bit status, it must read DQ7-DQ0 at least twice in a row to determine whether a toggle bit is toggling. Typically, the system would note and store the value of the toggle bit after the first read. After the second read, the system would compare the new value of the toggle bit with the previous value. If the toggle bit is not toggling, the device has completed the program or erases operation. The system can read array data on DQ15-DQ0 on the following read cycle.

However, if after the initial two read cycles, the system determines that the toggle bit is still toggling, the system also should note whether the value of DQ5 is High (see DQ5: Exceeded Timing Limits on page 35). If it is, the system should then determine again whether the toggle bit is toggling, since the toggle bit may have stopped toggling just as DQ5 went High. If the toggle bit is no longer toggling, the device has successfully completed the program or erase operation. If it is still toggling, the device did not complete the operation successfully, and the system must write the reset command to return to reading array data.

The remaining scenario is that the system initially determines that the toggle bit is toggling and DQ5 has not gone High. The system may continue to monitor the toggle bit and DQ5 through successive read cycles, determining the status as described in the previous paragraph. Alternatively, it may choose to perform other system tasks. In this case, the system must start at the beginning of the algorithm when it returns to determine the status of the operation (top of Figure 5.6 on page 35).




Figure 5.6 Toggle Bit Program

Notes:

- 1. Read toggle bit twice to determine whether or not it is toggling. See text.
- 2. Recheck toggle bit because it may stop toggling as DQ5 changes to 1. See text.

5.4.2.6 DQ5: Exceeded Timing Limits

DQ5 indicates whether the program or erase time has exceeded a specified internal pulse count limit. Under these conditions DQ5 produces a 1. This is a failure condition that indicates the program or erase cycle was not successfully completed. The system must issue the reset command to return the device to reading array data.

When a timeout occurs, the software must send a reset command to clear the timeout bit (DQ5) and to return the EAC to read array mode. In this case, it is possible that the flash will continue to communicate busy for up to 2 µs after the reset command is sent.



5.4.2.7 DQ1: Write-to-Buffer Abort

DQ1 indicates whether a Write-to-Buffer operation was aborted. Under these conditions DQ1 produces a 1. The system must issue the Write-to-Buffer-Abort-Reset command sequence to return the EAC to standby (Read Mode) and the Status Register failed bits are cleared. See Write Buffer Programming on page 22 for more details.

Table 5.3 Data Polling Status

Operation		DQ7 (Note 2)	DQ6	DQ5 (Note 1)	DQ3	DQ2 (Note 2)	DQ1 (Note 4)	RY/BY#
Standard Mode	Embedded Program Algorithm	DQ7#	Toggle	0	N/A	No Toggle	0	0
	Reading within Erasing Sector	0	Toggle	0	1	Toggle	N/A	0
	Reading Outside erasing Sector	0	Toggle	0	1	No Toggle	N/A	0
Program Suspend Mode (Note 3)	Reading within Program Suspended	INVALID	INVALID	INVALID	INVALID	INVALID	INVALID	1
	Sector Sector	(Not Allowed)	(Not Allowed)	(Not Allowed)	(Not Allowed)	(Not Allowed)	(Not Allowed)	
	Reading within Non-Program Suspended Sector	Data	Data	Data	Data	Data	Data	1
Erase Suspend Mode	Reading within Erase Suspended Sector	1	No Toggle	0	N/A	Toggle	N/A	1
	Reading within Non-Erase Suspend Sector	Data	Data	Data	Data	Data	Data	1
	Programming within Non-Erase Suspended Sector	DQ7#	Toggle	0	N/A	N/A	N/A	0
Write-to- Buffer (Notes 4, 5)	BUSY State	DQ7#	Toggle	0	N/A	No Toggle	0	0
	Exceeded Timing Limits	DQ7#	Toggle	1	N/A	N/A	0	0
	ABORT State	DQ7#	Toggle	0	N/A	N/A	1	0

Notes:

^{1.} DQ5 switches to '1' when an Embedded Program or Embedded Erase operation has exceeded the maximum timing limits. See DQ5: Exceeded Timing Limits on page 35 for more information.

^{2.} DQ7 and DQ2 require a valid address when reading status information. Refer to the appropriate subsection for further details.

^{3.} Data are invalid for addresses in a Program Suspended Line. All addresses other than the program suspended line can be read for valid data.

^{4.} DQ1 indicates the Write-to-Buffer ABORT status during Write-Buffer-Programming operations.

^{5.} Applies only to program operations.



5.5 Error Types and Clearing Procedures

There are three types of errors reported by the embedded operation status methods. Depending on the error type, the status reported and procedure for clearing the error status is different. Following is the clearing of error status:

- If an ASO was entered before the error the device remains entered in the ASO awaiting ASO read or a command write.
- If an erase was suspended before the error the device returns to the erase suspended state awaiting flash array read or a command write.
- Otherwise, the device will be in standby state awaiting flash array read or a command write.

5.5.1 Embedded Operation Error

If an error occurs during an embedded operation (program, erase, blank check, or password unlock) the device (EAC) remains busy. The RY/BY# output remains Low, data polling status continues to be overlaid on all address locations, and the status register shows ready with valid status bits. The device remains busy until the error status is detected by the host system status monitoring and the error status is cleared.

During embedded algorithm error status the Data Polling status will show the following:

- DQ7 is the inversion of the DQ7 bit in the last word loaded into the write buffer or last word of the password in the case of the password unlock command. DQ7 = 0 for an erase or blank check failure
- DQ6 continues to toggle
- DQ5 = 1; Failure of the embedded operation
- DQ4 is RFU and should be treated as don't care (masked)
- DQ3 = 1 to indicate embedded sector erase in progress
- DQ2 continues to toggle, independent of the address used to read status
- DQ1 = 0; Write buffer abort error
- DQ0 is RFU and should be treated as don't care (masked)

During embedded algorithm error status the Status Register will show the following:

- SR[7] = 1; Valid status displayed
- SR[6] = X; May or may not be erase suspended during the EA error
- SR[5] = 1 on erase or blank check error; else = 0
- SR[4] = 1 on program or password unlock error; else = 0
- SR[3] = 0; Write buffer abort
- SR[2] = 0; Program suspended
- SR[1] = 0; Protected sector
- SR[0] = X; RFU, treat as don't care (masked)

When the embedded algorithm error status is detected, it is necessary to clear the error status in order to return to normal operation, with RY/BY# High, ready for a new read or command write. The error status can be cleared by writing:

- Reset command
- Status Register Clear command

Commands that are accepted during embedded algorithm error status are:

- Status Register Read
- Reset command
- Status Register Clear command



5.5.2 Protection Error

If an embedded algorithm attempts to change data within a protected area (program, or erase of a protected sector or OTP area) the device (EAC) goes busy for a period of 20 to 100 μ s then returns to normal operation. During the busy period the RY/BY# output remains Low, data polling status continues to be overlaid on all address locations, and the status register shows not ready with invalid status bits (SR[7] = 0).

During the protection error status busy period the data polling status will show the following:

- DQ7 is the inversion of the DQ7 bit in the last word loaded into the write buffer. DQ7 = 0 for an erase failure
- DQ6 continues to toggle, independent of the address used to read status
- DQ5 = 0; to indicate no failure of the embedded operation during the busy period
- DQ4 is RFU and should be treated as don't care (masked)
- DQ3 = 1 to indicate embedded sector erase in progress
- DQ2 continues to toggle, independent of the address used to read status
- DQ1 = 0; Write buffer abort error
- DQ0 is RFU and should be treated as don't care (masked)

Commands that are accepted during the protection error status busy period are:

■ Status Register Read

When the busy period ends the device returns to normal operation, the data polling status is no longer overlaid, RY/BY# is High, and the status register shows ready with valid status bits. The device is ready for flash array read or write of a new command.

After the protection error status busy period the Status Register will show the following:

- SR[7] = 1; Valid status displayed
- SR[6] = X; May or may not be erase suspended after the protection error busy period
- \blacksquare SR[5] = 1 on erase error, else = 0
- SR[4] = 1 on program error, else = 0
- SR[3] = 0; Program not aborted
- SR[2] = 0; No Program in suspension
- SR[1] = 1; Error due to attempting to change a protected location
- SR[0] = X; RFU, treat as don't care (masked)

Commands that are accepted after the protection error status busy period are:

Any command

Document Number: 001-98285 Rev. *J



5.5.3 Write Buffer Abort

If an error occurs during a Write to Buffer command the device (EAC) remains busy. The RY/BY# output remains Low, data polling status continues to be overlaid on all address locations, and the status register shows ready with valid status bits. The device remains busy until the error status is detected by the host system status monitoring and the error status is cleared.

During write to buffer abort (WBA) error status the Data Polling status will show the following:

- DQ7 is the inversion of the DQ7 bit in the last word loaded into the write buffer
- DQ6 continues to toggle, independent of the address used to read status
- DQ5 = 0; to indicate no failure of the programming operation. WBA is an error in the values input by the Write to Buffer command before the programming operation can begin
- DQ4 is RFU and should be treated as don't care (masked)
- DQ3 is don't care after program operation as no erase is in progress. If the Write Buffer Program operation was started after an erase operation had been suspended then DQ3 = 1. If there was no erase operation in progress then DQ3 is a don't care and should be masked.
- DQ2 does not toggle after program operation as no erase is in progress. If the Write Buffer Program operation was started after an erase operation had been suspended then DQ2 will toggle in the sector where the erase operation was suspended and not in any other sector. If there was no erase operation in progress then DQ2 is a don't care and should be masked.
- DQ1 = 1: Write buffer abort error
- DQ0 is RFU and should be treated as don't care (masked)

During embedded algorithm error status the Status Register will show the following:

- SR[7] = 1; Valid status displayed
- SR[6] = X; May or may not be erase suspended during the WBA error status
- SR[5] = 0; Erase successful
- SR[4] = 1; Programming related error
- SR[3] = 1; Write buffer abort
- SR[2] = 0; No Program in suspension
- SR[1] = 0; Sector not locked during operation
- SR[0] = X; RFU, treat as don't care (masked)

When the WBA error status is detected, it is necessary to clear the error status in order to return to normal operation, with RY/BY# High, ready for a new read or command write. The error status can be cleared and device returned to normal operation by writing:

- Write Buffer Abort Reset command
 - -Clears the status register and returns to normal operation
- Status Register Clear command

Commands that are accepted during embedded algorithm error status are:

- Status Register Read
- Write Buffer Abort Reset command
- Status Register Clear command



5.6 Embedded Algorithm Performance Table

Table 5.4 Embedded Algorithm Characteristics (–40 °C to +85°C)

Parameter		Typ (Note 2)	Max (Note 3)	Unit	Comments
Sector Erase Time 128 kbyte		275	1100	ms	Includes pre-programming prior to erasure (Note 5)
Single Word Programming Time	(Note 1)	125	400	μs	
	2-byte (Note 1)	125	750		
	32-byte (Note 1)	160	750		
Duffer Dresserenies a Times	64-byte (Note 1)	175	750		
Buffer Programming Time	128-byte (Note 1)	198	750	μs	
	256-byte (Note 1)	239	750		
	512-byte	340	750		
Effective Write Buffer Program Operation per Word	512-byte	1.33		μs	
Sector Programming Time 128 k Programming)	B (full Buffer	108	192	ms	(Note 6)
Erase Suspend/Erase Resume (t _{ESL})		40	μs	
Program Suspend/Program Resu	ıme (t _{PSL})		40	μs	
Erase Resume to next Erase Su	spend (t _{ERS})	100		μs	Minimum of 60 ns but ≥ typical periods are needed for Erase to progress to completion.
Program Resume to next Progra	m Suspend (t _{PRS})	100		μs	Minimum of 60 ns but ≥ typical periods are needed for Program to progress to completion.
Blank Check		6.2	8.5	ms	
NOP (Number of Program-opera	tions, per Line)		256		

Notes:

- 1. Not 100% tested.
- $2. \ \ \, \text{Typical program and erase times assume the following conditions: } 25^{\circ}\text{C}, \, 3.0 \text{V V}_{\text{CC}}, \, 10,000 \text{ cycle, and a random data pattern.}$
- 3. Under worst case conditions of 90°C, $V_{\rm CC}$ = 2.70V, 100,000 cycles, and a random data pattern.
- 4. Effective write buffer specification is based upon a 512-byte write buffer operation.
- 5. In the pre-programming step of the Embedded Erase algorithm, all words are programmed to 0000h before Sector and Chip erasure.
- 6. System-level overhead is the time required to execute the bus-cycle sequence for the program command. See Table 6.1, Command Definitions on page 52 for further information on command definitions.

Document Number: 001-98285 Rev. *J Page 40 of 102



Table 5.5 Embedded Algorithm Characteristics (-40°C to +105°C)

Parameter		Typ (Note 2)	Max (Note 3)	Unit	Comments
Sector Erase Time 128 kbyte		275	1100	ms	Includes pre-programming prior to erasure (Note 5)
Single Word Programming Time	(Note 1)	125	400	μs	
	2-byte (Note 1)	150	1050		
	32-byte (Note 1)	200	1050		
Buffer Programming Time	64-byte (Note 1)	220	1050		
Builer Programming Time	128-byte (Note 1)	250	1050	μs	
	256-byte (Note 1)	320	1050		
	512-byte	420	1050		
Effective Write Buffer Program Operation per Word	512-byte	1.64		μs	
Sector Programming Time 128 k Programming)	B (full Buffer	108	269	ms	(Note 6)
Erase Suspend/Erase Resume (t _{ESL})		50	μs	
Program Suspend/Program Resu	ıme (t _{PSL})		50	μs	
Erase Resume to next Erase Sus	spend (t _{ERS})	100		μs	Minimum of 60 ns but ≥ typical periods are needed for Erase to progress to completion.
Program Resume to next Progra	m Suspend (t _{PRS})	100		μs	Minimum of 60 ns but ≥ typical periods are needed for Program to progress to completion.
Blank Check		7.6	9.0	ms	
NOP (Number of Program-opera	tions, per Line)		1 per 16 word		

Notes:

- 1. Not 100% tested.
- 2. Typical program and erase times assume the following conditions: 25° C, 3.0V V_{CC} , 10,000 cycle, and a random data pattern.
- 3. Under worst case conditions of 105°C, $V_{\rm CC}$ = 2.70V, 100,000 cycles, and a random data pattern.
- 4. Effective write buffer specification is based upon a 512-byte write buffer operation.
- 5. In the pre-programming step of the Embedded Erase algorithm, all words are programmed to 0000h before Sector and Chip erasure.
- 6. System-level overhead is the time required to execute the bus-cycle sequence for the program command. See Table 6.1, Command Definitions on page 52 for further information on command definitions.

Document Number: 001-98285 Rev. *J Page 41 of 102



5.6.1 Command State Transitions

Table 5.6 Read Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Blank Check	CFI Entry
	Address	RA	xh	x555h	x555h	x555h	(SA)555h	(SA)55h
	Data	RD	xF0h	x70h	x71h	xAAh	x33h	x98h
	-			READSR			-	
READ	Read Protect = False	READ	READ	(READ)	READ	READUL1	BLCK	CFI
READSR	-	(return)	-	=	=	-	-	=

Table 5.7 Read Unlock Command State Transition

Current State	Command and Condition	Read	Status Registe r Read Enter	Unlock 2	Word Progra m Entry	Write to Buffer Enter	Erase Enter	ID (Auto- select) Entry	SSR Entry	Lock Registe r Entry	Pass- word ASO Entry	PPB Entry	PPB Lock Entry	DYB ASO Entry
	Address	RA	x555h	x2AAh	x555h	(SA)xh	x555h	(SA)555 h	(SA)555 h	x555h	x555h	x555h	x555h	x555h
	Data	RD	x70h	x55h	xA0h	x25h	x80h	x90h	x88h	x40h	x60h	xC0h	x50h	xE0h
READUL 1	-	READ UL1	READS R (READ)	READ UL2	-	-	-	-	-	-	-	-	-	-
	Read Protect = True				-	-	-		-	-			-	-
READUL 2	Read Protect = False	READ UL2	READS R (READ)	-				CFI			PP	-	PPBL	
	Read Protect = False and LR(8) = 0		(,,,)		PG1	WB	ER		SSR	LR		PPB	В	DYB

Table 5.8 Erase State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Unlock 2	Chip Erase Start	Sector Erase Start	Erase Suspend Enhanced Method (2)
	Address	RA	xh	x555h	x555h	x555h	x2AAh	x555h	(SA)xh	xh
	Data	RD	xF0h	x70h	x71h	xAAh	x55h	x10h	x30h	xB0h
ER	-	ER	-	READSR (READ)	-	ERUL1	-	-	-	-
ERUL1	-	ERUL1	-	READSR (READ)	-	-	ERUL2	-	-	-
ERUL2	-	ERUL2	-	READSR (READ)	-	-	-	CER	SER	-
CER (1)	-	CER	-	ERSR (CER)	-	-	-	-	-	-
SER (1)	SR(7) = 0	SER	-	ERSR	-			_		ESR (ES)
SER (I)	SR(7) = 1	SER	READ	(SER)	READ	_	-	-	_	LON (ES)



Table 5.8 Erase State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Unlock 2	Chip Erase Start	Sector Erase Start	Erase Suspend Enhanced Method (2)
BLCK (1)	SR(7) = 0	BLCK	-	ERSR	-					
BLOK (1)	SR(7) = 1	BLCK	READ	(BLCK)	READ	_	-	-	-	-
ERSR	-	(return)								

Notes:

- 1. State will automatically move to READ state at the completion of the operation.
- 2. Also known as Erase Suspend/Program Suspend Legacy Method.

Table 5.9 Erase Suspend State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Sector Erase Start
	Address	RA	xh	x555h	x555h	x555h	(SA)xh
	Data	RD	xF0h	x70h	x71h	xAAh	x30h
ESR (1)	-	ESR		ERSR (ESR)	-	-	-
ES	SR(7) = 0	F.C.	ES	ECCD (EC)	ES	ESUL1	-
E2	SR(7) = 1	ES	ES	ESSR (ES)	ES	ESULI	SER
ESSR	-	(return)	-	-	-	-	-

Note:

Table 5.10 Erase Suspend Unlock State Command Transition

Current State	Command and Condition	Read	Softwar e Reset / ASO Exit	Status Registe r Read Enter	Unlock 1	Word Progra m Entry	Write to Buffer Enter	Write- to- Buffer- Abort Reset Start	Erase Resume Enhanced Method (1)	DYB ASO Entry			Vrite-to-l " Comm	
	Address	RA	xh	x555h	x2AAh	x555h	(SA)xh	x555h	xh	x555h	NOT x555h	xh	NOT x2AAh	xh
	Data	RD	xF0h	x70h	x55h	xA0h	x25h	xF0h	x30h	xE0h	xh	NOT xF0h	xh	NOT x55h
	-												-	-
ESUL1	SR(3) = 1	ESUL1	-	ESSR (ES)	ESUL2	-	-	-	-	-	-	-	ESPG	ESPG
	DQ(1) = 1			(20)									ESFG	ESFG
	-									-				
ESUL2	Read Protect = False	ESUL2	ES	ESSR (ES)	-	ESPG1	ES_W B	-	SER	ESDYB	-	-	-	-
	SR(3) = 1							ES		_	ESPG	ESPG		
	DQ(1) = 1		-					ES		-	LOFG	LOFG		

Note:

Document Number: 001-98285 Rev. *J

^{1.} State will automatically move to ES state by $t_{\rm ESL}$.

^{1.} Also known as Erase Resume/Program Resume Legacy Method.



Table 5.11 Erase Suspend - DYB State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Command Set Exit Entry	Command Set Exit	DYB Set/ Clear Entry	Password Word Count
	Address	RA	xh	x555h	x555h	xh	xh	xh	xh
	Data	RD	xF0h	x70h	x71h	x90h	x00h	xA0h	x03h
ESDYB	-	ESDYB	ES	ESSR (ESDYB)	ESDYB	ESDYBEX T	-	ESDYBSE T	-
ESDYBSET	-	ESDYBSET	-	-	-	-	-	-	-
ESDYBEXT	-	ESDYBEXT	-	-	-	-	ES	-	ES

Table 5.12 Erase Suspend - Program Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Erase Suspend Enhance d Method (1)	Program Suspend Enhance d Method	Write Data
	Address	RA	xh	x555h	x555h	x555h	xh	xh	xh
	Data	RD	xF0h	x70h	x71h	xAAh	xB0h	x51h	xh
ES WB	WC > 256 or SA ≠ SA	ES WB							ESPG
E9_WB	WC ≤ 256 and SA = SA	E2_WB	-	-	-	-	-	-	ES_WB_ D
ES_WB_D	WC < 0 or Write Buffer ≠ Write Buffer	ES_WB_D							ESPG
ES_WB_D	WC > 0 and Write Buffer = Write Buffer	ES_WB_D	-	-	-	-	-	-	ES_WB_ D
ESPG1	-	ESPG1	-	-	-	-	-	-	ESPG
ESPG	SR(7) = 0	ESPG	-	ESPGSR	-	-	ESPSR	ESPSR	ESPG
LSFG	SR(7) = 1	LSFG	ES	(ESPG)	ES	ESUL1	(ESPG)	(ESPG)	LSFG
ESPGSR	-	(return)	-	-	-	-	-	-	(return)

Note:

 Table 5.13 Erase Suspend - Program Suspend Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Unlock 2	Erase Resume Enhanced Method (2)	Program Resume Enhanced Method
	Address	RA	xh	x555h	x555h	x555h	x2AAh	xh	xh
	Data	RD	xF0h	x70h	x71h	xAAh	x55h	x30h	x50h
ESPSR (1)	-	ESPSR	-	ESPGSR (ESPSR)	-	-	-	-	-
ESPS	-	ESPS	ESPS	ESPSSR (ESSP)	ESPS	ESPSUL1	1	ESPG	ESPG
ESPSSR	-	(return)	-	-	-	-	-	-	-
ESPSUL1	-	ESPSUL1	-	ESPSSR (ESPS)	-	-	ESPSUL2	-	-
ESPSUL2	-	ESPSUL2	-	ESPSSR (ESPS)	-	-	-	ESPG	ESPG

^{1.} Also known as Erase Suspend/Program Suspend Legacy Method.

^{1.} State will automatically move to ESPS state by t_{PSL} .

^{2.} Also known as Erase Resume/Program Resume Legacy Method.



Table 5.14 Program State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Program Buffer to flash (confirm)	Erase Suspend Enhanced Method (2)	Program Suspend Enhanced Method	Write Data
	Address	RA	xh	x555h	x555h	x555h	(SA)xh	xh	xh	xh
	Data	RD	xF0h	x70h	x71h	xAAh	x29h	xB0h	x51h	xh
WB	WC > 256 or SA ≠ SA	WB	_	_	_	_	_	_	_	PG
WB	WC ≤ 256 and SA = SA	WB	-	-	-	_	_	_	_	WB_D
	Write Buffer ≠ Write Buffer									PG
WB_D	WC = 0	WB_D	_	_	_	_	_	_	_	PBF
	WC > 0 and Write Buffer = Write Buffer									WB_D
PBF	-	-	-	-	-	-	PG	-	-	PG
PG1	-	PG1	=	-	=	-	-	-	-	PG
	SR(7) = 0		=		=	-		PSR (PG)	PSR (PG)	
	SR(7) = 1									
PG (1)	SR(7) = 1 and SR(1) = 0	PG	READ	PGSR (PG)	READ	WBUL1	-	-	-	PG

Table 5.15 Program Unlock State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Unlock 2	NOT a valid	"Write-to-Buff	er-Abort Rese	t" Command
	Address	RA	xh	x555h	x2AAh	NOT x555h	xh	NOT x2AAh	xh
	Data	RD	xF0h	x70h	x55h	xh	NOT xF0h	xh	NOT x55h
	-							-	-
WBUL1	SR(3) = 1	WBUL1	-	-	WBUL2	-	-	PG	PG
	DQ(1) = 1							FG	FG
	-					-	-		
WBUL2	SR(3) = 1	WBUL2	READ	-	-	PG	PG	-	=
	DQ(1) = 1					FG	FG		
PGSR	-	(return)	-	=	=	-	-	-	=

^{1.} State will automatically move to READ state at the completion of the operation.

^{2.} Also known as Erase Suspend/Program Suspend Legacy Method.



Table 5.16 Program Suspend State Command Transition

Current State	Command and Condition	Read	Status Register Read Enter	Status Register Clear	Erase Resume Enhanced Method (2)	Program Resume Enhanced Method
	Address	RA	x555h	x555h	xh	xh
	Data	RD	x70h	x71h	x30h	x50h
PSR (1)	-	PSR	PGSR (PSR)	-	-	-
PS	-	PS	PSSR (PS)	PS	PG	PG
PSSR	-	(return)	-	-	-	-

Notes:

- 1. State will automatically move to PS state by $t_{\rm PSL}$.
- 2. Also known as Erase Resume/Program Resume Legacy Method.

Table 5.17 Lock Register State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Command Set Exit Entry	Command Set Exit	PPB Lock Bit Set Entry	Password Word Count
	Address	RA	xh	x555h	x555h	xh	xh	xh	Xh
	Data	RD	xF0h	x70h	x71h	x90h	x00h	xA0h	x03h
LR	=	LR	READ	LRSR (LR)	LR	LREXT	=	LRPG1	=
LRPG1	=	LRPG1	-	-	=	-	=	=	=
LRPG	-	LRPG	-	LRSR (LRPG)	-	-	-	-	-
LRSR	-	(return)	-	-	-	-	-	-	-
LREXT	-	LREXT	-	-	-	-	READ	=	READ

Table 5.18 CFI State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear
	Address	RA	xh	x555h	x555h
	Data	RD	xF0h	x70h	x71h
CFI	-	CFI	READ	CFISR (CFI)	CFI
CFISR	-	(return)	-	-	-

Table 5.19 Secure Silicon Sector State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1
	Address	RA	xh	x555h	x555h	x555h
	Data	RD	xF0h	x70h	x71h	xAAh
SSR	-	SSR	READ	SSRSR (SSR)	SSR	SSRUL1

Document Number: 001-98285 Rev. *J Page 46 of 102



Table 5.20 Secure Silicon Sector Unlock State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Unlock 2	Word Program Entry	Write to Buffer Enter	Comma nd Set Exit Entry	NOT a valid "Write-to-Buffer-Abort Reset" Command		-Abort	
	Address	RA	xh	x555h	x2AAh	x555h	(SA)xh	x555h	NOT x555h	xh	NOT x2AAh	xh
	Data	RD	xF0h	x70h	x55h	xA0h	x25h	x90h	xh	NOT xF0h	xh	NOT x55h
	-			00000							-	-
SSRUL1	DQ(1) = 1	SSRUL1	READ	SSRSR (SSR)	SSRUL2	-	-	-	-	-	SSRPG	SSRPG
	SR(3) = 1			(00.1)							SSKFG	SSKEG
	-						000		-	i		
SSRUL2	DQ(1) = 1	SSRUL2	SSR	-	-	SSRPG1	SSR_W B	SSREXT	SSRPG	SSRPG	-	-
	SR(3) = 1								001(10	55111 6		



 Table 5.21
 Secure Silicon Sector Program State Command Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Unlock 1	Command Set Exit
	Address	RA	xh	x555h	x555h	x555h	xh
	Data	RD	xF0h	x70h	x71h	xAAh	x00h
SSRPG1	-	SSRPG1	-	-	SSRPG1	-	-
CCD WD	WC > 256 or SA ≠ SA	CCD WD					
SSR_WB	WC ≤ 256 and SA = SA	SSR_WB	-	-	-	-	-
SSR_WB_D	WC < 0 or Write Buffer ≠ Write Buffer	SSR_WB_D					
33K_WB_D	WC > 0 and Write Buffer = Write Buffer	33K_WB_D	-	-	-	-	-
	SR(7) = 0				-		
	SR(7) = 1		-			_	
SSRPG	SR(7) = 1 and $DQ(1) = 0$	SSRPG	READ	SSRSR (SSRPG)	SSR		-
	DQ(1) = 1					0001114	
	SR(3) = 1		-		-	SSRUL1	
SSRSR	-	(return)	-	-	-	-	-
SSREXT	-	SSREXT	-	SSRSR (SSR)	-	-	READ

 Table 5.22 Password Protection Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Password ASO Unlock Enter	Password ASO Unlock Start	Command Set Exit Entry	Comman d Set Exit	Program Entry	Password Word Count
	Address	RA	xh	x555h	x555h	0h	0h	xh	xh	xh	Xh
	Data	RD	xF0h	x70h	x71h	x25h	x29h	x90h	x00h	xA0h	x03h
PP	-	PP	READ	PPSR (PP)	PP	PPWB25	-	PPEXT	-	PPPG1	-
PPWB25	-	PPWB25	-	=	=	-	=	-	-	-	PPD
PPD	WC > 0	PPD				_	-				
PPD	WC ≤ 0	=] -	-	-	-	PPPG	-	-	-	-
PPPG1	-	PPPG1	-	=	=	-	=	-	=	-	-
PPPG	-	PPPG	-	PPSR (PPPG)	-	-	-	-	-	-	-
PPSR	-	(return)	-	-	-	-	-	-	-	-	-
PPEXT	-	PPEXT	-	-	-	-	-	-	READ	-	-



Table 5.23 Non-Volatile Protection Command State Transition

Current State	Comman d and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Comman d Set Exit Entry	Comman d Set Exit	Program Entry	DYB Set Start	All PPB Erase Enter	All PPB Erase Start
	Address	RA	xh	x555h	x555h	xh	xh	xh	(SA)xh	Xh	0h
	Data	RD	xF0h	x70h	x71h	x90h	x00h	xA0h	x00h	x80h	x30h
PPB	-	PPB	READ	PPBSR (PPB)	PPB	PPBEXT	-	PPBPG1	-	PPBPG1	-
PPBPG1	-	PPBPG1	READ	=	-	-	PPBPG	=	PPB	=	PPBER
PPBPG	SR(7) = 0	PPBPG	-	PPBSR	-		_				
FFBFG	SR(7) = 1	FFBFG	READ	(PPBPG)	READ	_	-	-	-	-	-
PPBER	SR(7) = 0	PPBER	-	PPBSR	-				_		
FFBER	SR(7) = 1	FFBER	READ	(PPBER)	READ	_	-	-	-	-	-
PPBSR	-	(return)	-	-	-	-	-	-	-	-	-
PPBEXT	-	PPBEXT	-	-	-	-	READ	-	-	-	-

Table 5.24 PPB Lock Bit Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Command Set Exit Entry	Command Set Exit	Program Entry
	Address	RA	xh	x555h	x555h	xh	xh	xh
	Data	RD	xF0h	x70h	x71h	x90h	x00h	xA0h
PPBLB	-	PPBLB	READ	PPBLBSR (PPBLB)	PPBLB	PPBLBEXT	-	PPBLBSET
PPBLBSR	-	(return)	-	-	-	-	-	-
PPBLBSET	- LR(2) = 0 and LR(5) = 0	PPBLBSET	-	-	-	-	PPBLB	-
PPBLBEXT	-	PPBLBEXT	=	=	=	-	READ	-

 Table 5.25
 Volatile Sector Protection Command State Transition

Current State	Command and Condition	Read	Software Reset / ASO Exit	Status Register Read Enter	Status Register Clear	Command Set Exit Entry	Command Set Exit	Program Entry	DYB Set Start	DYB Clear Start
	Address	RA	xh	x555h	x555h	xh	xh	xh	(SA)xh	(SA)xh
	Data	RD	xF0h	x70h	x71h	x90h	x00h	xA0h	x00h	x01h
DYB	-	DYB	READ	DYBSR (DYB)	DYB	DTBEXT	-	DYBSET	-	-
DYBSR	-	(return)	-	-	-	-	-	-	-	-
DYBSET	-	DYBSET	-	-	-	-	-	-	DYB	DYB
DYBEXT	-	DYBEXT	-	-	-	-	READ	-	-	-

Document Number: 001-98285 Rev. *J Page 49 of 102



Table 5.26 State Transition Definitions

Current State	Command Transition	Definition
BLCK	Table 5.8	Blank Check
CER	Table 5.8	Chip Erase Start
CFI	Table 5.18	ID (Autoselect)
CFISR	Table 5.18	ID (Autoselect) - Status Register Read
DYB	Table 5.25	DYB ASO
DYBEXT	Table 5.25	DYB ASO - Command Exit
DYBSET	Table 5.25	DYB ASO - Set
DYBSR	Table 5.25	DYB ASO - Status Register Read
ER	Table 5.8	Erase Enter
ERSR	Table 5.8	Erase - Status Register Read
ERUL1	Table 5.8	Erase - Unlock Cycle 1
ERUL2	Table 5.8	Erase - Unlock Cycle 2
ES	Table 5.9	Erase Suspended
ESDYB	Table 5.11	Erase Suspended - DYB ASO
ESDYBEXT	Table 5.11	Erase Suspended - DYB Command Exit
ESDYBSET	Table 5.11	Erase Suspended - DYB Set/Clear
ESPG	Table 5.12	Erase Suspended - Program
		Erase Suspended - Program - Status Register
ESPGSR	Table 5.12	Read
ESPG1	Table 5.12	Erase Suspended - Word Program
ESPS	Table 5.13	Erase Suspended - Program Suspended
ESPSR	Table 5.13	Erase Suspended - Program Suspend
		Erase Suspended - Program Suspend - Status
ESPSSR	Table 5.13	Register Read
		Erase Suspended - Program Suspend - Unlock
ESPSUL1	Table 5.13	1
		Erase Suspended - Program Suspend - Unlock
ESPSUL2	Table 5.13	2
ESR	Table 5.9	Erase Suspend Request
ESSR	Table 5.9	Erase Suspended - Status Register Read
ESUL1	Table 5.10	Erase Suspended - Unlock Cycle 1
ESUL2	Table 5.10	Erase Suspended - Unlock Cycle 2
ES_WB	Table 5.12	Erase Suspended - Write to Buffer
ES_WB_D	Table 5.12	Erase Suspended - Write to Buffer Data
LR	Table 5.17	Lock Register
LREXT	Table 5.17	Lock Register - Command Exit
LRPG	Table 5.17	Lock Register - Program
LRPG1	Table 5.17	Lock Register - Program Start
LRSR	Table 5.17	Lock Register - Status Register Read
PBF	Table 5.14	Page Buffer Full
PG	Table 5.14	Program
PGSR	Table 5.15	Program - Status Register Read
	10010 0.10	1 Togram Status Register Redu



 Table 5.26
 State Transition Definitions (Continued)

PPP Table 5.22 Password ASO PPB Table 5.23 PPB PPBER Table 5.23 PPB PPBER Table 5.23 PPB PPBER Table 5.23 PPB PPBER Table 5.23 PPB PPB Command Exit PPBLB Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit PPBLBSR Table 5.24 PPB Lock Bit PPBLBSR Table 5.23 PPB PPBPG Table 5.23 PPB PPBPG Table 5.23 PPB PPBPG Program PPBPG Table 5.23 PPB PPBPG Program PPBPG PPB P	Current State	Command Transition	Definition
PPB Table 5.23 PPB - Erase PPBERT Table 5.23 PPB - Erase PPBEXT Table 5.23 PPB - Command Exit PPBLB Table 5.24 PPB Lock Bit - Command Exit PPBLBEXT Table 5.24 PPB Lock Bit - Set PPBLBSET Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.23 PPB - Program PPBPG Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Program Request PPB - PPD Table 5.22 Password ASO - Data PPD Table 5.22 Password ASO - Command Exit PPPCT Table 5.22 Password ASO - Command Exit PPPCG Table 5.22 Password ASO - Program Request PPPCG Table 5.22 Password ASO - Status Register Read PPSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Progr	PG1	Table 5.14	Word Program
PPBER Table 5.23 PPB - Erase PPBESTT Table 5.23 PPB - Command Exit PPBLBB Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit - Command Exit PPBLBEST Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.23 PPB - Program PPBPGG Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Program Request PPBSR Table 5.22 Password ASO - Data PPEXT Table 5.22 Password ASO - Data PPEXT Table 5.22 Password ASO - Oata PPEXT Table 5.22 Password ASO - Program PPPG Table 5.22 Password ASO - Program Request PPPG Table 5.22 Password ASO - Status Register Read PPSR Table 5.22 Password ASO - Status Register Read PPSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended PSR Table 5.16 Program Su	PP	Table 5.22	Password ASO
PPBEXT Table 5.23 PPB - Command Exit PPBLB Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit - Command Exit PPBLBEST Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Status Register Read PPBPG Table 5.23 PPB - Program PPBPG Table 5.23 PPB - Program PPBPG1 Table 5.23 PPB - Status Register Read PPBSR Table 5.23 PPB - Status Register Read PPDD Table 5.22 Password ASO - Dottal PPEXT Table 5.22 Password ASO - Command Exit PPEXT Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program PPPG3 Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PPSR Table 5.22 Password ASO - Status Register Read PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read </td <td>PPB</td> <td>Table 5.23</td> <td>PPB</td>	PPB	Table 5.23	PPB
PPBLB Table 5.24 PPB Lock Bit PPBLBEXT Table 5.24 PPB Lock Bit - Command Exit PPBLBSET Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Status Register Read PPBPG Table 5.23 PPB - Program PPBPG Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Program Request PPD Table 5.22 Password ASO - Data PPD Table 5.22 Password ASO - Command Exit PPD Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.6 Read Array READ Table 5.6 Read Fabrus Register Read PPWB25 Table 5	PPBER	Table 5.23	PPB - Erase
PPBLBEXT Table 5.24 PPB Lock Bit - Command Exit PPBLBSET Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Set PPBPG Table 5.23 PPB - Program PPBPG Table 5.23 PPB - Program PPBSR Table 5.23 PPB - Status Register Read PPD Table 5.22 Password ASO - Data PPPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG Table 5.22 Password ASO - Program Request PPPG Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PPSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READDL Table 5.6 Read Status Register READUL1 Table 5.7	PPBEXT	Table 5.23	PPB - Command Exit
PPBLBSET Table 5.24 PPB Lock Bit - Set PPBLBSR Table 5.24 PPB Lock Bit - Status Register Read PPBPG Table 5.23 PPB - Program PPBPG1 Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Program Request PPDD Table 5.22 Password ASO - Data PPEXT Table 5.22 Password ASO - Data PPPG1 Table 5.22 Password ASO - Program PPPG6 Table 5.22 Password ASO - Program Request PPPG1 Table 5.22 Password ASO - Status Register Read PPSR Table 5.16 Program Suspended PPSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READUL1 Table 5.6 Read Array READUL2 Table 5.7 Read - Unlock Cycle 1 READUL2 Ta	PPBLB	Table 5.24	PPB Lock Bit
PPBLBSR Table 5.24 PPB Lock Bit - Status Register Read PPBPG Table 5.23 PPB - Program PPBPG1 Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Status Register Read PPD Table 5.22 Password ASO - Data PPD Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program Request PPPSR Table 5.22 Password ASO - Status Register Read PSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read READ Table 5.6 Read Afray READ Table 5.6 Read Stat	PPBLBEXT	Table 5.24	PPB Lock Bit - Command Exit
PPBPG Table 5.23 PPB - Program PPBPG1 Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Status Register Read PPD Table 5.22 Password ASO - Data PPPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG Table 5.22 Password ASO - Program Request PPPG1 Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspended Status Register Read PPSR Table 5.16 Program Suspended Status Register Read PPSR Table 5.16 Program Suspended Status Register Read PPWB25 Table 5.16 Program Suspended Status Register Read READ Table 5.6 Read Array READUL1 Table 5.6 Read Status Register READUL2 Table 5.7 Read - Unlock Cycle 1 SER Table 5.7 Read - Unlock Cycle 2	PPBLBSET	Table 5.24	PPB Lock Bit - Set
PPBPG1 Table 5.23 PPB - Program Request PPBSR Table 5.23 PPB - Status Register Read PPD Table 5.22 Password ASO - Data PPPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG Table 5.22 Password ASO - Program Request PPPG1 Table 5.22 Password ASO - Status Register Read PPSR Table 5.22 Password ASO - Status Register Read PSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.16 Program Suspended - Status Register Read PPSR Table 5.21 Read Atray READUL Table 5.21 Read Status Register Read READUL Table 5.	PPBLBSR	Table 5.24	PPB Lock Bit - Status Register Read
PPBSR Table 5.23 PPB - Status Register Read PPD Table 5.22 Password ASO - Data PPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program Request PPPG1 Table 5.22 Password ASO - Status Register Read PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.16 Program Suspended - Status Register Read READ Table 5.6 Read Array READD Table 5.6 Read Status Register READUL1 Table 5.6 Read Status Register READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.7 Read - Unlock Cycle 2 SER Table 5.19 Secure Silicon - Command Exit SSR Y Table 5.21 Secure Silicon - Program	PPBPG	Table 5.23	PPB - Program
PPD Table 5.22 Password ASO - Data PPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program Request PPPR Table 5.22 Password ASO - Status Register Read PSR Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSR Table 5.16 Program Suspended - Status Register Read PSR Table 5.16 Program Suspended - Status Register Read PSR Table 5.16 Program Suspended - Status Register Read PSR Table 5.16 Program Suspended - Status Register Read PSR Table 5.21 Read Array READD Read Status Register Read Pullock READD Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 2 SER Table 5.7 Read - Unlock Cycle 2 SER Table 5.1 Secure Silicon - Command Exit SSR Table 5.21 Secure Silicon - Program	PPBPG1	Table 5.23	PPB - Program Request
PPEXT Table 5.22 Password ASO - Command Exit PPPG Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READUL1 Table 5.6 Read Status Register READUL2 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sectore Silicon SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR	PPBSR	Table 5.23	PPB - Status Register Read
PPPG Table 5.22 Password ASO - Program PPPG1 Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.16 Program Suspended - Status Register Read READ Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READDR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Write Table Satus Register Read SSRSR Table 5.21 Secure Silicon - Unlock Cycle 2	PPD	Table 5.22	Password ASO - Data
PPPG1 Table 5.22 Password ASO - Program Request PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspended - Status Register Read PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.9 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer <	PPEXT	Table 5.22	Password ASO - Command Exit
PPSR Table 5.22 Password ASO - Status Register Read PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspend Request PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSRRXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer S	PPPG	Table 5.22	Password ASO - Program
PS Table 5.16 Program Suspended PSR Table 5.16 Program Suspend Request PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Vortaus Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer	PPPG1	Table 5.22	Password ASO - Program Request
PSR Table 5.16 Program Suspend Request PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Unlock Cycle 1 SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.15 Write Buffer - Unlock Cycle 1 <td>PPSR</td> <td>Table 5.22</td> <td>Password ASO - Status Register Read</td>	PPSR	Table 5.22	Password ASO - Status Register Read
PSSR Table 5.16 Program Suspended - Status Register Read PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.15 Write Buffer - Unlock Cycle 1 WBUL1 Table 5.15 Write Buffer - Unlock Cy	PS	Table 5.16	Program Suspended
PPWB25 Table 5.22 Password ASO - Unlock READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.15 Write Buffer - Unlock Cycle 1 WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2	PSR	Table 5.16	Program Suspend Request
READ Table 5.6 Read Array READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Word Program SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer - Unlock Cycle 1 WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2	PSSR	Table 5.16	Program Suspended - Status Register Read
READSR Table 5.6 Read Status Register READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Word Program SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer - Unlock Cycle 1 WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2	PPWB25	Table 5.22	Password ASO - Unlock
READUL1 Table 5.7 Read - Unlock Cycle 1 READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	READ	Table 5.6	Read Array
READUL2 Table 5.7 Read - Unlock Cycle 2 SER Table 5.8 Sector Erase Start SSR Table 5.19 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer - Unlock Cycle 1 WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2	READSR	Table 5.6	Read Status Register
SER Table 5.8 Secure Silicon SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	READUL1	Table 5.7	Read - Unlock Cycle 1
SSR Table 5.19 Secure Silicon SSRPG Table 5.21 Secure Silicon - Command Exit SSRPG1 Table 5.21 Secure Silicon - Program SSRSR Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	READUL2	Table 5.7	Read - Unlock Cycle 2
SSREXT Table 5.21 Secure Silicon - Command Exit SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer WBUL1 Table 5.14 Write to Buffer Write to Buffer Write buffer - Unlock Cycle 1 Write Buffer - Unlock Cycle 2 Write Buffer - Unlock Cycle 2 Write Buffer - Unlock Cycle 1	SER	Table 5.8	Sector Erase Start
SSRPG Table 5.21 Secure Silicon - Program SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2 Write Buffer - Unlock Cycle 1	SSR	Table 5.19	Secure Silicon
SSRPG1 Table 5.21 Secure Silicon - Word Program SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 2 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSREXT	Table 5.21	Secure Silicon - Command Exit
SSRSR Table 5.21 Secure Silicon - Status Register Read SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Write to Buffer - Write Data WB Table 5.14 Write to Buffer Write to Buffer Write to Buffer Write to Buffer Write Data Write Buffer - Unlock Cycle 1 Write Buffer - Unlock Cycle 2	SSRPG	Table 5.21	Secure Silicon - Program
SSRUL1 Table 5.20 Secure Silicon - Unlock Cycle 1 SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSRPG1	Table 5.21	Secure Silicon - Word Program
SSRUL2 Table 5.20 Secure Silicon - Unlock Cycle 2 SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSRSR	Table 5.21	Secure Silicon - Status Register Read
SSR_WB Table 5.21 Secure Silicon - Write to Buffer SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSRUL1	Table 5.20	Secure Silicon - Unlock Cycle 1
SSR_WB_D Table 5.21 Secure Silicon - Write to Buffer - Write Data WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSRUL2	Table 5.20	Secure Silicon - Unlock Cycle 2
WB Table 5.14 Write to Buffer WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSR_WB	Table 5.21	Secure Silicon - Write to Buffer
WBUL1 Table 5.15 Write Buffer - Unlock Cycle 1 WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	SSR_WB_D	Table 5.21	Secure Silicon - Write to Buffer - Write Data
WBUL2 Table 5.15 Write Buffer - Unlock Cycle 2	WB	Table 5.14	Write to Buffer
·	WBUL1	Table 5.15	Write Buffer - Unlock Cycle 1
	WBUL2	Table 5.15	Write Buffer - Unlock Cycle 2
WB_D Write to Buffer Write Data	WB_D	Table 5.14	Write to Buffer Write Data



6. Software Interface Reference

6.1 Command Summary

Table 6.1 Command Definitions

		s						Bu	s Cycles	(Notes 2	2-5)					
	Command Sequence (Note 1)	Cycles	Fi	rst	Sec	ond	Th	ird	Fou	ırth	Fi	fth	Six	ĸth	Sev	enth
	(Note 1)	5	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data
Rea	ad (Note 6)	1	RA	RD												
Res	set/ASO Exit (Notes 7, 16)	1	XXX	F0												
Sta	tus Register Read	2	555	70	XXX	RD										
Sta	tus Register Clear	1	555	71												
Wo	rd Program	4	555	AA	2AA	55	555	A0	PA	PD						
Wri	te to Buffer	6	555	AA	2AA	55	SA	25	SA	WC	WBL	PD	WBL	PD		
	gram Buffer to Flash nfirm)	1	SA	29												
	te-to-Buffer-Abort Reset ote 11)	3	555	AA	2AA	55	555	F0								
Chi	p Erase	6	555	AA	2AA	55	555	80	555	AA	2AA	55	555	10		
Sec	ctor Erase	6	555	AA	2AA	55	555	80	555	AA	2AA	55	SA	30		
Sus	se Suspend/Program spend gacy Method (Note 9)	1	XXX	В0												
	se Suspend Enhanced thod															
Res	se Resume/Program sume gacy Method (Note 10)	1	XXX	30												
	se Resume Enhanced thod															
	gram Suspend Enhanced thod	1	XXX	51												
	gram Resume Enhanced thod	1	XXX	50												
Bla	nk Check	1	(SA) 555	33												
ASO	ID (Autoselect) Entry	3	555	AA	2AA	55	(SA) 555	90								
select)	CFI Enter (Note 8)	1	(SA) 55	98												
Auto	ID-CFI Read	1	RA	RD												
ID-CFI (Autoselect)	Reset/ASO Exit (Notes 7, 16)	1	xxx	F0												
	I				Secur	e Silicon	Region	Comman	d Definit	ions	I		I	I	I	1



Table 6.1 Command Definitions (Continued)

		s						Bu	s Cycles	(Notes 2	?-5)					
	Command Sequence (Note 1)		Fi	First		ond	Th	ird	For	ırth	Fit	fth	Six	cth	Sev	enth
	()	Cycles	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data
0	SSR Entry	3	555	AA	2AA	55	(SA) 555	88								
ASO	Read (Note 6)	1	RA	RD												
SSR)	Word Program	4	555	AA	2AA	55	555	A0	PA	PD						
S) uc	Write to Buffer	6	555	AA	2AA	55	SA	25	SA	WC	WBL	PD	WBL	PD		
n Region	Program Buffer to Flash (confirm)	1	SA	29												
Silicon	Write-to-Buffer-Abort Reset (Note 11)	3	555	AA	2AA	55	555	F0								
Secure	SSR Exit (Note 11)	4	555	AA	2AA	55	555	90	XX	0						
Se	Reset/ASO Exit (Notes 7, 16)	1	XXX	F0												



Table 6.1 Command Definitions (Continued)

		"						Bu	s Cycles	(Notes 2	2-5)					
	Command Sequence (Note 1)	Cycles	Fi	rst	Sec	ond	Th	ird	Fo	urth	Fi	fth	Six	ĸth	Sev	enth
	(Note 1)	હ	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data
					Loc	k Regist	er Comm	and Set	Definitio	ns						
	Lock Register Entry	3	555	AA	2AA	55	555	40								
ASO	Program (Note 15)	2	XXX	A0	XXX	PD										
ster,	Read (Note 15)	1	0	RD												
Lock Register ASO	Command Set Exit (Notes 12, 16)	2	XXX	90	XXX	0										
Loc	Reset/ASO Exit (Notes 7, 16)	1	XXX	F0												
					Passw	ord Prote	ection Co	mmand \$	Set Defin	itions						
	Password ASO Entry	3	555	AA	2AA	55	555	60								
	Program (Note 14)	2	XXX	A0	PWA x	PWDx										
AASO	Read (Note 13)	4	0	PWD0	1	PWD1	2	PWD2	3	PWD 3						
Password ASO	Unlock	7	0	25	0	3	0	PWD0	1	PWD 1	2	PWD2	3	PWD 3	0	29
Pe	Command Set Exit (Notes 12, 16)	2	XXX	90	XXX	0										
	Reset/ASO Exit (Notes 7, 16)	1	XXX	F0												
				No	n-Volatile	e Sector I	Protectio	n Comm	and Set	Definition	ıs					
(uo	PPB Entry	3	555	AA	2AA	55	555	C0								
tecti	PPB Program (Note 17)	2	XXX	A0	SA	0										
Pro	All PPB Erase (Note 17)	2	XXX	80	0	30										
ctor	PPB Read (Note 17)	1	SA	RD (0)												
latile Se	Command Set Exit (Notes 12, 16)	2	XXX	90	XXX	0										
PPB (Non-Volatile Sector Protection)	Reset/ASO Exit (Notes 7, 16)	1	xxx	F0												
			G	lobal No	n-Volatile	Sector I	Protectio	n Freeze	Comma	nd Set De	efinitions	3				
	PPB Lock Entry	3	555	AA	2AA	55	555	50								
Bit	PPB Lock Bit Cleared	2	XXX	A0	XXX	0										
PPB Lock E	PPB Lock Status Read (Note 17)	1	XXX	RD (0)												
PPB	Command Set Exit (Notes 12, 16)	2	XXX	90	XXX	0										
	Reset/ASO Exit (Note 16)	1	XXX	F0												



Table 6.1 Command Definitions (Continued)

		s						Bu	s Cycles	(Notes 2	?- 5)					
	Command Sequence (Note 1)	Cycles	Fi	rst	Sec	ond	Th	ird	Fourth		Fifth		Sixth		Seventh	
	()	ပ	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data	Addr	Data
	Volatile Sector Protection Command Set Definitions															
SO	DYB ASO Entry	3	555	AA	2AA	55	555	E0								
⋖	DYB Set (Note 17)	2	XXX	A0	SA	0										
ctio	DYB Clear (Note 17)	2	XXX	A0	SA	1										
Protection)	DYB Status Read (Note 17)	1	SA	RD (0)												
Sector F	Command Set Exit (Notes 12, 16)	2	XXX	90	XXX	0										
DYB (Volatile	Reset/ASO Exit (Note 16)	1	xxx	F0												

Legend:

X = Don't care.

RA = Address of the memory to be read.

RD = Data read from location RA during read operation.

PA = Address of the memory location to be programmed.

PD = Data to be programmed at location PA.

SA = Address of the sector selected. Address bits A_{MAX} -A16 uniquely select any sector.

WBL = Write Buffer Location. The address must be within the same Line.

WC = Word Count is the number of write buffer locations to load minus 1.

PWAx = Password address for word0 = 00h, word1 = 01h, word2 = 02h, and word3 = 03h.

PWDx = Password data word0, word1, word2, and word3.

- 1. See Table 8.1, Interface States on page 63 for description of bus operations.
- 2. All values are in hexadecimal.
- 3. Except for the following, all bus cycles are write cycle: read cycle during Read, ID/CFI Read (Manufacturing ID / Device ID), Indicator Bits, Secure Silicon Region Read, SSR Lock Read, and 2nd cycle of Status Register Read.
- 4. Data bits DQ15-DQ8 are don't care in command sequences, except for RD, PD, WC and PWD.
- 5. Address bits A_{MAX}-A11 are don't cares for unlock and command cycles, unless SA or PA required. (A_{MAX} is the Highest Address pin.).
- 6. No unlock or command cycles required when reading array data.
- 7. The Reset command is required to return to reading array data when device is in the ID-CFI (autoselect) mode, or if DQ5 goes High (while the device is providing status data).
- 8. Command is valid when device is ready to read array data or when device is in ID-CFI (autoselect) mode.
- 9. The system can read and program/program suspend in non-erasing sectors, or enter the ID-CFI ASO, when in the Erase Suspend mode. The Erase Suspend command is valid only during a sector erase operation.
- 10. The Erase Resume/Program Resume command is valid only during the Erase Suspend/Program Suspend modes.
- 11. Issue this command sequence to return to READ mode after detecting device is in a Write-to-Buffer-Abort state. IMPORTANT: the full command sequence is required if resetting out of ABORT.
- 12. The Exit command returns the device to reading the array.
- 13. The password portion can be entered or read in any order as long as the entire 64-bit password is entered or read.
- 14. For PWDx, only one portion of the password can be programmed per each A0 command. Portions of the password must be programmed in sequential order (PWD0 PWD3).
- 15. All Lock Register bits are one-time programmable. The program state = 0 and the erase state = 1. Also, both the Persistent Protection Mode Lock Bit and the Password Protection Mode Lock Bit cannot be programmed at the same time or the Lock Register Bits Program operation aborts and returns the device to read mode. Lock Register bits that are reserved for future use are undefined and may be 0's or 1's.
- 16. If any of the Entry commands was issued, an Exit command must be issued to reset the device into read mode.
- 17. Protected State = 00h, Unprotected State = 01h. The sector address for DYB set, DYB clear, or PPB Program command may be any location within the sector the lower order bits of the sector address are don't care.



6.2 Device ID and Common Flash Interface (ID-CFI) ASO Map

The Device ID portion of the ASO (word locations 0h to 0Fh) provides manufacturer ID, device ID, Sector Protection State, and basic feature set information for the device.

ID-CFI Location 02h displays sector protection status for the sector selected by the sector address (SA) used in the ID-CFI enter command. To read the protection status of more than one sector it is necessary to exit the ID ASO and enter the ID ASO using the new SA. The access time to read location 02h is always t_{ACC} and a read of this location requires CE# to go High before the read and return Low to initiate the read (asynchronous read access). Page mode read between location 02h and other ID locations is not supported. Page mode read between ID locations other than 02h is supported.

For additional information see ID-CFI ASO on page 29.

Table 6.2 ID (Autoselect) Address Map

Description	Address	Read Data
Manufacture ID	(SA) + 0000h	0001h
Device ID	(SA) + 0001h	227Eh
Protection Verification	(SA) + 0002h	Sector Protection State (1= Sector protected, 0= Sector unprotected). This protection state is shown only for the SA selected when entering ID-CFI ASO. Reading other SA provides undefined data. To read a different SA protection state ASO exit command must be used and then enter ID-CFI ASO again with the new SA.
Indicator Bits	(SA) + 0003h	DQ15-DQ08 = 1 (Reserved) DQ7 - Factory Locked Secure Silicon Region 1 = Locked, 0 = Not Locked DQ6 - Customer Locked Secure Silicon Region 1 = Locked 0 = Not Locked DQ5 = 1 (Reserved) DQ4 - WP# Protects 0 = lowest address Sector 1 = highest address Sector DQ3 - DQ0 = 1 (Reserved)
	(SA) + 0004h	Reserved
	(SA) + 0005h	Reserved
	(SA) + 0006h	Reserved
RFU	(SA) + 0007h	Reserved
KFU	(SA) + 0008h	Reserved
	(SA) + 0009h	Reserved
	(SA) + 000Ah	Reserved
	(SA) + 000Bh	Reserved
Lower Software Bits	(SA) + 000Ch	Bit 0 - Status Register Support 1 = Status Register Supported 0 = Status Register not supported Bit 1 - DQ polling Support 1 = DQ bits polling supported 0 = DQ bits polling not supported Bit 3-2 - Command Set Support 11 = reserved 10 = reserved 01 = Reduced Command Set 00 = Classic Command set Bits 4-15 - Reserved = 0
Upper Software Bits	(SA) + 000Dh	Reserved



Table 6.2 ID (Autoselect) Address Map (Continued)

Description	Address	Read Data
Device ID	(SA) + 000Eh	2228h = 1 Gb 2223h = 512 Mb 2222h = 256 Mb 2221h = 128 Mb
Device ID	(SA) + 000Fh	2201h

Table 6.3 CFI Query Identification String

Word Address	Data	Description
(SA) + 0010h	0051h	
(SA) + 0011h	0052h	Query Unique ASCII string "QRY"
(SA) + 0012h	0059h	
(SA) + 0013h	0002h	Primary OEM Command Set
(SA) + 0014h	0000h	Filliary OEM Command Set
(SA) + 0015h	0040h	Address for Primary Extended Table
(SA) + 0016h	0000h	Address for Filinary Extended Table
(SA) + 0017h	0000h	Alternate OEM Command Set
(SA) + 0018h	0000h	(00h = none exists)
(SA) + 0019h	0000h	Address for Alternate OEM Extended Table
(SA) + 001Ah	0000h	(00h = none exists)

Table 6.4 CFI System Interface String

Word Address	Data	Description
(SA) + 001Bh	0027h	V _{CC} Min. (erase/program) (D7-D4: volts, D3-D0: 100 mV)
(SA) + 001Ch	0036h	V _{CC} Max. (erase/program) (D7-D4: volts, D3-D0: 100 mV)
(SA) + 001Dh	0000h	V _{PP} Min. voltage (00h = no V _{PP} pin present)
(SA) + 001Eh	0000h	V _{PP} Max. voltage (00h = no V _{PP} pin present)
(SA) + 001Fh	0008h	Typical timeout per single word write 2 ^N µs
(SA) + 0020h	0009h	Typical timeout for max multi-byte program, 2 ^N µs (00h = not supported)
(SA) + 0021h	0008h	Typical timeout per individual block erase 2 ^N ms
(SA) + 0022h	0012h (1 Gb) 0011h (512 Mb) 0010h (256 Mb) 000Fh (128 Mb)	Typical timeout for full chip erase 2 ^N ms (00h = not supported)
(SA) + 0023h	0001h	Max. timeout for single word write 2 ^N times typical
(SA) + 0024h	0002h	Max. timeout for buffer write 2 ^N times typical
(SA) + 0025h	0003h	Max. timeout per individual block erase 2 ^N times typical
(SA) + 0026h	0003h	Max. timeout for full chip erase 2 ^N times typical (00h = not supported)

Document Number: 001-98285 Rev. *J



Table 6.5 CFI Device Geometry Definition

Word Address	Data	Description
(SA) + 0027h	001Bh (1 Gb) 001Ah (512 Mb) 0019h (256 Mb) 0018h (128 Mb)	Device Size = 2 ^N byte;
(SA) + 0028h	0001h	Floor Device Interface Description 0 , v9 only 1 , v46 only 2 , v9/v46 canable
(SA) + 0029h	0000h	Flash Device Interface Description 0 = x8-only, 1 = x16-only, 2 = x8/x16 capable
(SA) + 002Ah	0009h	Max. number of byte in multi-byte write = 2 ^N
(SA) + 002Bh	0000h	(00 = not supported)
(SA) + 002Ch	0001h	Number of Erase Block Regions within device 1 = Uniform Device, 2 = Boot Device
(SA) + 002Dh	00XXh	Erase Block Region 1 Information (refer to JEDEC JESD68-01 or JEP137
(SA) + 002Eh	000Xh	specifications) 00FFh, 0003h, 0000h, 0002h =1 Gb
(SA) + 002Fh	0000h	00FFh, 0001h, 0000h, 0002h = 512 Mb
(SA) + 0030h	000Xh	00FFh, 0000h, 0000h, 0002h = 256 Mb 007Fh, 0000h, 0000h, 0002h = 128 Mb
(SA) + 0031h	0000h	
(SA) + 0032h	0000h	France Blook Bossian 2 Information (refer to OFI mublication 400)
(SA) + 0033h	0000h	Erase Block Region 2 Information (refer to CFI publication 100)
(SA) + 0034h	0000h	
(SA) + 0035h	0000h	
(SA) + 0036h	0000h	France Black Bassian O Information (refer to OFI multipation 400)
(SA) + 0037h	0000h	Erase Block Region 3 Information (refer to CFI publication 100)
(SA) + 0038h	0000h	
(SA) + 0039h	0000h	
(SA) + 003Ah	0000h	
(SA) + 003Bh	0000h	Erase Block Region 4 Information (refer to CFI publication 100)
(SA) + 003Ch	0000h	1
(SA) + 003Dh	FFFFh	Reserved
(SA) + 003Eh	FFFFh	Reserved
(SA) + 003Fh	FFFFh	Reserved



Table 6.6 CFI Primary Vendor-Specific Extended Query

Word Address	Data	Description
(SA) + 0040h	0050h	
(SA) + 0041h	0052h	Query-unique ASCII string "PRI"
(SA) + 0042h	0049h	
(SA) + 0043h	0031h	Major version number, ASCII
(SA) + 0044h	0035h	Minor version number, ASCII
(SA) + 0045h	001Ch	Address Sensitive Unlock (Bits 1-0) 00b = Required 01b = Not Required Process Technology (Bits 5-2) 0000b = 0.23 µm Floating Gate 0001b = 0.17 µm Floating Gate 0010b = 0.23 µm MirrorBit 0011b = 0.13 µm Floating Gate 0100b = 0.11 µm MirrorBit 0101b = 0.09 µm MirrorBit 0110b = 0.09 µm Floating Gate 0111b = 0.065 µm MirrorBit Eclipse 1000b = 0.065 µm MirrorBit
(SA) + 0046h	0002h	Erase Suspend 0 = Not Supported 1 = Read Only 2 = Read and Write
(SA) + 0047h	0001h	Sector Protect 00 = Not Supported X = Number of sectors in smallest group
(SA) + 0048h	0000h	Temporary Sector Unprotect 00 = Not Supported 01 = Supported
(SA) + 0049h	0008h	Sector Protect/Unprotect Scheme 04 = High Voltage Method 05 = Software Command Locking Method 08 = Advanced Sector Protection Method
(SA) + 004Ah	0000h	Simultaneous Operation 00 = Not Supported X = Number of banks
(SA) + 004Bh	0000h	Burst Mode Type 00 = Not Supported 01 = Supported
(SA) + 004Ch	0003h	Page Mode Type 00 = Not Supported 01 = 4 Word Page 02 = 8 Word Page 03=16 Word Page



Table 6.6 CFI Primary Vendor-Specific Extended Query (Continued)

Word Address	Data	Description
(SA) + 004Dh	0000h	ACC (Acceleration) Supply Minimum 00 = Not Supported D7-D4: Volt D3-D0: 100 mV
(SA) + 004Eh	0000h	ACC (Acceleration) Supply Maximum 00 = Not Supported D7-D4: Volt D3-D0: 100 mV
(SA) + 004Fh	0004h (Bottom) 0005h (Top)	WP# Protection 00h = Flash device without WP Protect (No Boot) 01h = Eight 8 kB Sectors at TOP and Bottom with WP (Dual Boot) 02h = Bottom Boot Device with WP Protect (Bottom Boot) 03h = Top Boot Device with WP Protect (Top Boot) 04h = Uniform, Bottom WP Protect (Uniform Bottom Boot) 05h = Uniform, Top WP Protect (Uniform Top Boot) 06h = WP Protect for all sectors 07h = Uniform, Top and Bottom WP Protect
(SA) + 0050h	0001h	Program Suspend 00 = Not Supported 01 = Supported
(SA) +0051h	0000h	Unlock Bypass 00 = Not Supported 01 = Supported
(SA) + 0052h	0009h	Secured Silicon Sector (Customer OTP Area) Size 2 ^N (bytes)
(SA) + 0053h	008Fh	Software Features bit 0: status register polling (1 = supported, 0 = not supported) bit 1: DQ polling (1 = supported, 0 = not supported) bit2:newprogramsuspend/resume commands (1 = supported, 0 = not supported) bit 3: word programming (1 = supported, 0 = not supported) bit 4: bit-field programming (1 = supported, 0 = not supported) bit 5: autodetect programming (1 = supported, 0 = not supported) bit 6: RFU bit 7: multiple writes per Line (1 = supported, 0 = not supported)
(SA) + 0054h	0005h	Page Size = 2 ^N bytes
(SA) + 0055h	0006h	Erase Suspend Timeout Maximum < 2 ^N (μs)
(SA) + 0056h	0006h	Program Suspend Timeout Maximum < 2 ^N (μs)
(SA) + 0057h to (SA) + 0077h	FFFFh	Reserved
(SA) + 0078h	0006h	Embedded Hardware Reset Timeout Maximum $< 2^N (\mu s)$ Reset with Reset Pin
(SA) + 0079h	0009h	Non-Embedded Hardware Reset Timeout Maximum < 2 ^N (μs) Power on Reset



Hardware Interface

7. Signal Descriptions

7.1 Address and Data Configuration

Address and data are connected in parallel (ADP) via separate signal inputs and I/Os.

7.2 Input/Output Summary

Table 7.1 I/O Summary

Symbol	Туре	Description
RESET#	Input	Hardware Reset. At $V_{\rm IL}$, causes the device to reset control logic to its standby state, ready for reading array data.
CE#	Input	Chip Enable. At $V_{\rm IL}$, selects the device for data transfer with the host memory controller.
OE#	Input	Output Enable. At $V_{\rm IL}$, causes outputs to be actively driven. At $V_{\rm IH}$, causes outputs to be high impedance (High-Z).
WE#	Input	Write Enable. At $V_{\rm IL}$, indicates data transfer from host to device. At $V_{\rm IH}$, indicates data transfer is from device to host.
A _{MAX} -A0	Input	Address inputs. A25-A0 for S29GL01GS A24-A0 for S29GL512S A23-A0 for S29GL256S A22-A0 for S29GL128S
DQ15-DQ0	Input/Output	Data inputs and outputs
WP#	Input	Write Protect. At V_{IL} , disables program and erase functions in the lowest or highest address 64-kword (128-kB) sector of the device. At V_{IH} , the sector is not protected. WP# has an internal pull up; When unconnected WP# is at V_{IH} .
RY/BY#	Output - open drain	Ready/Busy. Indicates whether an Embedded Algorithm is in progress or complete. At V_{IL} , the device is actively engaged in an Embedded Algorithm such as erasing or programming. At High-Z, the device is ready for read or a new command write - requires external pull-up resistor to detect the High-Z state. Multiple devices may have their RY/BY# outputs tied together to detect when all devices are ready.
V _{CC}	Power Supply	Core power supply
V _{IO}	Power Supply	Versatile IO power supply.
V _{SS}	Power Supply	Power supplies ground
NC	No Connect	Not Connected internally. The pin/ball location may be used in Printed Circuit Board (PCB) as part of a routing channel.
RFU	No Connect	Reserved for Future Use. Not currently connected internally but the pin/ball location should be left unconnected and unused by PCB routing channel for future compatibility. The pin/ball may be used by a signal in the future.
DNU	Reserved	Do Not Use. Reserved for use by Cypress. The pin/ball is connected internally. The input has an internal pull down resistance to V_{SS} . The pin/ball can be left open or tied to V_{SS} on the PCB.



7.3 Versatile I/O Feature

The maximum output voltage level driven by, and input levels acceptable to, the device are determined by the V_{IO} power supply. This supply allows the device to drive and receive signals to and from other devices on the same bus having interface signal levels different from the device core voltage.

7.4 Ready/Busy# (RY/BY#)

RY/BY# is a dedicated, open drain output pin that indicates whether an Embedded Algorithm, Power-On Reset (POR), or Hardware Reset is in progress or complete. The RY/BY# status is valid after the rising edge of the final WE# pulse in a command sequence, when V_{CC} is above V_{CC} minimum during POR, or after the falling edge of RESET#. Since RY/BY# is an open drain output, several RY/BY# pins can be tied together in parallel with a pull up resistor to V_{IO} .

If the output is Low (Busy), the device is actively erasing, programming, or resetting. (This includes programming in the Erase Suspend mode). If the output is High (Ready), the device is ready to read data (including during the Erase Suspend mode), or is in the standby mode.

Table 5.3, Data Polling Status on page 36 shows the outputs for RY/BY# in each operation.

If an Embedded algorithm has failed (Program / Erase failure as result of max pulses or Sector is locked), RY/BY# will stay Low (busy) until status register bits 4 and 5 are cleared and the reset command is issued. This includes Erase or Programming on a locked sector.

7.5 Hardware Reset

The RESET# input provides a hardware method of resetting the device to standby state. When RESET# is driven Low for at least a period of t_{RP}, the device immediately:

- terminates any operation in progress,
- exits any ASO,
- tristates all outputs,
- resets the Status Register,
- resets the EAC to standby state.
- CE# is ignored for the duration of the reset operation (t_{RPH}).
- To meet the Reset current specification (I_{CC5}) CE# must be held High.

To ensure data integrity any operation that was interrupted should be reinitiated once the device is ready to accept another command sequence.

Document Number: 001-98285 Rev. *J



8. Signal Protocols

The following sections describe the host system interface signal behavior and timing for the 29GL-S family flash devices.

8.1 Interface States

Table 8.1 describes the required value of each interface signal for each interface state.

Table 8.1 Interface States

Interface State	V _{CC}	V _{IO}	RESET#	CE#	OE#	WE#	A _{MAX} -A0	DQ15- DQ0
Power-Off with Hardware Data Protection	< V _{LKO}	≤ V _{CC}	Х	Х	Х	Х	Х	High-Z
Power-On (Cold) Reset	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Х	Х	Х	Х	х	High-Z
Hardware (Warm) Reset	$\geq V_{CC}$ min	$\geq V_{IO} \min$ $\leq V_{CC}$	L	Х	Х	Х	Х	High-Z
Interface Standby	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Н	Н	Х	Х	Х	High-Z
Automatic Sleep (Notes 1, 3)	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Н	L	Х	Х	Valid	Output Available
Read with Output Disable (Note 2)	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Н	L	Н	Н	Valid	High-Z
Random Read	≥ V _{CC} min	$\geq V_{IO}$ min	Н	L	L	Н	Valid	Output Valid
Page Read	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Н	L	L	Н	A _{MAX} -A4 Valid A3-A0 Modified	Output Valid
Write	≥ V _{CC} min	$\geq V_{IO} \min$ $\leq V_{CC}$	Н	L	Н	L	Valid	Input Valid

Legend:

 $L = V_{IL}$

 $H = V_{IH}$

 $X = either V_{IL} or V_{IH}$

L/H = rising edge

H/L = falling edge

Valid = all bus signals have stable L or H level

Modified = valid state different from a previous valid state

Available = read data is internally stored with output driver controlled by OE#

Notes:

- 1. WE# and OE# can not be at V_{IL} at the same time.
- 2. Read with Output Disable is a read initiated with OE# High.
- 3. Automatic Sleep is a read/write operation where data has been driven on the bus for an extended period, without CE# going High and the device internal logic has gone into standby mode to conserve power.

8.2 Power-Off with Hardware Data Protection

The memory is considered to be powered off when the core power supply (V_{CC}) drops below the lock-out voltage (V_{LKO}) . When V_{CC} is below V_{LKO} , the entire memory array is protected against a program or erase operation. This ensures that no spurious alteration of the memory content can occur during power transition. During a power supply transition down to Power-Off, V_{IO} should remain less than or equal to V_{CC} .

If V_{CC} goes below V_{RST} (Min) then returns above V_{RST} (Min) to V_{CC} minimum, the Power-On Reset interface state is entered and the EAC starts the Cold Reset Embedded Algorithm.



8.3 Power Conservation Modes

8.3.1 Interface Standby

Standby is the default, low power, state for the interface while the device is not selected by the host for data transfer (CE# = High). All inputs are ignored in this state and all outputs except RY/BY# are high impedance. RY/BY# is a direct output of the EAC, not controlled by the Host Interface.

8.3.2 Automatic Sleep

The automatic sleep mode reduces device interface energy consumption to the sleep level (I_{CC6}) following the completion of a random read access time. The device automatically enables this mode when addresses remain stable for t_{ACC} + 30 ns. While in sleep mode, output data is latched and always available to the system. Output of the data depends on the level of the OE# signal but, the automatic sleep mode current is independent of the OE# signal level. Standard address access timings (t_{ACC} or t_{PACC}) provide new data when addresses are changed. I_{CC6} in DC Characteristics on page 69 represents the automatic sleep mode current specification.

Automatic sleep helps reduce current consumption especially when the host system clock is slowed for power reduction. During slow system clock periods, read and write cycles may extend many times their length versus when the system is operating at high speed. Even though CE# may be Low throughout these extended data transfer cycles, the memory device host interface will go to the Automatic Sleep current at t_{ACC} + 30 ns. The device will remain at the Automatic Sleep current for t_{ASSB} . Then the device will transition to the standby current level. This keeps the memory at the Automatic Sleep or standby power level for most of the long duration data transfer cycles, rather than consuming full read power all the time that the memory device is selected by the host system.

However, the EAC operates independent of the automatic sleep mode of the host interface and will continue to draw current during an active Embedded Algorithm. Only when both the host interface and EAC are in their standby states is the standby level current achieved.

8.4 Read

8.4.1 Read With Output Disable

When the CE# signal is asserted Low, the host system memory controller begins a read or write data transfer. Often there is a period at the beginning of a data transfer when CE# is Low, Address is valid, OE# is High, and WE# is High. During this state a read access is assumed and the Random Read process is started while the data outputs remain at high impedance. If the OE# signal goes Low, the interface transitions to the Random Read state, with data outputs actively driven. If the WE# signal is asserted Low, the interface transitions to the Write state. Note, OE# and WE# should never be Low at the same time to ensure no data bus contention between the host system and memory.

8.4.2 Random (Asynchronous) Read

When the host system interface selects the memory device by driving CE# Low, the device interface leaves the Standby state. If WE# is High when CE# goes Low, a random read access is started. The data output depends on the address map mode and the address provided at the time the read access is started.

The data appears on DQ15-DQ0 when CE# is Low, OE# is Low, WE# remains High, address remains stable, and the asynchronous access times are satisfied. Address access time (t_{ACC}) is equal to the delay from stable addresses to valid output data. The chip enable access time (t_{CE}) is the delay from stable CE# to valid data at the outputs. In order for the read data to be driven on to the data outputs the OE# signal must be Low at least the output enable time (t_{CE}) before valid data is available.

At the completion of the random access time from CE# active (t_{CE}), address stable (t_{ACC}), or OE# active (t_{OE}), whichever occurs latest, the data outputs will provide valid read data from the currently active address map mode. If CE# remains Low and any of the A_{MAX} to A4 address signals change to a new value, a new random read access begins. If CE# remains Low and OE# goes High the interface transitions to the Read with Output Disable state. If CE# remains Low, OE# goes High, and WE# goes Low, the interface transitions to the Write state. If CE# returns High, the interface goes to the Standby state. Back to Back accesses, in which CE# remains Low between accesses, requires an address change to initiate the second access.

See Asynchronous Read Operations on page 75.



8.4.3 Page Read

After a Random Read access is completed, if CE# remains Low, OE# remains Low, the A_{MAX} to A4 address signals remain stable, and any of the A3 to A0 address signals change, a new access within the same Page begins. The Page Read completes much faster (t_{PACC}) than a Random Read access.

8.5 Write

8.5.1 Asynchronous Write

When WE# goes Low after CE is Low, there is a transition from one of the read states to the Write state. If WE# is Low before CE# goes Low, there is a transition from the Standby state directly to the Write state without beginning a read access.

When CE# is Low, OE# is High, and WE# goes Low, a write data transfer begins. Note, OE# and WE# should never be Low at the same time to ensure no data bus contention between the host system and memory. When the asynchronous write cycle timing requirements are met the WE# can go High to capture the address and data values in to EAC command memory.

Address is captured by the falling edge of WE# or CE#, whichever occurs later. Data is captured by the rising edge of WE# or CE#, whichever occurs earlier.

When CE# is Low before WE# goes Low and stays Low after WE# goes High, the access is called a WE# controlled Write. When WE# is High and CE# goes High, there is a transition to the Standby state. If CE# remains Low and WE# goes High, there is a transition to the Read with Output Disable state.

When WE# is Low before CE# goes Low and remains Low after CE# goes High, the access is called a CE# controlled Write. A CE# controlled Write transitions to the Standby state.

If WE# is Low before CE# goes Low, the write transfer is started by CE# going Low. If WE# is Low after CE# goes High, the address and data are captured by the rising edge of CE#. These cases are referred to as CE# controlled write state transitions.

Write followed by Read accesses, in which CE# remains Low between accesses, requires an address change to initiate the following read access.

Back to Back accesses, in which CE# remains Low between accesses, requires an address change to initiate the second access.

The EAC command memory array is not readable by the host system and has no ASO. The EAC examines the address and data in each write transfer to determine if the write is part of a legal command sequence. When a legal command sequence is complete the EAC will initiate the appropriate EA.

8.5.2 Write Pulse "Glitch" Protection

Noise pulses of less than 5 ns (typical) on WE# will not initiate a write cycle.

8.5.3 Logical Inhibit

Write cycles are inhibited by holding OE# at V_{IL} , or CE# at V_{IH} , or WE# at V_{IH} . To initiate a write cycle, CE# and WE# must be Low (V_{IL}) while OE# is High (V_{IH}) .

Document Number: 001-98285 Rev. *J



9. Electrical Specifications

9.1 Absolute Maximum Ratings

Table 9.1 Absolute Maximum Ratings

Storage Temperature Plastic Packages	−65 °C to +150 °C
Ambient Temperature with Power Applied	−65 °C to +125 °C
Voltage with Respect to Ground	
All pins other than RESET# (Note 1)	-0.5V to (V _{IO} + 0.5V)
RESET# (Note 1)	-0.5V to (V _{CC} + 0.5V)
Output Short Circuit Current (Note 2)	100 mA
V _{CC}	−0.5V to +4.0V
V _{IO}	−0.5V to +4.0V

Notes:

- 2. No more than one output may be shorted to ground at a time. Duration of the short circuit should not be greater than one second.
- Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the
 device at these or any other conditions above those indicated in the operational sections of this data sheet is not implied. Exposure of the device to absolute maximum
 rating conditions for extended periods may affect device reliability.

9.2 Latchup Characteristics

This product complies with JEDEC standard JESD78C latchup testing requirements.

9.3 Operating Ranges

9.3.1 Temperature Ranges

Industrial (I) Devices

Ambient Temperature (T_A) -40°C to +85°C

9.3.2 Power Supply Voltages

V_{CC} 2.7V to 3.6V

 V_{IO} 1.65V to V_{CC} + 200 mV

Operating ranges define those limits between which the functionality of the device is guaranteed.

9.3.3 Power-Up and Power-Down

During power-up or power-down V_{CC} must always be greater than or equal to V_{IO} ($V_{CC} \ge V_{IO}$).

The device ignores all inputs until a time delay of t_{VCS} has elapsed after the moment that V_{CC} and V_{IO} both rise above, and stay above, the minimum V_{CC} and V_{IO} thresholds. During t_{VCS} the device is performing power on reset operations.

During power-down or voltage drops below V_{CC} Lockout maximum (V_{LKO}), the V_{CC} and V_{IO} voltages must drop below V_{CC} Reset (V_{RST}) minimum for a period of t_{PD} for the part to initialize correctly when V_{CC} and V_{IO} again rise to their operating ranges. See Figure 9.2 on page 67. If during a voltage drop the V_{CC} stays above V_{LKO} maximum the part will stay initialized and will work correctly when V_{CC} is again above V_{CC} minimum. If the part locks up from improper initialization, a hardware reset can be used to initialize the part correctly.

Normal precautions must be taken for supply decoupling to stabilize the V_{CC} and V_{IO} power supplies. Each device in a system should have the V_{CC} and V_{IO} power supplies decoupled by a suitable capacitor close to the package connections (this capacitor is generally on the order of 0.1 μ F). At no time should V_{IO} be greater then 200 mV above V_{CC} ($V_{CC} \ge V_{IO} - 200$ mV).

Minimum DC voltage on input or I/O pins is -0.5V. During voltage transitions, input or I/O pins may undershoot V_{SS} to -2.0V for periods of up to 20 ns. See Figure 9.3
on page 68. Maximum DC voltage on input or I/O pins is V_{CC} +0.5V. During voltage transitions, input or I/O pins may overshoot to V_{CC} +2.0V for periods up to 20 ns.
See Figure 9.4 on page 68

time



Table 9.2 Power-Up/Power-Down Voltage and Timing

Symbol	Parameter	Min	Max	Unit
V _{CC}	V _{CC} Power Supply	2.7	3.6	V
V _{LKO}	V _{CC} level below which re-initialization is required (Note 1)	2.25	2.5	V
V _{RST}	V_{CC} and V_{IO} Low voltage needed to ensure initialization will occur (Note 1)	1.0		V
t _{VCS}	V _{CC} and V _{IO} ≥ minimum to first access (Note 1)	300		μs
t _{PD}	Duration of V _{CC} ≤ V _{RST} (min) (Note 1)	15		μs

Power Supply Voltage

Vcc (max)


V_{IO} (min)


V_{IO} (min)

V_{IO} (min)

V_{IO} (min)

Figure 9.1 Power-up





^{1.} Not 100% tested.



9.3.4 Input Signal Overshoot

Figure 9.3 Maximum Negative Overshoot Waveform





Figure 9.4 Maximum Positive Overshoot Waveform





9.4 DC Characteristics

Table 9.3 DC Characteristics (-40 °C to +85 °C)

Paramete r	Description	Test Conditions	Min	Typ (Note 2)	Max	Unit
I _{LI}	Input Load Current	$V_{IN} = V_{SS}$ to V_{CC} , $V_{CC} = V_{CC}$ max		+0.02	±1.0	μΑ
I _{LO}	Output Leakage Current	$V_{OUT} = V_{SS}$ to V_{CC} , $V_{CC} = V_{CC}$ max		+0.02	±1.0	μA
I _{CC1}	V _{CC} Active Read Current	CE# = V _{IL} , OE# = V _{IH} , Address switching@ 5 MHz, V _{CC} = V _{CC} max		55	60	mA
I _{CC2}	V _{CC} Intra-Page Read Current	CE# = V_{IL} , OE# = V_{IH} , Address switching@ 33 MHz, V_{CC} = V_{CC} max		9	25	mA
I _{CC3}	V _{CC} Active Erase/Program Current (Notes 1, 2)	$CE\# = V_{IL}$, $OE\# = V_{IH}$, $V_{CC} = V_{CC}$ max		45	100	mA
I _{CC4}	V _{CC} Standby Current	CE#, RESET#, OE# = V_{IH} , V_{IH} = V_{IO} V_{IL} = V_{SS} , V_{CC} = V_{CC} max		70	100	μΑ
I _{CC5}	V _{CC} Reset Current (Notes 2, 7)	$CE\# = V_{IH}, RESET\# = V_{IL},$ $V_{CC} = V_{CC} max$		10	20	mA
	Automatic Sleep Mode (Note 3)	$V_{IH} = V_{IO}$, $V_{IL} = V_{SS}$, $V_{CC} = V_{CC}$ max, $t_{ACC} + 30$ ns		3	6	mA
I _{CC6}	Automatic Sleep Mode (Note 3)	$\begin{aligned} & V_{IH} = V_{IO}, \ V_{IL} = V_{SS}, \\ & V_{CC} = V_{CC} \ \text{max}, \ t_{ASSB} \end{aligned}$		100	150	μΑ
I _{CC7}	V _{CC} Current during power up (Notes 2, 6)	$\begin{aligned} \text{RESET\#} &= \text{V}_{\text{IO}}, \text{CE\#} &= \text{V}_{\text{IO}}, \text{OE\#} &= \text{V}_{\text{IO}}, \\ \text{V}_{\text{CC}} &= \text{V}_{\text{CC}} \text{ max}, \end{aligned}$		53	80	mA
V _{IL}	Input Low Voltage (Note 4)		-0.5		0.3 x V _{IO}	V
V _{IH}	Input High Voltage (Note 4)		0.7 x V _{IO}		V _{IO} + 0.4	V
V _{OL}	Output Low Voltage (Notes 4, 8)	I_{OL} = 100 μ A for DQ15-DQ0; I_{OL} = 2 mA for RY/BY#			0.15 x V _{IO}	V
V _{OH}	Output High Voltage (Note 4)	I _{OH} = 100 μA	0.85 x V _{IO}			V
V _{LKO}	Low V _{CC} Lock-Out Voltage (Note 2)		2.25		2.5	V
V _{RST}	Low V _{CC} Power on Reset Voltage (Note 2)			1.0		V

- 1. $I_{\rm CC}$ active while Embedded Algorithm is in progress.
- 2. Not 100% tested.
- 3. Automatic sleep mode enables the lower power mode when addresses remain stable for the specified designated time.
- 4. $V_{IO} = 1.65 V$ to V_{CC} or 2.7V to V_{CC} depending on the model.
- 5. $V_{CC} = 3V$ and $V_{IO} = 3V$ or 1.8V. When V_{IO} is at 1.8V, I/O pins cannot operate at >1.8V.
- 6. During power-up there are spikes of current demand, the system needs to be able to supply this current to insure the part initializes correctly.
- 7. If an embedded operation is in progress at the start of reset, the current consumption will remain at the embedded operation specification until the embedded operation is stopped by the reset. If no embedded operation is in progress when reset is started, or following the stopping of an embedded operation, I_{CC5} will be drawn during the remainder of t_{RPH}. After the end of t_{RPH} the device will go to standby mode until the next read or write.
- 8. The recommended pull-up resistor for RY/BY# output is 5k to 10k Ohms.



Table 9.4 DC Characteristics (-40 °C to +105 °C)

Paramete r	Description	Test Conditions	Min	Typ (Note 2)	Max	Unit
I _{LI}	Input Load Current	$V_{IN} = V_{SS}$ to V_{CC} , $V_{CC} = V_{CC}$ max		+0.02	±1.0	μΑ
I _{LO}	Output Leakage Current	$V_{OUT} = V_{SS}$ to V_{CC} , $V_{CC} = V_{CC}$ max		+0.02	±1.0	μΑ
I _{CC1}	V _{CC} Active Read Current	CE# = V_{IL} , OE# = V_{IH} , Address switching@ 5 MHz, V_{CC} = V_{CC} max		55	60	mA
I _{CC2}	V _{CC} Intra-Page Read Current	CE# = V_{IL} , OE# = V_{IH} , Address switching@ 33 MHz, V_{CC} = V_{CC} max		9	25	mA
I _{CC3}	V _{CC} Active Erase/Program Current (Notes 1, 2)	$CE\# = V_{IL}$, $OE\# = V_{IH}$, $V_{CC} = V_{CC}$ max		45	100	mA
I _{CC4}	V _{CC} Standby Current	CE#, RESET#, OE# = V_{IH} , V_{IH} = V_{IO} V_{IL} = V_{SS} , V_{CC} = V_{CC} max		70	200	μΑ
I _{CC5}	V _{CC} Reset Current (Notes 2, 7)	$CE\# = V_{IH}$, $RESET\# = V_{IL}$, $V_{CC} = V_{CC}$ max		10	20	mA
1	Automatic Sleep Mode (Note 3)	$V_{IH} = V_{IO}, V_{IL} = V_{SS},$ $V_{CC} = V_{CC} \text{ max, } t_{ACC} + 30 \text{ ns}$		3	6	mA
I _{CC6}	Automatic Sleep Mode (Note 3)	$V_{IH} = V_{IO}, V_{IL} = V_{SS},$ $V_{CC} = V_{CC} \text{ max, } t_{ASSB}$		100	200	μΑ
I _{CC7}	V _{CC} Current during power up (Notes 2, 6)	$\begin{aligned} \text{RESET\#} &= \text{V}_{\text{IO}}, \text{CE\#} &= \text{V}_{\text{IO}}, \text{OE\#} &= \text{V}_{\text{IO}}, \\ \text{V}_{\text{CC}} &= \text{V}_{\text{CC}} \text{ max}, \end{aligned}$		53	80	mA
V _{IL}	Input Low Voltage (Note 4)		-0.5		0.3 x V _{IO}	V
V _{IH}	Input High Voltage (Note 4)		0.7 x V _{IO}		V _{IO} + 0.4	V
V _{OL}	Output Low Voltage (Notes 4, 8)	I_{OL} = 100 μ A for DQ15-DQ0; I_{OL} = 2 mA for RY/BY#			0.15 x V _{IO}	V
V _{OH}	Output High Voltage (Note 4)	I _{OH} = 100 μA	0.85 x V _{IO}			V
V _{LKO}	Low V _{CC} Lock-Out Voltage (Note 2)		2.25		2.5	V
V _{RST}	Low V _{CC} Power on Reset Voltage (Note 2)			1.0		٧

- 1. $I_{\rm CC}$ active while Embedded Algorithm is in progress.
- 2. Not 100% tested.
- 3. Automatic sleep mode enables the lower power mode when addresses remain stable for the specified designated time.
- 4. $V_{IO} = 1.65 V$ to V_{CC} or 2.7V to V_{CC} depending on the model.
- 5. $V_{CC} = 3V$ and $V_{IO} = 3V$ or 1.8V. When V_{IO} is at 1.8V, I/O pins cannot operate at >1.8V.
- 6. During power-up there are spikes of current demand, the system needs to be able to supply this current to insure the part initializes correctly.
- 7. If an embedded operation is in progress at the start of reset, the current consumption will remain at the embedded operation specification until the embedded operation is stopped by the reset. If no embedded operation is in progress when reset is started, or following the stopping of an embedded operation, I_{CC7} will be drawn during the remainder of t_{RPH}. After the end of t_{RPH} the device will go to standby mode until the next read or write.
- 8. The recommended pull-up resistor for RY/BY# output is 5k to 10k Ohms.



9.5 Capacitance Characteristics

Table 9.5 Connector Capacitance for FBGA (LAA) Package

Parameter Symbol	Parameter Description	Test Setup	Тур	Max	Unit
C _{IN}	Input Capacitance	V _{IN} = 0	8	9	pF
C _{OUT}	Output Capacitance	V _{OUT} = 0	5	7	pF
C _{IN2}	Control Pin Capacitance	V _{IN} = 0	4	8	pF
RY/BY#	Output Capacitance	V _{OUT} = 0	3	4	pF

Notes:

- 1. Sampled, not 100% tested.
- 2. Test conditions $T_A = 25$ °C, f = 1.0 MHz.

Table 9.6 Connector Capacitance for FBGA (LAE) Package

Parameter Symbol	Parameter Description	Test Setup	Тур	Max	Unit
C _{IN}	Input Capacitance	V _{IN} = 0	7	8	pF
C _{OUT}	Output Capacitance	V _{OUT} = 0	5	6	pF
C _{IN2}	Control Pin Capacitance	V _{IN} = 0	3	7	pF
RY/BY#	Output Capacitance	V _{OUT} = 0	3	4	pF

Notes:

- 1. Sampled, not 100% tested.
- 2. Test conditions $T_A = 25$ °C, f = 1.0 MHz.

Table 9.7 Connector Capacitance for TSOP Package

Parameter Symbol	Parameter Description	Test Setup	Тур	Max	Unit
C _{IN}	Input Capacitance	V _{IN} = 0	7	8	pF
C _{OUT}	Output Capacitance	$V_{OUT} = 0$	5	6	pF
C _{IN2}	Control Pin Capacitance	V _{IN} = 0	3	7	pF
RY/BY#	Output Capacitance	V _{OUT} = 0	3	4	pF

- 1. Sampled, not 100% tested.
- 2. Test conditions $T_A = 25$ °C, f = 1.0 MHz.



10. Timing Specifications

10.1 Key to Switching Waveforms

Waveform	Inputs Outputs				
	Steady				
	Changing from H to L				
	Changing from L to H				
	Don't Care, Any Change Permitted Changing, State Unknown				
	Does Not Apply Center Line is High Impedance State (High				

10.2 AC Test Conditions

Figure 10.1 Test Setup





Table 10.1 Test Specification

Parameter	All Speeds	Units
Output Load Capacitance, C _L	30	pF
Input Rise and Fall Times (Note 1)	1.5	ns
Input Pulse Levels	0.0-V _{IO}	V
Input timing measurement reference levels	V _{IO} /2	V
Output timing measurement reference levels	V _{IO} /2	V

Note:

Figure 10.2 Input Waveforms and Measurement Levels



Document Number: 001-98285 Rev. *J Page 72 of 102

^{1.} Measured between V_{IL} max and V_{IH} min.



10.3 Power-On Reset (POR) and Warm Reset

Normal precautions must be taken for supply decoupling to stabilize the V_{CC} and V_{IO} power supplies. Each device in a system should have the V_{CC} and V_{IO} power supplies decoupled by a suitable capacitor close to the package connections (this capacitor is generally on the order of 0.1 μ F).

Table 10.2 Power ON and Reset Parameters

Parameter	Description	Limit	Value	Unit
t _{VCS} V _{CC} Setup Time to first access (Notes 1, 2)		Min	300	μs
t _{VIOS}	V _{IO} Setup Time to first access (Notes 1, 2)	Min	300	μs
t _{RPH}	t _{RPH} RESET# Low to CE# Low		35	μs
t _{RP}	RESET# Pulse Width	Min	200	ns
t _{RH}	Time between RESET# (High) and CE# (low)	Min	50	ns
t _{CEH}	CE# Pulse Width High	Min	20	ns

Notes:

- 1. Not 100% tested.
- 2. Timing measured from V_{CC} reaching V_{CC} minimum and V_{IO} reaching V_{IO} minimum to V_{IH} on Reset and V_{IL} on CE#.
- 3. RESET# Low is optional during POR. If RESET is asserted during POR, the later of t_{RPH}, t_{VIOS}, or t_{VCS} will determine when CE# may go Low. If RESET# remains Low after t_{VIOS}, or t_{VCS} is satisfied, t_{RPH} is measured from the end of t_{VIOS}, or t_{VCS}. RESET must also be High t_{RH} before CE# goes Low.
- 4. $V_{CC} \ge V_{IO}$ 200 mV during power-up.
- 5. V_{CC} and V_{IO} ramp rate can be non-linear.
- Sum of t_{RP} and t_{RH} must be equal to or greater than t_{RPH}.

10.3.1 Power-On (Cold) Reset (POR)


During the rise of power supplies the V_{IO} supply voltage must remain less than or equal to the V_{CC} supply voltage. V_{IH} also must remain less than or equal to the V_{IO} supply.

The Cold Reset Embedded Algorithm requires a relatively long, hundreds of μ s, period (t_{VCS}) to load all of the EAC algorithms and default state from non-volatile memory. During the Cold Reset period all control signals including CE# and RESET# are ignored. If CE# is Low during t_{VCS} the device may draw higher than normal POR current during t_{VCS} but the level of CE# will not affect the Cold Reset EA. CE# or OE# must transition from High to Low after t_{VCS} for a valid read or write operation. RESET# may be High or Low during t_{VCS} . If RESET# is Low during t_{VCS} it may remain Low at the end of t_{VCS} to hold the device in the Hardware Reset state. If RESET# is High at the end of t_{VCS} the device will go to the Standby state.

When power is first applied, with supply voltage below V_{RST} then rising to reach operating range minimum, internal device configuration and warm reset activities are initiated. CE# is ignored for the duration of the POR operation (t_{VCS} or t_{VIOS}). RESET# Low during this POR period is optional. If RESET# is driven Low during POR it must satisfy the Hardware Reset parameters t_{RP} and t_{RPH} . In which case the Reset operations will be completed at the later of t_{VCS} or t_{VIOS} or t_{RPH} .

During Cold Reset the device will draw I_{CC7} current.

Figure 10.3 Power-Up Diagram





10.3.2 Hardware (Warm) Reset

During Hardware Reset (t_{RPH}) the device will draw t_{CC5} current.

When RESET# continues to be held at V_{SS} , the device draws CMOS standby current (I_{CC4}). If RESET# is held at V_{IL} , but not at V_{SS} , the standby current is greater.


If a Cold Reset has not been completed by the device when RESET# is asserted Low after t_{VCS} , the Cold Reset# EA will be performed instead of the Warm RESET#, requiring t_{VCS} time to complete.

See Figure 10.4, Hardware Reset on page 74.

After the device has completed POR and entered the Standby state, any later transition to the Hardware Reset state will initiate the Warm Reset Embedded Algorithm. A Warm Reset is much shorter than a Cold Reset, taking tens of μ s (t_{RPH}) to complete. During the Warm Reset EA, any in progress Embedded Algorithm is stopped and the EAC is returned to its POR state without reloading EAC algorithms from non-volatile memory. After the Warm Reset EA completes, the interface will remain in the Hardware Reset state if RESET# remains Low. When RESET# returns High the interface will transit to the Standby state. If RESET# is High at the end of the Warm Reset EA, the interface will directly transit to the Standby state.

If POR has not been properly completed by the end of t_{VCS}, a later transition to the Hardware Reset state will cause a transition to the Power-on Reset interface state and initiate the Cold Reset Embedded Algorithm. This ensures the device can complete a Cold Reset even if some aspect of the system Power-On voltage ramp-up causes the POR to not initiate or complete correctly. The RY/BY# pin is Low during cold or warm reset as an indication that the device is busy performing reset operations.

Hardware Reset is initiated by the RESET# signal going to V_{II}.



Document Number: 001-98285 Rev. *J



10.4 AC Characteristics

10.4.1 Asynchronous Read Operations

Table 10.3 Read Operation $V_{IO} = V_{CC} = 2.7V$ to 3.6V (-40 °C to +85 °C)

Param	neter	Description	Doscription			Speed Option			Unit
JEDEC	Std	Description		Test Setup)	90	100	110	Unit
		Dood Cycle Time (Note 1)		128 Mb, 256 Mb	Min	90	100		no
t _{AVAV}	t _{RC}	Read Cycle Time (Note 1)		512 Mb, 1 Gb	IVIII		100	110	ns
+ .	4	Address to Output Dolay	CE# = V _{IL}	128 Mb, 256 Mb	Max	90	100		- ns
t _{AVQV}	t _{ACC}	Address to Output Delay	OE# = V _{IL}	512 Mb, 1 Gb	IVIAX		100	110	115
		Chin Enable to Output Delay	OF# - V	128 Mb, 256 Mb	Max	90	100		no
t _{ELQV}	t _{CE} Chip Enable to Output Delay OE		OE# = V _{IL}	512 Mb, 1 Gb	IVIAX		100	110	ns
	tpACC Page Access Time			128 Mb, 256 Mb	Max	15	20		ns
	t _{PACC}	age Access Time		512 Mb, 1 Gb	IVIAX		15	20	
t _{GLQV}	t _{OE}	Output Enable to Output Delay			Max	25			ns
t _{AXQX}	t _{OH}	Output Hold time from address Whichever Occurs First	es, CE# or OE#,		Min	0			ns
t _{EHQZ}	t _{DF}	Chip Enable or Output Enable (Note 1)	to Output High-Z		Max	15			ns
		Output Enoble Hold Time	Read		Min		0		ns
	t _{OEH}	(INOLE I)	Toggle and Data# Polling		Min		10		ns
	Automatic Olean to Otavalloutine (New 4)		CE# = V _{IL} ,	Тур	5			μs	
	t _{ASSB}	Automatic Sleep to Standby tim	ie (Note I)	Address stable	Max	8			μs

Table 10.4 Read Operation V_{IO} = 1.65V to V_{CC} , V_{CC} = 2.7V to 3.6V (-40 °C to +85 °C)

Param	eter	Description		Toot Sotu		Speed Options			Unit
JEDEC	Std	Description		Test Setu	þ	100	110	120	Ullit
+	+ .	Read Cycle Time (Note 1)		128 Mb, 256 Mb	Min	100	110		ns
t _{AVAV}	t _{RC}	Read Cycle Time (Note 1)		512 Mb, 1 Gb	IVIIII		110	120	115
		Address to Output Delay	CE# = V _{IL}	128 Mb, 256 Mb	Max	100	110		no
t _{AVQV}	t _{ACC}	Address to Output Delay	OE# = V _{IL}	512 Mb, 1 Gb	iviax		110	120	ns
		Chin Enable to Output Delay	OF# V	128 Mb, 256 Mb	Max	100	110		ns
t _{ELQV}	t _{CE}	Chip Enable to Output Delay	OE# = V _{IL}	512 Mb, 1 Gb			110	120	
		Daga Assass Time		128 Mb, 256 Mb	Max	25	30		- ns
	t _{PACC}	Page Access Time		512 Mb, 1 Gb	IVIAX		25	30	
t _{GLQV}	t _{OE}	Output Enable to Output Delay			Max	35			ns
t _{AXQX}	t _{OH}	Output Hold time from addresses, CE# or OE#, Whichever Occurs First			Min	0			ns
t _{EHQZ}	t _{DF}	Chip Enable or Output Enable Z (Note 1)	to Output High-		Max		20		ns

^{1.} Not 100% tested.



Table 10.4 Read Operation V_{IO} = 1.65V to V_{CC} , V_{CC} = 2.7V to 3.6V (-40 °C to +85 °C) (Continued)

Param	eter	Description		Toot Setup		Speed Options			Unit	
JEDEC	Std	Description		Test Setup		100	110	120	Oiiit	
	Output Enable Hold Time	Read		Min		0		ns		
	t _{OEH}	(Note 1)	Toggle and Data# Polling		Min	10			ns	
		Automatic Sloop to Standby ti	utamatia Slaan ta Standby tima (Nata 1)		Тур		5		μs	
	t _{ASSB}	Automatic Sleep to Standby time (Note 1)		Address stable Max			8		μs	

Table 10.5 Read Operation $V_{IO} = V_{CC} = 2.7V$ to 3.6V (-40 °C to +105 °C)

Para	meter	Description		Test Setup		Speed Option			Unit
JEDEC	Std	Description	•	rest Setup		100	110	120	Onit
	4	Pood Cycle Time (Note 1)		128 Mb, 256 Mb	Min	100	110		ns
t _{AVAV}	t _{RC}	Read Cycle Time (Note 1)		512 Mb, 1 Gb	IVIIII		110	120	115
t	t. a. Address	Address to Output Delay	CE# = V _{IL}	128 Mb, 256 Mb	Max	100	110		ns
t _{AVQV}	t _{ACC}	Address to Odtput Delay	OE# = V _{IL}	512 Mb, 1 Gb	IVIAX		110	120	115
t	t	Chip Enable to Output	OE# = V _{IL}	128 Mb, 256 Mb	Max	100	110		ns
t _{ELQV}	t _{CE}	Delay OE# = V _I		512 Mb, 1 Gb	IVIAX		110	120	115
	t	I Page Access Time		128 Mb, 256 Mb	Max	15	20		- ns
	t _{PACC}			512 Mb, 1 Gb	IVIAX		15	20	
t _{GLQV}	t _{OE}	Output Enable to Output Delay			Max	25			ns
t _{AXQX}	t _{OH}	Output Hold time from addi OE#, Whichever Occurs Fi			Min	0			ns
t _{EHQZ}	t _{DF}	Chip Enable or Output Ena High-Z (Note 1)	ble to Output		Max	15			ns
		Output Enable Hold Time	Read		Min		0		ns
	t _{OEH}	toeh (Note 1) Toggle and Data# Polling		Min		10		ns	
	t	Automatic Sleep to Standby time (Note		CE# = V _{IL} , Address	Тур	5		μs	
	t _{ASSB}	Automatic oleep to otalido	y unite (Note 1)	stable	Max		8	•	μs

^{1.} Not 100% tested.

^{1.} Not 100% tested.



Table 10.6 Read Operation V_{IO} = 1.65V to V_{CC} , V_{CC} = 2.7V to 3.6V (-40 °C to +105 °C)

Para	meter	Description		Took Cotum		SI	peed Opti	on	Unit
JEDEC	Std	- Description	1	Test Setup		110	120	130	Unit
+	+	Read Cycle Time (Note 1)		128 Mb, 256 Mb	Min	110	120		ns
t _{AVAV}	t _{RC}	Read Cycle Time (Note 1)		512 Mb, 1 Gb	IVIIII		120	130	115
+	+		CE# = V _{IL}	128 Mb, 256 Mb	Max	110	120		ns
t _{AVQV}	t _{ACC}	Address to Output Delay	OE# = V _{IL} 512 Mb, 1 Gb		IVIAX		120	130	115
+	+ .	Chip Enable to Output	OE# = V _{IL}	128 Mb, 256 Mb	Max	110	120		ns
t _{ELQV}	t _{CE}	Delay	OE# = VIL	512 Mb, 1 Gb	IVIAX		120	130	115
	+	Page Access Time	Page Access Time		Max	25	30		ns
	t _{PACC}	C Tage Access Time		512 Mb, 1 Gb	IVIAX		25	30	115
t_{GLQV}	t _{OE}	Output Enable to Output D	elay		Max	35			ns
t _{AXQX}	t _{OH}	Output Hold time from add OE#, Whichever Occurs Fi			Min	0			ns
t _{EHQZ}	t _{DF}	Chip Enable or Output Ena High-Z (Note 1)	ble to Output		Max		20		ns
		Output Enable Hold Time	Read		Min		0		ns
	t _{OEH}	toeh Output Enable Hold Time (Note 1) Toggle and Data# Polling		Min		10		ns	
	+	Automatic Sloop to Standh	v timo (Note 1)	CE# = V _{IL} , Address	Тур	5		μs	
	t _{ASSB}	Automatic Sleep to Standb	y unie (Note I)	stable	Max		8		μs

^{1.} Not 100% tested.



Amax-A0

tCE#

tOH

tCE#

tOH


tDF

tOH

OE#

Figure 10.5 Back to Back Read (t_{ACC}) Operation Timing Diagram

Figure 10.6 Back to Back Read Operation (t_{RC}) Timing Diagram



Back to Back operations, in which CE# remains Low between accesses, requires an address change to initiate the second access.

Amax-A4
A3-A0

CE#

TOE

tPACC

DQ15-DQ0

Figure 10.7 Page Read Timing Diagram

Note:

Word Configuration: Toggle A0, A1, A2, and A3.



10.4.2 Asynchronous Write Operations

Table 10.7 Write Operations

Para	meter	Deceyintian		$V_{10} = 2.7V \text{ to}$	V _{IO} = 1.65V	Unit
JEDEC	Std	— Description		. v _{cc}	to V _{CC}	Unit
t _{AVAV}	t _{WC}	Write Cycle Time (Note 1)	Min	60		ns
t _{AVWL}	t _{AS}	Address Setup Time	Min	0		ns
	t _{ASO}	Address Setup Time to OE# Low during toggle bit polling	Min	1	5	ns
t _{WLAX}	t _{AH}	Address Hold Time	Min	4	5	ns
	t _{AHT}	Address Hold Time From CE# or OE# High during toggle bit polling	Min	()	ns
t _{DVWH}	t _{DS}	Data Setup Time	Min	3	0	ns
t _{WHDX}	t _{DH}	Data Hold Time	Min	()	ns
	t _{OEPH}	Output Enable High during toggle bit polling or following status register read.	Min	2	0	ns
t _{GHWL}	t _{GHWL}	Read Recovery Time Before Write (OE# High to WE# Low)	Min	()	ns
t _{ELWL}	t _{CS}	CE# Setup Time	Min	()	ns
t _{WHEH}	t _{CH}	CE# Hold Time	Min	()	ns
t _{WLWH}	t _{WP}	WE# Pulse Width	Min	2	5	ns
t_{WHWL}	t _{WPH}	WE# Pulse Width High	Min	2	0	ns

Amax-A0

tAS

tAH

tCS

tCH

CE#

OE#

UDS

tDH

DQ15-DQ0

Figure 10.8 Back to Back Write Operation Timing Diagram

^{1.} Not 100% tested.



Amax-A0

tAS

tAH

tCS

tWP

tWPH

tDS

tDH

Figure 10.9 Back to Back (CE#VIL) Write Operation Timing Diagram










Figure 10.11 Write to Read (t_{CE}) Operation Timing Diagram










Figure 10.13 Read to Write (CE# Toggle) Operation Timing Diagram

Table 10.8 Erase/Program Operations

Para	meter	Description		V _{IO} = 2.7V	V _{IO} = 1.65V	Unit
JEDEC	Std	- Description		V _{IO} = 2.7V to V _{CC}	V _{IO} = 1.65V to V _{CC}	Unit
		Write Buffer Program Operation	Тур	(No	te 3)	μs
t _{WHWH1}	t _{WHWH1}	Effective Write Buffer Program Operation per Word	Тур	(No	te 3)	μs
		Program Operation per Word or Page	Тур	(No	te 3)	μs
t _{WHWH2}	t _{WHWH2}	Sector Erase Operation (Note 1)	Тур	(No	te 3)	ms
	t _{BUSY}	Erase/Program Valid to RY/BY# Delay	Max	80		ns
	t _{SR/W}	Latency between Read and Write operations (Note 2)	Min	1	0	ns
	t _{ESL}	Erase Suspend Latency	Max	(No	te 3)	μs
	t _{PSL}	Program Suspend Latency	Max	(No	te 3)	μs
	t _{RB}	RY/BY# Recovery Time	Min	()	μs

- 1. Not 100% tested.
- 2. Upon the rising edge of WE#, must wait $t_{SR/W}$ before switching to another address.
- 3. See Table 5.4 on page 40 and Table 5.5 on page 41 for specific values.






Figure 10.14 Program Operation Timing Diagram

1. $PA = program \ address, \ PD = program \ data, \ D_{OUT}$ is the true data at the program address.




Figure 10.15 Chip/Sector Erase Operation Timing Diagram

Note:

1. SA = sector address (for sector erase), VA = valid address for reading status data.



Table 10.9 ASO Entry Timing

t _{ASOSTART}	Falling edge of CE# or address change whichever comes last
t _{ASOEND}	Rising edge of CE# or Rising edge of WE# whichever comes first
t _{ASO}	$25 \text{ ns} < t_{ASO} < 50 \text{ ns or } t_{ASO} > 150 \text{ ns}$

Addresses

CE#

WE#


Figure 10.16 ASO Entry Timing

55h (1st command cycle) of CFI

tasostart

tasoend

Figure 10.17 Data# Polling Timing Diagram (During Embedded Algorithms)



1. VA = Valid address. Illustration shows first status cycle after command sequence, last status read cycle, and array data read cycle.






Figure 10.18 Toggle Bit Timing Diagram (During Embedded Algorithms)

1. DQ6 will toggle at any read address while the device is busy. DQ2 will toggle if the address is within the actively erasing sector.

Enter Erase **Enter Erase** Embedded Erase Suspend Suspend Program Resume Erasing Erase Erase Suspend Erase Suspend Program Erase Complete WE# Erase Suspend Read Read DQ6 DQ2

Figure 10.19 DQ2 vs. DQ6 Relationship Diagram

Note:

1. The system may use OE# or CE# to toggle DQ2 and DQ6. DQ2 toggles only when read at an address within the erase-suspended sector.

10.4.3 Alternate CE# Controlled Write Operations

Table 10.10 Alternate CE# Controlled Write Operations

Para	meter	Description		V - 2.7V to V	V = 1.65V to V	Unit
JEDEC	Std	Description		V _{IO} = 2.7 V to V _{CC}	V_{IO} = 1.65V to V_{CC}	Onit
t _{AVAV}	t _{WC}	Write Cycle Time (Note 1)	Min	60		ns
t _{AVWL}	t _{AS}	Address Setup Time	Min	0		ns
	t _{ASO}	Address Setup Time to OE# Low during toggle bit polling	Min	15		ns
t _{WLAX}	t _{AH}	Address Hold Time	Min	4	! 5	ns
	t _{AHT}	Address Hold Time From CE# or OE# High during toggle bit polling	Min		0	ns
t _{DVWH}	t _{DS}	Data Setup Time	Min	3	30	ns
t _{WHDX}	t _{DH}	Data Hold Time	Min		0	ns
	t _{CEPH}	CE# High during toggle bit polling	Min	2	20	ns



Table 10.10 Alternate CE# Controlled Write Operations (Continued)

Para	meter	Description		$V_{IO} = 2.7V \text{ to } V_{CC}$ $V_{IO} = 1.65V \text{ to } V_{CC}$	Unit
JEDEC	Std	Description		V _{IO} = 2.7 V to V _{CC} V _{IO} = 1.03 V to V _{CC}	Ollit
	t _{0EPH}	OE# High during toggle bit polling	Min	20	ns
t _{GHEK}	t _{GHEL}	Read Recovery Time Before Write (OE# High to WE# Low)	Min	0	ns
t _{WLEL}	t _{WS}	WE# Setup Time	Min	0	ns
t _{ELWH}	t_{WH}	WE# Hold Time	Min	0	ns
t _{ELEH}	t _{CP}	CE# Pulse Width	Min	25	ns
t _{EHEL}	t _{CPH}	CE# Pulse Width High	Min	20	ns

Figure 10.20 Back to Back (CE#) Write Operation Timing Diagram





Figure 10.21 (CE#) Write to Read Operation Timing Diagram



^{1.} Not 100% tested.



11. Physical Interface

11.1 56-Pin TSOP

11.1.1 Connection Diagram

Figure 11.1 56-Pin Standard TSOP A24 -NC for GL256S, GL128S NC for GL128S -A23 56-Pin TSOP A25 NC for GL512S, GL256S, GL128S A22 55 A15 3 54 A16 53 RFU A14 4 52 A13 V_{SS} DQ15 5 51 A12 6 A11 50 DQ7 49 DQ14 A10 8 DQ6 A9 48 9 DQ13 Α8 47 10 DQ5 A19 46 11 45 DQ12 A20 12 13 WE# 44 DQ4 RESET# 43 14 42 DQ11 A21 15 WP# 16 41 DQ3 RY/BY# 17 40 DQ10 39 DQ2 A18 18 38 A17 19 Α7 20 37 DQ1 A6 DQ8 21 36 35 A5 22 DQ0 OE# V_{SS} A4 23 34 АЗ 24 33 A2 25 32 CE# A1 RFU 31 26 A0 RFU 27 30 DNU 28 V_{IO}


Pin 28, Do Not Use (DNU), a device internal signal is connected to the package connector. The connector may be used by Cypress for test or other purposes and is
not intended for connection to any host system signal. Do not use these connections for PCB Signal routing channels. Though not recommended, the ball can be
connected to V_{CC} or V_{SS} through a series resistor.

^{2.} Pin 27, 30, and 53 Reserved for Future Use (RFU).



11.1.2 Physical Diagram

Figure 11.2 56-Pin Thin Small Outline Package (TSOP), $14 \times 20 \text{ mm}$



PACKAGE		TS 56			
JEDEC	M	D-142 (B) E	С		
SYMBOL	MIN.	NOM.	MAX.		
Α			1.20		
A1	0.05		0.15		
A2	0.95	1.00	1.05		
b1	0.17	0.20	0.23		
b	0.17	0.22	0.27		
c1	0.10		0.16		
С	0.10		0.21		
D	19.80	20.00	20.20		
D1	18.30	18.40	18.50		
Е	13.90	14.00	14.10		
е	(0.50 BASIC			
L	0.50	0.60	0.70		
Ø	0°	-	8°		
R	0.08	·	0.20		
N	56				

NOTES:

CONTROLLING DIMENSIONS ARE IN MILLIMETERS (mm).
(DIMENSIONING AND TOLERANCING CONFORMS TO ANSI Y14.5M-1982.)



TO BE DETERMINED AT THE SEATING PLANE -C- . THE SEATING PLANE IS
DEFINED AS THE PLANE OF CONTACT THAT IS MADE WHEN THE PACKAGE
LEADS ARE ALLOWED TO REST FREELY ON A FLAT HORIZONTAL SURFACE.

DIMENSIONS D1 AND E DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE MOLD PROTUSION IS 0.15 mm PER SIDE.

DIMENSION 6 DOES NOT INCLUDE DAMBAR PROTUSION. ALLOWABLE DAMBAR PROTUSION SHALL BE 0.08 mm TOTAL IN EXCESS OF 6 DIMENSION AT MAX MATERIAL CONDITION. MINIMUM SPACE BETWEEN PROTRUSION AND AN ADJACENT LEAD TO BE 0.07 mm.

THESE DIMESIONS APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.10 mm AND 0.25 mm FROM THE LEAD TIP.

LEAD COPLANARITY SHALL BE WITHIN 0.10 mm AS MEASURED FROM THE SEATING PLANE.

8 DIMENSION "e" IS MEASURED AT THE CENTERLINE OF THE LEADS.

3160\38.10A




11.2 64-Ball FBGA

11.2.1 Connection Diagram

Figure 11.3 64-ball Fortified Ball Grid Array

TOP VIEW

PRODUCT Pinout





- Ball E1, Do Not Use (DNU), a device internal signal is connected to the package connector. The connector may be used by Cypress for test or other purposes and is
 not intended for connection to any host system signal. Do not use these connections for PCB Signal routing channels. Though not recommended, the ball can be
 connected to V_{CC} or V_{SS} through a series resistor.
- 2. Balls F7 and G1, Reserved for Future Use (RFU).
- 3. Balls A1, A8, C1, D1, H1, and H8, No Connect (NC).



11.2.2 Physical Diagram – LAE064

Figure 11.4 LAE064—64-ball Fortified Ball Grid Array (FBGA), 9 x 9 mm





SIDE VIEW

PACKAGE	LAE 064			
JEDEC	N/A			
	9.00 mm x 9.00 mm PACKAGE			
SYMBOL	MIN	NOM	MAX	NOTE
Α			1.40	PROFILE HEIGHT
A1	0.40			STANDOFF
A2	0.60			BODY THICKNESS
D		9.00 BSC.		BODY SIZE
E	9.00 BSC.			BODY SIZE
D1	7.00 BSC.			MATRIX FOOTPRINT
E1	7.00 BSC.			MATRIX FOOTPRINT
MD	8			MATRIX SIZE D DIRECTION
ME	8			MATRIX SIZE E DIRECTION
N		64		BALL COUNT
b	0.50 0.60 0.70		0.70	BALL DIAMETER
eD	1.00 BSC.			BALL PITCH - D DIRECTION
eЕ	1.00 BSC.			BALL PITCH - E DIRECTION
SD / SE	0.50 BSC.			SOLDER BALL PLACEMENT
?	NONE			DEPOPULATED SOLDER BALLS

BOTTOM VIEW

NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- 2. ALL DIMENSIONS ARE IN MILLIMETERS.
- 3. BALL POSITION DESIGNATION PER JESD 95-1, SPP-010? EXCEPT AS NOTED).
- 4. e REPRESENTS THE SOLDER BALL GRID PITCH.
- 5. SYMBOL "MD" IS THE BALL ROW MATRIX SIZE IN THE "D" DIRECTION.
 - SYMBOL "ME" IS THE BALL COLUMN MATRIX SIZE IN THE "E" DIRECTION.
 - N IS THE TOTAL NUMBER OF SOLDER BALLS.
- Ó DIMENSION "b" IS MEASURED AT THE MAXIMUM BALL DIAMETER IN A PLANE PARALLEL TO DATUM C.
- A AND SE ARE MEASURED WITH RESPECT TO DATUMS A AND B AND DEFINE THE POSITION OF THE CENTER SOLDER BALL IN THE OUTER ROW.

WHEN THERE IS AN ODD NUMBER OF SOLDER BALLS IN ? THE OUTER ROW PARALLEL TO THE D OR E DIMENSION, RESPECTIVELY, SD OR SE = 0.000.


WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, SD OR SE = $\boxed{0/2}$

- 8. NOT USED.
- "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED BALLS.

3623 \ 16-038.12 \ 1.16.07



11.2.3 Physical Diagram – LAA064



PACKAGE	LAA 064			
JEDEC	N/A			
SEBEC		11/73		-
	13.0	0 mm x 11.00 PACKAGE	0 mm	
SYMBOL	MIN	NOM	MAX	NOTE
А			1.40	PROFILE HEIGHT
A1	0.40			STANDOFF
A2	0.60			BODY THICKNESS
D		13.00 BSC.		BODY SIZE
E	11.00 BSC.			BODY SIZE
D1	7.00 BSC.			MATRIX FOOTPRINT
E1	7.00 BSC.			MATRIX FOOTPRINT
MD	8			MATRIX SIZE D DIRECTION
ME		8		MATRIX SIZE E DIRECTION
N	64			BALL COUNT
φb	0.50 0.60 0.70		0.70	BALL DIAMETER
eD	1:00 BSC.			BALL PITCH - D DIRECTION
eЕ	1.00 BSC.			BALL PITCH - E DIRECTION
SD / SE	0.50 BSC.			SOLDER BALL PLACEMENT
	NONE			DEPOPULATED SOLDER BALLS

NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- 2. ALL DIMENSIONS ARE IN MILLIMETERS.
- 3. BALL POSITION DESIGNATION PER JESD 95-1, SPP-010 (EXCEPT AS NOTED).
- 5. SYMBOL "MD" IS THE BALL ROW MATRIX SIZE IN THE "D" DIRECTION.
 - SYMBOL "ME" IS THE BALL COLUMN MATRIX SIZE IN THE "E" DIRECTION.

N IS THE TOTAL NUMBER OF SOLDER BALLS.

- DIMENSION "b" IS MEASURED AT THE MAXIMUM BALL DIAMETER IN A PLANE PARALLEL TO DATUM C.
- SD AND SE ARE MEASURED WITH RESPECT TO DATUMS
 A AND B AND DEFINE THE POSITION OF THE CENTER
 SOLDER BALL IN THE OUTER ROW.

WHEN THERE IS AN ODD NUMBER OF SOLDER BALLS IN THE OUTER ROW PARALLEL TO THE D OR E DIMENSION, RESPECTIVELY, SD OR SE = 0.000.

WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, SD OR SE = $\left[e/2 \right]$

- 8. NOT USED.
- 9. "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED BALLS.

3354 \ 16-038.12d




11.3 56-Ball FBGA

11.3.1 Connection Diagram

Figure 11.5 56-ball Fortified Ball Grid Array

TOP VIEW


Product Pinout



- Ball G1, Do Not Use (DNU), a device internal signal is connected to the package connector. The connector may be used by Cypress® for test or other purposes and is
 not intended for connection to any host system signal. Do not use these connections for PCB Signal routing channels. Though not recommended, the ball can be
 connected to V_{CC} or V_{SS} through a series resistor.
- 2. Balls E7, F8, and H5, Reserved for Future Use (RFU).
- 3. Balls A3 and B3, No Connect (NC).



11.3.2 Physical Diagram - VBU 056



PACKAGE	VBU 056			
JEDEC	N/A			
	9.00 mm x 7.00 mm NOM PACKAGE			
SYMBOL	MIN	NOM	MAX	NOTE
Α			1.00	OVERALL THICKNESS
A1	0.17			BALL HEIGHT
D		9.00 BSC.		BODY SIZE
E	7.00 BSC.			BODY SIZE
D1	5.60 BSC.			BALL FOOTPRINT
E1	5.60 BSC.			BALL FOOTPRINT
MD	8			ROW MATRIX SIZE D DIRECTION
ME	8			ROW MATRIX SIZE E DIRECTION
N	56			TOTAL BALL COUNT
Øb	0.35 0.40 0.45		0.45	BALL DIAMETER
е	0.80 BSC.			BALL PITCH
SD/SE	0:40 BSC.			SOLDER BALL PLACEMENT
	A1,A8,	D4,D5,E4,E5	5,H1,H8	DEPOPULATED SOLDER BALLS

NOTES:

- DIMENSIONING AND TOLERANCING METHODS PER ASME Y14.5M-1994.
- 2. ALL DIMENSIONS ARE IN MILLIMETERS.
- 3. BALL POSITION DESIGNATION PER JEP95, SECTION 4.3, SPP-010.
- 4. e REPRESENTS THE SOLDER BALL GRID PITCH.
- 5. SYMBOL "MD" IS THE BALL MATRIX SIZE IN THE "D" DIRECTION.
 - SYMBOL "ME" IS THE BALL MATRIX SIZE IN THE "E" DIRECTION.
 - N IS THE TOTAL NUMBER OF POPULATED SOLDER BALL POSITIONS FOR MATRIX SIZE MD X ME.
- DIMENSION "b" IS MEASURED AT THE MAXIMUM BALL DIAMETER IN A PLANE PARALLEL TO DATUM C.
- \(\frac{1}{2} \) SD AND SE ARE MEASURED WITH RESPECT TO DATUMS A AND B AND DEFINE THE POSITION OF THE CENTER SOLDER BALL IN THE OUTER ROW.
 - WHEN THERE IS AN ODD NUMBER OF SOLDER BALLS IN THE OUTER ROW SD OR SE = 0.000.
 - WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, SD OR SE = e/2
- "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED BALLS.
- 41 CORNER TO BE IDENTIFIED BY CHAMFER, LASER OR INK MARK, METALLIZED MARK INDENTATION OR OTHER MEANS.
- 10. OUTLINE AND DIMENSIONS PER CUSTOMER REQUIREMENT.



12. Special Handling Instructions for FBGA Package

Special handling is required for Flash Memory products in FBGA packages.

Flash memory devices in FBGA packages may be damaged if exposed to ultrasonic cleaning methods. The package and/or data integrity may be compromised if the package body is exposed to temperatures above 150°C for prolonged periods of time.

13. Ordering Information

Valid Combinations

Table 13.1 lists configurations planned to be available in volume. The table will be updated as new combinations are released. Consult your local sales representative to confirm availability of specific combinations and to check on newly released combinations.

Table 13.1 S29GL-S Valid Combinations

		S29GL-S Valid	Combinations			
Base OPN	Speed (ns)	Package and Temperature	Model Number	Packing Type	Ordering Part Number (yy = Model Number, x = Packing Type)	
	100	DHI, FHI, TFI (Note 1)	01, 02		S29GL01GS10DHlyyx S29GL01GS10FHlyyx S29GL01GS10TFlyyx	
S20CI 04CS		DHV, TFV (Note 1)	01, 02	0, 3	S29GL01GS11DHVyyx S29GL01GS11TFVyyx	
S29GL01GS	110	DHI, FHI, TFI (Note 1)	V1, V2	(Note 2)	S29GL01GS11DHlyyx S29GL01GS11FHlyyx S29GL01GS11TFlyyx	
	120	DHV, TFV (Note 1)	V1, V2		S29GL01GS12DHVyyxx S29GL01GS12TFVyyxx	
	100	DHI, FHI, GHI, TFI (Note 1)	01, 02		S29GL512S10DHlyyx S29GL512S10FHlyyx S29GL512S10GHlyyx S29GL512S10TFlyyx	
		GHI (Note 1)	01, 02	1	S29GL512S11GHlyyx	
S29GL512S	110	DHV, TFV (Note 1)	01, 02	0, 3 (Note 2)	S29GL512S11DHVyyx S29GL512S11TFVyyx	
		DHI, FHI, TFI (Note 1)	V1, V2		S29GL512S11DHlyyx S29GL512S11FHlyyx S29GL512S11TFlyyx	
	120	DHV, TFV (Note 1)	V1, V2		S29GL512S12DHVyyxx S29GL512S12TFVyyxx	
S29GL256S	90	DHI, FHI, GHI, TFI (Note 1)	01, 02	0, 3	S29GL256S90DHIyyx S29GL256S90FHIyyx S29GL256S90GHIyyx S29GL256S90TFIyyx	
		DHV, TFV (Note 1)	01, 02		S29GL256S10DHVyyx S29GL256S10TFVyyx	
	100	DHI, FHI, TFI (Note 1)	V1, V2 (Note 2)		S29GL256S10DHlyyx S29GL256S10FHlyyx S29GL256S10TFlyyx	
	110	DHV, TFV (Note 1)	V1, V2		S29GL256S11DHVyyxx S29GL256S11TFVyyxx	




Table 13.1 S29GL-S Valid Combinations (Continued)

	S29GL-S Valid Combinations								
Base OPN	Speed (ns)	Package and Temperature	Model Number	Packing Type	Ordering Part Number (yy = Model Number, x = Packing Type)				
	90	DHI, FHI, GHI, TFI (Note 1)	01, 02		S29GL128S90DHlyyx S29GL128S90FHlyyx S29GL128S90GHlyyx S29GL128S90TFlyyx				
S29GL128S		DHV, TFV (Note 1)	01, 02 0, 3 (Note 2)	S29GL128S10DHVyyx S29GL128S10TFVyyx					
	100	DHI, FHI, TFI (Note 1)	V1, V2	(Note 2)	S29GL128S10DHIyyx S29GL128S10FHIyyx S29GL128S10TFIyyx				
	110	DHV, TFV (Note 1)	V1, V2		S29GL128S11DHVyyxx S29GL128S11TFVyyxx				

- 1. Additional speed, package, and temperature options maybe offered in the future. Check with your local sales representative for availability.
- 2. Package Type 0 is standard option.



The ordering part number for the General Market device is formed by a valid combination of the following:



S29GL01GS, S29GL512S, S29GL256S, S29GL128S
3.0 Volt Core, with V_{IO} Option, 1024, 512, 256, 128 Megabit Page-Mode Flash Memory, Manufactured on 65-nm MirrorBit® Eclipse™ Process Technology



14. Other Resources

Visit www.cypress.com to obtain the below related documents.

14.1 Links to Software

Downloads and related information on flash device support is available at www.cypress.com/Support/Pages/DriversSoftware.aspx

- Cypress low-level drivers
- Enhanced flash drivers
- Flash file system

Downloads and related information on simulation modeling and CAD modeling support is available at

www.cypress.com/Support/Pages/SimulationModels.aspx

- VHDL and Verilog
- IBIS
- ORCAD

14.2 Links to Application Notes

The following is a sample list of application notes related to this product. All application notes are available at

www.cypress.com/spansionappnotes

- Common Flash Interface Version 1.5 Vendor Specific Extensions
- Common Flash Memory Interface Specification
- Connecting Unused Data Lines of MirrorBit Flash
- Developing System-Level Validation Routines
- Flash Memory: An Overview
- Interfacing i.MX3x to S29GL MirrorBit NOR Flash
- Interfacing the S29GL-S to Freescale Coldfire Processor
- Interfacing Cypress GL MirrorBit Family to Freescale i.MX31 Processors
- MirrorBit Flash Memory Write Buffer Programming and Page Buffer Read
- Optimizing Program/Erase Times
- Practical Guide to Endurance and Data Retention
- Programmer's Guide for the Cypress 65-nm GL-S Eclipse Family Architecture
- Reset Voltage and Timing Requirements for MirrorBit Flash
- Signal Integrity and Reliable Flash Operations
- Understanding AC Characteristics
- Understanding Load Capacitance and Access Time
- Understanding Page Mode Flash Memory Devices
- Using CFI to Read and Debug Systems
- Versatile IO: DQ and Enhanced
- Wear Leveling



14.3 Specification Bulletins

Contact your local Cypress sales office for details.

14.4 Contacting Cypress

Obtain the latest list of company locations and contact information on our web site at www.cypress.com/about-us/sales-offices

Document Number: 001-98285 Rev. *J Page 98 of 102



15. Revision History

Document History Page

Document Title: S29GL01GS, S29GL512S, S29GL256S, S29GL128S, 1 Gbit (128 Mbyte), 512 Mbit (64 Mbyte), 256 Mbit (32 Mbyte), 128 Mbit (16 Mbyte), 3.0V GL-S Flash Memory

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	=	BWHA	02/11/2011	Initial release
*A	-	BWHA	03/21/2011	Global: Modified document from "Advance Information" to "Preliminary" OPN: Added FBGA package offering for V1 & V2 Model Number Removed KGD information, which is documented in a separate Supplement Command Definitions Table: Removed duplicated commands Changed the number of command cycles for a CFI Enter from 3 to 1 Physical Interface: Updated 56-pin TSOP pinout figure Updated 64-ball FBGA pinout figure Other Resources: Added additional application notes in "Links to Application Notes" Lock Register Table: Changed the default value of bit 7 in the Lock register
*B	-	BWHA	07/08/2011	Performance Summary: Updated table: Typical Program and Erase Rates Secure Silicon Region ASO: Corrected table: Secure Silicon Region DQ1: Write-to-Buffer Abort: Corrected table: Data Polling Staus Embedded Algorithm Performance Table: Updated table: Embedded Algorithm Characteristics Command State Transitions: Corrected tables: changed Software Reset/ASO Exit Data value to from 00F0h to xF0l Corrected table: Erase Suspend Unlock State Command Transition Corrected table: Erase Suspend - DYB State Command Transition Corrected table: Program Unlock State Command Transition Corrected table: Lock Register State Command Transition Corrected table: Secure Silicon Sector Program State Command Transition Corrected table: Password Protection Command State Transition Corrected table: PPB Lock Bit Command State Transition Corrected table: Volatile Sector Protection Command State Transition

Document Number: 001-98285 Rev. *J Page 99 of 102



Document History Page (Continued)

Document Title: S29GL01GS, S29GL512S, S29GL256S, S29GL128S, 1 Gbit (128 Mbyte), 512 Mbit (64 Mbyte), 256 Mbit (32 Mbyte), 128 Mbit (16 Mbyte), 3.0V GL-S Flash Memory

Document Number: 001-98285					
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change	
*B (cont)	-	BWHA	07/08/2011	Device ID and Common Flash Interface (ID-CFI) ASO Map: Corrected table: Corrected CFI Primary Vendor-Specific Extended Query description for Word Address (SA) + 0045h DC Characteristics: Updated VIL Max Updated Note Power-On Reset (POR) and Warm Reset: Updated table: added row to bottom of table Power-On (Cold) Reset (POR): Updated text Updated figure: Power-Up Diagram Hardware (Warm) Reset: Updated figure: Hardware Reset Asynchronous Write Operations: Added figure: Back to Back (CE#VIL) Write Operation Timing Diagram Updated table: Erase/Program Operations Physical Diagram - LAA064: Added figure	
*C	-	BWHA	10/03/2011	Power-Up Write Inhibit: Minor correction PPB Password Protection Mode: Minor correction Embedded Algorithm Characteristics table: Updated Buffer Programming Time maximum limits Absolute Maximum Ratings table: Added clarification DC Characteristics table: Output High Voltage clarification Power-Up/Power-Down Voltage and Timing table: Added clarification Power-Up figure: Added clarification Power-On (Cold) Reset (POR): Added clarification Valid Combinations table: Updated table	
*D	-	BWHA	12/14/2011	Global: Data sheet designation changed from Preliminary to Full Production Sector Erase: Updated Typical Erase Time Capacitance Characteristics: Updated section Ordering Information: Corrected note designation in valid combination table	
*E	_	BWHA	03/16/2012	Global: Added 9 mm x 7 mm package Added 105°C offering Ordering Information: Updated Valid Combinations	



Document History Page (Continued)

Document Title: S29GL01GS, S29GL512S, S29GL256S, S29GL128S, 1 Gbit (128 Mbyte), 512 Mbit (64 Mbyte), 256 Mbit (32 Mbyte), 128 Mbit (16 Mbyte), 3.0V GL-S Flash Memory Document Number: 001-98285

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
*F	-	BWHA	12/21/2012	Distinctive Characteristics: Added In-Cabin temperature range Status Register ASO: Added clarification Advanced Sector Protection Overview: Updated figure PPB Lock: Added clarification Persistent Protection Bits (PPB): Added clarification Dynamic Protection Bits (DYB): Added clarification PPB Password Protection Mode: Added clarification Chip Erase: Added clarification Sector Erase: Added clarification Sector Erase: Added clarification Erase Suspend / Erase Resume: Added clarification Status Register ASO: Added clarification Status Register Added clarification DQ1: Data# Polling: Added clarification DQ1: Write-to-Buffer Abort: Added clarification Data Polling Status: Updated table Embedded Operation Error: Added clarification Protection Error: Added clarification Write Buffer Abort: Added clarification Performance Table: Updated Embedded Algorithm Characteristics (-40°C to +105°C table Device ID and Common Flash Interface (ID-CFI) ASO Map: Updated CFI Device Geometry Definition table Updated CFI Primary Vendor-Specific Extended Query table Asynchronous Read Operations: Added Read Operation VIO = 1.65 (-40°C to +105°C table Asynchronous Write Operations: Updated Read to Write (CE# VIL) figure Updated Read to Write (CE# Toggle) figure
*G	_	BWHA	10/09/2015	S29GL-S Valid Combinations Table: Added VIO Models for Automotive In Cabin Temperature Range
*H	4871480	BWHA	08/13/2015	Updated to new template.
*	5162387	RYSU	03/04/2016	Updated 13., Ordering Information on page 94: Updated part numbers. Replaced "In Cabin" with "Industrial Plus" in Ordering Code Definitions below Table 13.1 on page 94. Updated to new template.
*J	5428780	NFB	09/07/2016	Updated ASO Entry Timing: Figure 10.16, ASO Entry Timing on page 84 and Table 10.9, ASO Entry Timing on page 84. Updated Copyright and Disclaimer.



Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

cypress.com/usb

cypress.com/wireless

Products

USB Controllers

Wireless/RF

ARM® Cortex® Microcontrollers cypress.com/arm Automotive cypress.com/automotive Clocks & Buffers cypress.com/clocks Interface cypress.com/interface Internet of Things cypress.com/iot Lighting & Power Control cypress.com/powerpsoc Memory cypress.com/memory **PSoC** cypress.com/psoc **Touch Sensing** cypress.com/touch

PSoC® Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP

Cypress Developer Community

Forums | Projects | Video | Blogs | Training | Components

Technical Support

cypress.com/support

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

Document Number: 001-98285 Rev. *J Revised September 7, 2016 Page 102 of 102

[©] Cypress Semiconductor Corporation, 2011-2016. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, for other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.