

 ϵ

Model Number

U-P6-B5

Base for INTERBUS

Features

- · INTERBUS-remote bus subscriber
- · 2 PG screw fittings for IN and OUT 2 EMV PG screw fittings for BUS IN and OUT
- Complete read/write functionality via the INTERBUS
- Transfer of 10 bytes of data in one cycle
- DIP switch for ring termination
- Field device with protection degree **IP67**

Function

The base is used in combination with an upper part, the IPT*-FP read/write station. The device is operated as a slave on the INTERBUS remote bus. The device makes available the complete read/write functionality. Up to 10 bytes are transmitted per cycle. The continuing bus is activated via DIP switch.

Matching system components

IPT-FP

099100 eng.xml

Date of issue: 2011-07-19


Release date: 2011-07-19 12:11

Read/write station


IPT1-FP

Read/write station


Dimensions



Electrical connection



Indicating / Operating means



Technical data

Indicators/operating means

DIP-switch	ring termination 0 = closed 1 = bus continued				
Electrical specifications					
5		~~	001/00		

Rated operational voltage	U_e	20 30 V DC , ripple 10 $\%_{\mbox{\footnotesize SS}}$, PELV
Power consumption	P_0	max. 5 W with read/write head IPT*-FF

Electrical isolation	
Operating voltage/interface	functional insulation acc. to DIN EN 50178, rated insulation voltage 50 $\ensuremath{V_{eff}}$

Interface	
Physical	RS 485
Protocol	INTERBUS remote bus
ID code	03
Transfor rato	500 kRit/s or 2 MRit/s internally switchable

Ambient conditions

Subject to modifications without notice Copyright Pepperl+Fuchs USA: +1 330 486 0001 Germany: +49 621 776-4411 Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Ambient temperature

Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Protection degree	IP67 according to EN 60529 with IPT*-FP
Connection	screw terminals
Interface cable	up to 1.5 mm ²
Supply	up to 3 x 1.5 mm ²
Material	
Housing	aluminum, black anodized

2