

Cleaning agent sprayer EK 1

Low-pressure spraying device

KÄRCHER

Application:

The low-pressure spraying device for efficiently applying cleaning agents over large areas.

Version:

- Max. Fill quantity: 10 l
- Max. Spraying pressure: 6 bar
- Stainless steel container
- With integrated hand pump, ergonomic pump handle and level control
- The spraying device can be filled with compressed air by either manually pumping the pump handle or by connecting a pressure source (max. 6 bar).
- The pressure in the tank is indicated by a manometer. If the pressure in the tank exceeds 6 bar, the excess compressed air can escape via the safety valve
- Pressing the shut-off valve on the handle allows the user to spray cleaning agent, for example.

Advantage:

- The spraying device is also suitable for spraying formwork oils and low-viscosity mineral oils, slightly alkaline construction chemicals (pH value less than 9) and pesticides, including herbicides, in the specified concentrations. In addition, solvent- and chlorine-free, neutral cleaning agents as well as low-viscosity, solvent-free dispersion paints and stains can also be used



Art. no.	75730 093
Max. feed quantity	0.78 l/min
Max. pressure	6 bar
Max. inlet temperature	40 °C
Length x width x height	640 x 285 x 270 mm
Weight	4.7 kg

EAN-Code

4039784533165