Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Schiefer	
--	--

Supplier's address: Schiefer Lighting, Potterbakkerstraat 35, 4871EP Etten-Leur, NL

Model identifier: 643031155

Type of light source	Type	of light	source:
----------------------	------	----------	---------


Lighting technology used:	HL	Non-directional or directional:	NDLS
Light source cap-type	G4		
(or other electric interface)			
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes

Product parameters

Parameter		Value	Parameter	Value
General product parameters:				
<u> </u>	nption in on- 00 h), rounded st integer	10	Energy efficiency class	G
dicating if it refe a sphere (360°)	s flux (фuse), in- ers to the flux in , in a wide cone arrow cone (90º)	80 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 800
On-mode pow pressed in W	ver (P _{on}), ex-	10,0	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00
(P _{net}) for CLS, 6	candby power expressed in W the second dec-	-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	100
Outer dimen-	Height	31	Spectral power dis-	See image
sions without	Width	8	tribution in the	in last page
separate con- trol gear, light- ing control	Depth	8	range 250 nm to 800 nm, at full-load	

parts and non- lighting con- trol parts, if any (millime- tre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,465 0,412

(a)'-': not applicable; (b)'-': not applicable;



Spectral Distribution