

Product Datasheet

Product code: **ES5247.CR.BG**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5247 is a high precision cutter belonging to the oblique head cutter family. The angled blade geometry supports the operator's ergonomics during the cut. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5247 is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Small, Oblique

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.10-1.20 mm (38-17 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:



Dimensions: OAL (A) 128.0 mm – 5.039 inch
 Width 60.0 mm – 2.362 inch
 Height 18.0 mm – 0.709 inch

Head dimensions: Width (C) 10.0 mm – 0.394 inch
 Thickness (D) 6.4 mm – 0.252 inch
 B 18.0 mm – 0.709 inch
 F 0.2 mm – 0.008 inch
 G 8.0 mm – 0.315 inch

