

TECHNICAL DATA SHEET



BASIC Mid S3
No. 16331

Sz. 36-48

LABELLING ACCORDING TO STANDARD

In accordance with EN ISO 20345 S3 SRC

Form B



- Safety boot, mid cut



SLIP RESISTANCE: When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach.

FIT

AREAS OF APPLICATION

- Indoors and outdoors
- Industry, storage, transport, construction etc.
- Areas where exposure to moisture is expected (S2)
- Areas where there is a risk of penetration from pointed and sharp objects (S3)

FEATURES

Design

- Functional design

Full, padded bellows tongue

- Extremely comfortable
- Prevents pressure points
- Prevents penetration of dirt

Collar padding

- Extremely comfortable
- Ankle-wrapping upper edging, softly padded, for good stability and firm support in the shoe (form B)

Reflective material



- Good visibility in the dark

FEATURES

Sizes (unisex model)	<ul style="list-style-type: none"> Expanded size range Available in sizes 36-48
PU toe protection (polyurethane)	<ul style="list-style-type: none"> Directly applied toe protection Excellent wear protection in the toe area Protects the upper leather in this area against premature wear



UPPER MATERIAL

Cowhide leather	<ul style="list-style-type: none"> Areas of application S2/S3 Natural material Wear-resistant Breathable Water penetration/absorption in accordance with EN ISO 20345 S2
-----------------	---

LINING

Climate-regulating textile lining	<ul style="list-style-type: none"> Climate-regulating Good ventilation Skin-friendly High absorption and emission of moisture
-----------------------------------	---

TOE PROTECTION CAP

<p>Steel toe cap</p>  	<ul style="list-style-type: none"> Protection against impacts of min. 200 joules and pressure loading of min. 15 kN Permanent edge coverage for cushioning Ergonomically shaped Comfortable toe-room Good coverage of the little toe area
---	--



INLAY SOLE

Full-length inlay sole	<ul style="list-style-type: none"> Excellent moisture absorption and release providing a comfortable foot climate Exchangeable Sturdy Antistatic
------------------------	--


INSOLE

Antistatic soft-fleece insole	<ul style="list-style-type: none"> Protection against electrostatic discharge (ESD), even when 100% dry, and without the need for additional aids to provide a bridge to the outsole Approx. 50% lighter than comparable soles made of natural materials Flexible and shape-retaining Good air permeability Excellent wear resistance High moisture absorption Quick drying (virtually overnight)
-------------------------------	--

PENETRATION PROTECTION

<p>Steel midsole</p>  	<ul style="list-style-type: none"> ▪ Fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345 ▪ Fulfils the penetration safety standard EN 12568 ▪ Corrosion-resistant ▪ Stainless steel
---	--

OUTSOLE

	<p>Double-density sole with profile</p>	<ul style="list-style-type: none"> ▪ Antistatic ▪ Excellent slip resistance
	<p>Outsole: PU</p>	<ul style="list-style-type: none"> ▪ Colour: black ▪ Particularly abrasion-resistant ▪ Heat-resistant to approx. 130°C, flexible at cold temperatures to approx. -20°C ▪ Oil and fuel resistant
	<p>Midsole: PU</p>	<ul style="list-style-type: none"> ▪ Colour: black ▪ The soft PU core provides a good impact absorption and high comfort