



Part Number : [1300390385](#)

Product Description : Micro-Change Terminator, Female with Resistor, 5 Pole

Series Number : 130039

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : DND150



Documents & Resources

Drawings

[Drawing 1300390385_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000409978_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410292_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	Micro-Change Terminator, Female with Resistor, 5 Pole
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Terminator
UPC	78678830952

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	Polyamide
Material - Contact	Copper Alloy
Material - Coupling Nut	Die-Cast Zinc
Material - Plating Mating	Gold
Net Weight	1.240/g
Orientation	Straight

Poles	5
Temperature Range - Operating	0°C to +60°C
Wire Size (AWG)	N/A

This document was generated on Sep 26, 2023