

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348050112](#)
Status: **Active**
Overview: [CTX Crimp Terminals](#)
Description: CTX150 Female Terminal, Tin (Sn), 18-20 AWG D-Wind, Left Payoff, Grip Code M

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 313025040-000 \(PDF\)](#)
[Product Specification PS-502307-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-502307-001-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [34805](#)
 Application Power, Wire-to-Wire
 Crimp Quality Equipment Yes
 Overview [CTX Crimp Terminals](#)
 Product Name CTX150
 UPC 884982651180

Physical

Durability (mating cycles max) 10
 Gender Female
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Material - Plating Termination Nickel
 Net Weight 0.242/g
 Packaging Type Reel
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.80mm
 Wire Size AWG 18, 20
 Wire Size mm² 0.75-1.00

Electrical

Current - Maximum per Contact 15.0A
 Voltage - Maximum 250V


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-502307-001-001
 Packaging Specification 313025040-000
 Product Specification PS-502307-001-001
 Sales Drawing SD-34805-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34805 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Crimp Hand Tool [638194000](#)

FineAdjust Applicator [639010500](#)