

EF200R5

High flow filter fan

nVent

HOFFMAN

CONNECT AND PROTECT



This vertical filter fan, EF, with a IP 54 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter, and the reliable fan motor will ensure constant ventilation.

CE EAC

IP 54 | TYPE 12

230 V AC, 50/60 Hz

| | |
|--|----------------|
| Bearing type | Sleeve |
| Connection | Terminal strip |
| Current (A) | 0.12/0.18 |
| Noise (dB) | 44 |
| EF+EFA Air flow (m ³ /h) | 44/50 |
| Connection Type | 2 |
| Unimpeded air-flow (m ³ /h) | 61/67 |
| Filter mat (EN779) | G4 |
| Filtration efficiency (%) | >90 |
| Service life L10 (40°C)(h) | 37.500 |
| Cut-out (mm) | 125 x 125 |
| Weight (kg) | 0.80 |
| Power (W) | 19/18 |
| Fuse (A) | 6 |
| Item no. | EF200R5 |

Description: Filter fan for forced ventilation. nVent HOFFMAN filter fans save time on installation as they are installed with a click-in system without screws. The hinged front cover can be easily opened for quick and easy filter replacement. The airflow direction and the connection position can easily be changed.

Material: Front cover manufactured from injection-moulded thermoplastic, self-extinguishing, UL94V0.

Temperature range: -40 °C to +55 °C.

Protection: IP 54 | TYPE 12.

Finish: RAL 7035.

Pack quantity: One fan with filter.