

Twist drill type N HSS, steam-treated

for universal use up to 1000 N/mm²

ORION[®]

Application:

Standard geometry for universal use up to 1000 N/mm².

Execution:

- Twist drill with universal standard geometry

Advantage:

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Steam treatment ensures favourable adherence of coolant



Art. no.	11071 333
Brand	ORION
Manufacturer Part Number	11071333
Cutting material	HSS
Surface	Vaporised
Type	N
Angle of the tip	118 Degree
DIN	345
Tool holding device	Morse taper shank
Cutting edge diameter	30 mm
Chip flute length	175 mm
Length	296 mm
Morse taper size	MK 3
f steel 700	0.37 mm/r
Gross Weight	0.850 kg
Product Group	1AP

EAN

4039247023189