

drilling hand vices

Mechanical clamping system

ORION[®]

Application:


Secure clamping and fixing of workpieces on drills and measuring machines

Execution:

- Basic body made of grey cast iron
- Universal means of attachment thanks to clamping slots and slotted holes
- Fixed clamping jaws with vee blocks
- Both jaws with step for clamping flat workpieces
- Black oxide-coated jaws and spindle

Delivery:

1 pc. Handheld drill vice



Art. no.	28660 063
Brand	ORION
Manufacturer Part Number	28660063
Jaws width	63 mm
Clamping width	65 mm
Jaws height	25 mm
Body length	105 mm
Body width	105 mm
Max. length	125 mm
Height	43 mm
Chip flute width	12.5 mm
Weight	1.35 kg
Gross Weight	1.352 kg
Product Group	282

EAN

4039247171125