

## Torque wrench

DREMOMETER with calibration certificate according to DIN EN ISO 6789



### Application:

The tightening value is set and read from the scale by means of rotary motion with angle key integrated in the handle end.

### Execution:

- Audible and perceptible release when the tightening torque is reached
- Single key, one arm, with automatic release

### Advantage:

- Special design ensures faultless operation
- The measured value or set torque is not changed
- Independent of handle position



<b>Art. no.</b>	<b>52248 060</b>
<b>Brand</b>	GEDORE
<b>Manufacturer Part Number</b>	7695250
<b>Min. torque</b>	750 Nm
<b>Max. torque</b>	2000 Nm
<b>Min./max. torque</b>	750-2000 Nm
<b>Scale value torque</b>	5 Nm
<b>Tip size</b>	1 inch
<b>Error limit (%)</b>	3 %
<b>Min./max. length</b>	932-2008 mm
<b>Calibration certificate</b>	Yes
<b>ISO</b>	6789
<b>Gross Weight</b>	12.900 kg
<b>Product Group</b>	556

### EAN

4002805856413