

Screw tap, HSSE M ISO 2 (6H) 0° 376 B

For use in stainless steels

ATORN®



Application

For producing metric threads on CNC or conventional machines in **through holes** in the stainless steel material group.

Version

- Dimensions to: DIN 371 = reinforced shank (to M10), DIN 376 = protruding shank (from M12)

Advantage

- Long service life and process reliability through innovative cutting geometry in machining stainless steel

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16	12		9	10														

Art. No.	13136 200
Type	M MAX Control
Thread type	Metric thread
Thread type x nominal diameter	M20
Pitch	2.5 mm
Hole type	Clearance hole ≤ 3xD
Cutting material	HSSE
Surface	Vaporised
Lead angle shape	B
Tolerance of screw taps	ISO 2 (6H)
Twist angle	0°
Shaft diameter	16 mm
Application type/machine type	CNC, Conventional
Core hole diameter	17.5 mm
Coolant supply	External
Length	140 mm
Shank square	12 mm
Cutting speed (steel 1000) suitability	2
Cutting speed (steel 1300) suitability	3
Overall stainless steel suitability	1
fitness not iron total	3
fitness Titan/Nickel/Super total	3
Cutting speed (cast) suitability	3
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	376

EAN-Code

4050293040562