

Tilting container with roll-off mechanism—favourable load centre

Carrying capacity 1000 kg, without wheels

Application:

For the collection and disposal of all types of bulk goods and solid materials.

Execution:

- Tilting at any height using a wire rope from the stacker seat
- Sheet metal tray with surrounding edge profile
- Sturdy base frame with fork pockets
- Protection against accidental slipping and tipping
- All dimensions without wheels

Advantage:

- With roll-off mechanism
- Favourable load centre

Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 541
Volume	0.75 m ³
Length	1420 mm
Width	1190 mm
Tipper edge height	1070 mm
Height	1070 mm
Fork pocket clearance	600 mm
Fork pocket size (W x H)	200 x 91 mm
With drain valve	No
With stacker seat tilt function	Yes
With perforated sheet	No
Load-carrying capacity	1000 kg
Surface	Lacquered
Colour	Light blue RAL 5012
Gross Weight	190.000 kg
Product Group	5AI

EAN

4052462019812