

Electrically operated drum pump TecPump 600 AC

Completely ready for use with suction pipe, pressure hose and tap valve



Execution:

- Electrically-operated, self-priming vane pump
- For pumping diesel, heating oil, and concentrated radiator frost protection agent
- Siphon protection/return line, barrel thread G 2"
- Suction filter in the pump chamber
- Integrated overflow valve
- 2-m connection cable, 1.6-m suction hose, 4-m pneumatic hose
- Automatic delivery valve

Art. no.	56345 160
Brand	HORN TECALEMIT
Manufacturer Part Number	105620400
Model	TecPump 600 AC
Max. immersion depth	1600 mm
Feed quantity	55 l/min
Suitable for container	60-200 litres
Gross Weight	12.100 kg
Product Group	575



EAN

4031109012812