

Pneumatic straight grinder SRH 3-85/2

With lever valve



Application:

For fine grinding, milling and engraving work.

Execution:

- Rear air exhaust

Advantage:

- Very light and handy - extremely slim design.

Delivery:

incl. collet chuck ZG 5/3 mm, collet chuck key size 6 + 8 and hose unit; in box



Art. no.	75036 025
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150001065
Model	SRH 3-85/2
Valve design	Lever valve
Max. idle speed	85000 rpm
Power output	80 W
Air consumption	170 l/min
Connection thread	M6
Inner hose diameter	4.5 mm
Length	180 mm
Diameter of housing	19.5 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	6 mm
Max. HM rotating milling cutter diameter	4 mm
Weight	0.17 kg
Gross Weight	0.900 kg
Product Group	748