

PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Armoured shutter lock
Catalogue number	175
Date	17/01/2008

Range Description

Steel armoured brass shutter lock

Features

- Hardened steel shackle – extra protection against hacksaw and cropping attacks
- Ball bearing locking mechanism – extra strength to resist torsion and pull attacks
- Solid brass body encased in a hardened steel jacket for extra strength and resistance to corrosion
- 5 pin cylinder with anti pick mushroom pins – extra protection from lock picking
- Paracentric keyway – extra protection from manipulation
- Drill resistant keyway – protects the cylinder from drill attack
- Weather rating: 2

These padlocks are supplied display packed in sealed blisters or individually boxed

2 keys are supplied with each padlock



Item Number	Item Description	EAN No	Commodity code	Carton Qty
K17580D	Armoured shutter lock 80mm Display packed	5013969901122	83011000	6
K17580	Armoured shutter lock 80mm Boxed	5013969902556	83011000	6
K17080A1	Armoured shutter lock 80mm KA - Boxed	5013969901375	83011000	6

<p>Technical product information</p>	<p>Body – Solid brass with hardened steel armour casing, Chrome plated</p> <p>Shackle- Hardened alloy steel, Chrome plated</p> <p>Locking mechanism- Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Driver pin 5 is plain, driver pins 1 to 4 are mushroom type. The cylinder is protected from drill attack with an anti drill plate</p> <p>Key differs- 1988</p> <p>Re-keyable – No</p> <p>Security rating:</p> <table border="1" data-bbox="488 661 878 835"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K17580D</td> <td>11</td> </tr> <tr> <td>K17580</td> <td>11</td> </tr> <tr> <td>K17580A1</td> <td>11</td> </tr> </tbody> </table> <p>Shackle Dimensions:</p> <table border="1" data-bbox="488 947 1216 1173"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> <th>Body</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> <th>Width</th> </tr> </thead> <tbody> <tr> <td>K17580D</td> <td>12</td> <td>37</td> <td>17</td> <td>30</td> </tr> <tr> <td>K17580</td> <td>12</td> <td>37</td> <td>17</td> <td>30</td> </tr> <tr> <td>K17580A1</td> <td>12</td> <td>37</td> <td>17</td> <td>30</td> </tr> </tbody> </table> <p>Use environment- Normal outdoor use</p> <p>Recommended applications- Specifically designed for shutters, grilles and use with chain, the shutter lock is increasingly used for a wide range of applications in industrial and commercial premises.</p>	Item	Security rating	K17580D	11	K17580	11	K17580A1	11	Dimensions mm	Shackle			Body	Dia	Internal width	Internal height	Width	K17580D	12	37	17	30	K17580	12	37	17	30	K17580A1	12	37	17	30
Item	Security rating																																
K17580D	11																																
K17580	11																																
K17580A1	11																																
Dimensions mm	Shackle			Body																													
	Dia	Internal width	Internal height	Width																													
K17580D	12	37	17	30																													
K17580	12	37	17	30																													
K17580A1	12	37	17	30																													
Standards compliance	None applicable																																
User health and safety information	None applicable																																
RoHS/WEEE compliance	This product does not fall within the scope of RoHS or WEEE regulations																																
Material safety data	None applicable																																
Warranty	<p>KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years</p> <p>Damage caused through inappropriate use or attempted break in is not covered</p>																																
Country of origin	China																																

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K17580D	78	30	65	810	140	35	170	857
K17580	78	30	65	810	80	32	67	820
K17580A1	78	30	65	810	80	32	67	820

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K17580D	145	210	125	5254		
K17580	90	145	105	4982		
K17580A1	90	145	105	4982		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K17580D	37	Blister	10	Backing card			112	Box
K17580			10	Box			62	Box
K17580A1			10	Box			62	Box