Resistors MELF Resistors

WRM Series

- AEC-Q200
- High reliability
- Predictable pulse handling capability
- Tolerances down to 0.1%
- TCR down to 5 ppm/°C





All parts are Pb-free and comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

	WRM 0102	WRM 0204	WRM 0207		
Power rating @70°C watts	0.2	0.2 0.25 0.4			
Resistance Range ohms	8R2-1M0	R22-5M1	R22- 10M		
Limiting element voltage volts	200	200	250		
TCR ppm/°C	15, 25, 50, 100	15, 25, 50, 100 5, 10, 15, 25, 50, 100 15, 25, 50, 10			
Resistance tolerance %	0.1, 0.25, 0.5, 1, 5				
Standard values		E24 & E96			
Thermal impedance k/W	250	250 200 140			
Ambient temperature range °C	-55 to +155	-55 to +155 -55 to +125			
Insulation resistance ohms	>1010				
Zero ohm jumper current rating amps	2 4				
Zero ohm jumper maximum residual resistance mΩ	15				

Physical Data

Dimensions (mm) & weight (g)							
Туре	L max	D max	D ¹ max	K min	L ¹ min	Weight	
WRM 0102	2.3	1.35	1.3	0.3	1.1	0.01	++ D
WRM 0204	3.7	1.55	1.55	0.5	1.5	0.02	
WRM 0207	6.1	2.4	2.4	0.5	2.9	0.08	

Construction

A metal film is deposited onto a high dissipation ceramic former to which tin plated teminating caps are fitted.

The resistor is adjusted to value by a helical cut in the film and the body is protected by a lacquer coating.

Marking

Resistance values are colour coded with four bands, three indicating value and one indicating the multiplier. (Note this describes standard marking, but certain values may still be supplied with the addition of a tolerance band following the multiplier.).

Terminations

Material Solderability Plated steel cap.

The pure tin finish produces ageing free contacts on which low melting solders can be used. Dipped area shall be covered with a smooth and bright solder coating after 3 seconds immersion at 215°C.

Solvent Resistance

The body protection and marking are resistant to all normal industrial cleaning solvents suitable for printed circuit boards.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

www.ttelectronics.com/resistors



TCR and Tolerance Range

Type Reference	TCR	TCR Tolerance				
		5%	1.0%	0.5%	0.25%	0.1%
	±100ppm	10R- 1M0	10R- 1M0	-	-	-
WRM0102	±50ppm	10R- 1M0	10R- 1M0	8R2-1M0	-	-
WRIVIO102	±25ppm	-	100R- 82K	100R- 100K	100R- 82K	100R- 82K
	±15ppm	-	100R- 56K	100R- 56K	100R- 56K	100R- 56K
	±100ppm	R22- R91	-	-	-	-
	±50ppm	-	1R- 5M1	10R- 1M6	22R- 332K	43R- 332K
WRM0204	±25ppm	-	4R7- 500K	10R- 500K	22R- 402K	43R- 332K
WRIVIO204	±15ppm	-	-	10R- 221K	22R- 221K	43R- 221K
	±10ppm	-	-	-	22R- 221K	43R- 221K
	±05ppm	-	-	-	100R- 100K	100R- 100K
WRM0207	±100ppm	R22- R91	-	-	-	-
	±50ppm	-	1R- 10M	10R-1M6	-	-
	±25ppm	-	10R- 1M	10R- 680K	51R1-330K	100R- 100K
	±15ppm	-	-	51R1-10K	51R1-10K	100R- 10K

* TC 10ppm & 5ppm is specified over the temperature range-10°C to +85°C.

Performance Data

		ΔR/R					
Test			0102				
		75R - 100K	10R - <75R & >100K - 332K	<10R & >332K	All values		
Short time overload*		≤0.05% + 0.01Ω	≤0.1% + 0.01Ω	≤0.25% + 0.05Ω	≤0.25% + 0.05Ω		
Bending test*		≤0.05% + 0.01Ω	≤0.1% + 0.01Ω	≤0.25% + 0.05Ω	≤0.25% + 0.05Ω		
Resistance to soldering heat	:	≤0.05% + 0.01Ω	≤0.1% + 0.01Ω	≤0.25% + 0.05Ω	≤0.25% + 0.05Ω		
Temperature rapid change		≤0.05% + 0.01Ω	≤0.1% + 0.01Ω	≤0.25% + 0.05Ω	≤0.25% + 0.05Ω		
Endurance*							
Load life	1000h	≤0.15% + 0.05Ω	≤0.15% + 0.05Ω	≤0.3% + 0.05Ω	≤0.5% + 0.05Ω		
	8000h	≤0.3% + 0.05Ω	≤0.3% + 0.05Ω	≤0.6% + 0.05Ω	≤1.0% + 0.05Ω		
	225,000h	≤0.9% + 0.05Ω	≤0.9% + 0.05Ω	≤1.8% + 0.05Ω	≤3.0% + 0.05Ω		
Climatic sequence*		≤0.25% + 0.05Ω	≤0.5% + 0.05Ω	≤1.0% + 0.05Ω	≤1.0% + 0.05Ω		
Damp heat steady state*		≤0.25% + 0.05Ω	≤0.5% + 0.05Ω	≤1.0% + 0.05Ω	≤1.0% + 0.05Ω		
Current noise		<0.05µV/V	<0.25µV/V	<3µV/V	<3µV/V		
Solderability		>95% coverage					
Voltage coefficient		0 to-0.5ppm/V					
Voltage proof		No flashover or breakdown					

* Resistors to be mounted on a PC-board according to IEC 115-1, clause 4.27.1.

* AEC-Q200 approval applies to all values up to and including 3M4 at TCRs above 5ppm/°C and to zero ohm jumpers.

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

MELF Resistors




WRM Series

Single Pulse



Continuous Pulses



Packaging

The WRM 0102 and 0204 resistors are supplied reeled on 8mm blister tape. WRM 0207 resistors are supplied on 12mm blister tape. Packaging complies with the requirements of IEC 286-3.

Ordering Procedure

Example: WRM0204C-1K0FI (WRM0204, 50ppm/°C, 1 kilohm ±1%, Pb-free) **Example: WRM0204-R000I** (WRM0204, zero ohm jumper, Pb-free)

W R M 0 2	04C-	1 K 0	F 1
1	2	3	4 5

1	2	3	4		5
Туре	TCR	Value	Tolerance	Packing	
WRM0102	V = ±5ppm/°C	3/4 characters	B = ±0.1%	I = Standard	
WRM0204	T = ±10ppm/°C	R = ohms	C = ±0.25%	0102	3000 / 7" reel
WRM0207	Y = ±15ppm/°C	K = kilohms	D = ±0.5%	0204	3000 / 7" reel ¹
	D = ±25ppm/°C	M = megohms	F = ±1%	0207	1500 / 7" reel
	C = ±50ppm/°C	R000 = Jumper	J = ±5%		
	Z = ±100ppm/°C		Omit for Jumper		
	Omit for Jumper				

Note 1: High precision parts may be supplied on 1000 piece reels - please enquire

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

www.ttelectronics.com/resistors