


## Data Sheet



**Type Number** ..... 6237  
**Designation IEC** ..... ---  
**System** ..... Li-Manganese dioxide / Organic Electrolyte

**UL Recognition:**..... MH 13654 (N)  
**Nominal Voltage** ..... 3 V  
**Typical Capacity C** ..... 1350 mAh  
 Load 1.0 kOhm, at 20°C down to 2.0 V

**Weight (approx.)** ..... 15 g  
**Volume** ..... 5,6 ccm  
**Coding**..... Date of Manufacturing Quarter / Year

**Temperature Ranges**

	min	max.
Storage .....	-55°C	75 °C
Discharge .....	-30°C	75°C

**Dimensions**

	min	max.
Diameter (A) .....	14,45	14,75
Height (B) .....	33,1	33,5
Shoulder Diameter[L].....	7	
Shoulder Height [M].....	0,6	

**Segment** ..... Electronic

**Main Applications** ..... Electronic

### Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w	1000 Ω	Time:	500 h
		Capacity [mAh]:	1350
		Energy [MWh]:	3600