

Ring bolt incl. Key

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

Delivery:

Includes Key



Art. no.	77232 230
Brand	CARTEC
Manufacturer Part Number	C807XCHT30
Design	With key
Thread dimension	M30
Load-carrying capacity	4.5 t
Distance between lower edge of retainer holder and retainer	86 mm
Bracket width	28 mm
Bracket height	25.5 mm
Outer diameter	111 mm
Diameter 2	75 mm
Internal width	60 mm
Width of support plate	66 mm
Usable thread length	45 mm
Width across flats	17 mm
Weight	2 kg
Gross Weight	2.142 kg
Product Group	775

EAN

8013429916878