

1

**Pushbutton opaque, mounting hole diameter 9.1 mm, non-illuminated, 24 V/100 mA**



**Technical data**

**General information**

Form of lens	protruding lens
Colour of lens	see order block
Form of collar	round

**Dimensions**

Diameter of collar	11 mm
Overall height	4.5 mm
Mounting depth	25.5 mm
Mounting hole	9.1 mm

**Mechanical design**

Mounting	ring nut
Terminals	solder terminals
Contact system	bridge contact
Contact function	momentary
Contact arrangement	1 NO
Contact materials	Ag
Illuminability	no
Lamp socket	no

**Mechanical characteristics**

Operating force max.	7 N
Operating travel	2 mm
Switching travel NO	1.3 mm
Robustness min.	100 N

**Electrical characteristics**

Rated voltage AC max.	24 V
Rated voltage DC max.	24 V
Rated current max.	0.1 A
Contact resistance max.	200 mΩ

**Other specifications**


Operating life	40000
Degree of protection from front side	IP40
Ambient temp. operating min.	-25 °C
Ambient temp. operating max.	+70 °C
Storage temperature min.	-40 °C
Storage temperature max.	+80 °C
Resistance to constant environment	according to IEC 600 68-2-3 and 2-30
Resistance at variable environment	according to IEC 600 68-2-14 and 2-33
Weight	2 g
Soldering time max.	3 sec.
Soldering temperature max.	350 °C

Other Pushb.

**Accessories Pushbutton opaque, mounting hole diameter 9.1 mm, non-illuminated, 24 V/100 mA**

Description	Photo	Order no.	Page
Fixing spanner M 9, M 10		<b>5.58.002.025/0105</b>	5 - 23

## Pushbutton opaque, mounting hole diameter 9.1 mm, non-illuminated, 24 V/0.1 A



Contact arrangement	Contact function	Illuminability	Rated voltage DC max.	Colour of lens	Order no.
1 NO	momentary	no	24 V	opaque black	<b>1.10.107.011/0104</b>
1 NO	momentary	no	24 V	opaque white	<b>1.10.107.011/0205</b>
1 NO	momentary	no	24 V	opaque red	<b>1.10.107.011/0301</b>
1 NO	momentary	no	24 V	opaque yellow	1.10.107.011/0404
1 NO	momentary	no	24 V	opaque green	<b>1.10.107.011/0507</b>

Technical data see page 1 - 74

1

Other  
Pushb.