

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : V-cut MP  
UFI : DGA0-M0VW-C00R-3132

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use, Industrial use  
Industrial/Professional use spec : For professional use only  
Industrial

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Manufacturer

ROCOL a division of ITW Ltd  
Rocol House  
Wakefield Rd, Swillington  
LS26 8BS Leeds - United Kingdom  
T +44 (0)113 232 2600  
[customer.service@rocol.com](mailto:customer.service@rocol.com) - [www.rocol.com](http://www.rocol.com)

#### 1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315  
Serious eye damage/eye irritation, Category 1 H318  
Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412  
Full text of H statements : see section 16

##### Adverse physicochemical, human health and environmental effects

No additional information available

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS05

Signal word (CLP) : Danger

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains	: ALKOXYAMINE
Hazard statements (CLP)	: H315 - Causes skin irritation. H318 - Causes serious eye damage. H412 - Harmful to aquatic life with long lasting effects.
Precautionary statements (CLP)	: P264 - Wash hands thoroughly after handling. P280 - Wear protective gloves, protective clothing, eye protection, face protection. P302+P352 - IF ON SKIN: Wash with plenty of water. P305+P351+P338+P310 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor.

### 2.3. Other hazards

No additional information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALKOXYAMINE	(CAS-No.) 111-42-2 (EC-No.) 203-868-0 (REACH-no) 01-2119488930-28	5 – 10	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 STOT RE 2, H373
ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED	(CAS-No.) 68920-66-1 (EC-No.) 500-236-9 (REACH-no) 01-2119489407-26	5 – 10	Skin Irrit. 2, H315 Aquatic Acute 1, H400 Aquatic Chronic 3, H412
ALKENYL ALKANOL AMIDE	(CAS-No.) 68603-38-3 (EC-No.) 271-653-9 (REACH-no) 01-2119951823-33	2.4 – 5	Skin Irrit. 2, H315 Eye Irrit. 2, H319 Aquatic Chronic 2, H411
SODIUM PYRITHIONE	(CAS-No.) 3811-73-2 (EC-No.) 223-296-5	0.1 – 1	Acute Tox. 4 (Oral), H302 Acute Tox. 3 (Dermal), H311 Acute Tox. 4 (Inhalation), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Aquatic Acute 1, H400 (M=100) Aquatic Chronic 1, H410 (M=10)

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Wash contaminated clothing before reuse. Get medical advice/attention. Specific treatment (see supplemental first aid instruction on this label).
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact : Causes skin irritation.  
Symptoms/effects after eye contact : Causes serious eye damage.

### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.  
Unsuitable extinguishing media : Do not use a heavy water stream.

### 5.2. Special hazards arising from the substance or mixture

No additional information available

### 5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.  
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

#### 6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.  
Emergency procedures : Ventilate area.

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters. Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.  
Collect spillage. Store away from other materials.

### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.  
Hygiene measures : Wash hands, forearms and face thoroughly after handling.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.  
Incompatible products : Strong bases. Strong acids.  
Incompatible materials : Sources of ignition. Direct sunlight.

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1 National occupational exposure and biological limit values

No additional information available

#### 8.1.2. Recommended monitoring procedures

No additional information available

#### 8.1.3. Air contaminants formed

No additional information available

#### 8.1.4. DNEL and PNEC

No additional information available

#### 8.1.5. Control banding

No additional information available

### 8.2. Exposure controls

#### 8.2.1. Appropriate engineering controls

No additional information available

#### 8.2.2. Personal protection equipment

##### Personal protective equipment:

Avoid all unnecessary exposure.

##### 8.2.2.1. Eye and face protection

###### Eye protection:

Chemical goggles or safety glasses

##### 8.2.2.2. Skin protection

###### Skin and body protection:

Wear suitable protective clothing

###### Hand protection:

Wear protective gloves.

##### 8.2.2.3. Respiratory protection

###### Respiratory protection:

Wear appropriate mask

##### 8.2.2.4. Thermal hazards

No additional information available

### 8.2.3. Environmental exposure controls

##### Other information:

Do not eat, drink or smoke during use.

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Yellow.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: 9 (≥ 10) No data available.
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available.
Freezing point	: No data available
Boiling point	: 100 °C
Flash point	: > 100 °C
Auto-ignition temperature	: > 200
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available.
Relative density	: 0,95
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

#### 9.2. Other information

No additional information available

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

No additional information available

#### 10.2. Chemical stability

Not established.

#### 10.3. Possibility of hazardous reactions

Not established.

#### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

#### 10.5. Incompatible materials

Strong acids. Strong bases.

#### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

### SECTION 11: Toxicological information

#### 11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)

LD50 oral rat	> 2000 mg/kg
---------------	--------------

### ALKENYL ALKANOL AMIDE (68603-38-3)

LD50 oral rat	> 3000 mg/kg
---------------	--------------

LD50 dermal	> 2000 mg/kg
-------------	--------------

Skin corrosion/irritation : Causes skin irritation.  
pH: 9 ( $\geq$  10) No data available.

Serious eye damage/irritation : Causes serious eye damage.  
pH: 9 ( $\geq$  10) No data available.

Respiratory or skin sensitisation : Not classified

Additional information : Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

### ALKOXYAMINE (111-42-2)

NOAEL (chronic, oral, animal/male, 2 years)	64 mg/kg bodyweight Animal: rat, Animal sex: male, Guideline: OECD Guideline 451 (Carcinogenicity Studies), Remarks on results: other:Effect type: carcinogenicity (migrated information)
---	---

Reproductive toxicity : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-repeated exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

### ALKOXYAMINE (111-42-2)

LOAEL (dermal, rat/rabbit, 90 days)	32 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 411 (Subchronic Dermal Toxicity: 90-Day Study)
-------------------------------------	---

NOAEC (inhalation, rat, dust/mist/fume, 90 days)	0.003 mg/l air Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study)
--	--

STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.
------------------------	--

Aspiration hazard : Not classified

Additional information : Based on available data, the classification criteria are not met

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - water : Toxic to aquatic life with long lasting effects.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)

LC50 - Fish [1]	10 – 100 mg/l
-----------------	---------------

### ALKOXYAMINE (111-42-2)

EC50 - Crustacea [1]	30.1 mg/l Test organisms (species): Ceriodaphnia dubia
EC50 - Crustacea [2]	89.9 mg/l Test organisms (species): Ceriodaphnia dubia
EC50 72h - Algae [1]	9.5 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 72h - Algae [2]	2.7 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 96h - Algae [1]	9.7 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 96h - Algae [2]	2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
LOEC (chronic)	1.56 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC (chronic)	0.78 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC chronic fish	> 1 mg/l Test organisms (species): other: freshwater fish

### ALKENYL ALKANOL AMIDE (68603-38-3)

LC50 - Fish [1]	1460 mg/l
EC50 - Other aquatic organisms [1]	55 mg/l

## 12.2. Persistence and degradability

### V-cut MP

Persistence and degradability	May cause long-term adverse effects in the environment.
-------------------------------	---

## 12.3. Bioaccumulative potential

### V-cut MP

Bioaccumulative potential	Not established.
---------------------------	------------------

## 12.4. Mobility in soil

No additional information available

## 12.5. Results of PBT and vPvB assessment

No additional information available

## 12.6. Other adverse effects

Additional information : Avoid release to the environment.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Ecology - waste materials : Avoid release to the environment.

# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.2. UN proper shipping name</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.4. Packing group</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.5. Environmental hazards</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

### 14.6. Special precautions for user

#### Overland transport

Not regulated

#### Transport by sea

Not regulated

#### Air transport

Not regulated

#### Inland waterway transport

Not regulated

#### Rail transport

Not regulated

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

##### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

##### 15.1.2. National regulations

No additional information available

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out



# V-cut MP

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:	
Acute Tox. 3 (Dermal)	Acute toxicity (dermal), Category 3
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
H302	Harmful if swallowed.
H311	Toxic in contact with skin.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.