

# **GLOBAL CONNECTIVITY SOLUTIONS**

2

SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft

# LCCA30004-FT10

#### Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Male Right Angle
- Cable Type: 402SS Series

#### **Features**

- Max Frequency 18 GHz
- Shielding Effectivity > 110dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket

#### Applications

- General Purpose
- Laboratory Use

- Wire Braid over Spiral Strip Shield
- Flexible Alternative to .141 Semi-Rigid
- Heavy Duty Heat Shrink Strain Relief Boot
- Precision Stainless Steel Connectors
- Flexible RF Interconnect
- Automated (ATE) Test Systems



#### Description

1

L-com's Cable Assembly LCCA30004 is an SMA male right angle to SMA male right angle, 10.0 ft cable using 402SS Series coax with Heavy Duty Boot that ships same-day. L-com's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This L-com SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible 402SS Series coax and operates to 18 GHz. The right angle SMA interface on the 402SS Series cable allows for easier connections in tight spaces. Highly durable stainless-steel connectors and heavy-duty booting extend the life of this versatile flexible cable assembly. The double shield includes a silver plated copper braid over a silver plated copper spiral strip providing excellent shielding effectiveness greater than 110dB.

Custom versions of this cable assembly along with the rest of L-com's RF cable assemblies can be built and shipped same day. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for custom cable quotes.



SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft



# LCCA30004-FT10

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
RF Shielding	110			dB
Capacitance		29.4 [96.46]		pF/ft [pF/m]

# **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	3	5	10	18		GHz
Insertion Loss (Max.)	2.474	3.224	4.817	6.825		dB

**Electrical Specification Notes:** 

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as 0.07\*SQRT(FGHz) dB per connector.

## **Mechanical Specifications**

<b>Cable Assembly</b> Length Diameter	120 in [304.8 cm] 0.315 in [8 mm]
Weight	0.3 lbs [136.08 g]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter	402SS Series 50 Ohms Stranded Copper, Silver PTFE 2 Silver Plated Copper Tape Silver Plated Copper Braid FEP, Tan 0.163 in [4.14 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]



SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft



# LCCA30004-FT10

# Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male Right Angle	SMA Male Right Angle	
Specification	MIL-STD-348A	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification	50 µin minimum	50 µin minimum	
Dielectric Type	PTFE	PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100 µin minimum	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum	
Hex Size	5/16 inch	5/16 inch	
Torque	12 in-lbs [1.36 Nm]	12 in-lbs [1.36 Nm]	
Boot Material	Heavy Duty Heat Shrink Boot	Heavy Duty Heat Shrink Boot	

## **Environmental Specifications**

Temperature Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

- Notes:
- Values at 25°C, sea level.




SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft

# LCCA30004-FT10

#### How to Order

Example:




LCCA30004-100cm = 100 cm long cable

SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

SMA Male Right Angle to SMA Male Right Angle Cable Using 402SS Series Coax with Heavy Duty Boot, 10.0 ft

### L-com CAD Drawing



LCCA30004-FT10 REV 1.0 | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.