


RoHS Compliant




1. Ratings:

Туре	4 Elements, 1206
Power Rating	0.0625W (1/16W)
Rated Current (Jumper)	1A
Max. Working Voltage	50 V
Max. Overload Voltage	100 V
Dielectric Withstanding Voltage	300 V
Temperature Range	-55°C to +155°C
Ambient Temperature	70°C


1.1 Power rating:

Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70° C. For temperature in excess of 70° C, The load shall be derate as shown in figure 1.




multicomp PRO


2. Construction



3. Power rating and dimensions

Equivalent Circuit Diagram





Dimension

			Dimension (mm)			
L	W	Н	£ 1	l 2	Р	Q
3.2 ±0.2	1.6 ±0.2	0.5 ±0.1	0.3±0.15	0.3 ±0.15	0.8 ±0.1	0.5 ±0.15

Power Rating

Power Rating at 70°C	Tolerance %	Resistance Range	T.C.R. PPM/°C	Standard Resistance values
0.0625W(1/16W)	Jumper ±5	$< 50 \text{m}\Omega \ 10\Omega \ \text{to} \ 1 \text{M}\Omega$	<10Ω:±400 ≥10Ω:±200	E-24

4. Marking:

4.1 Resistors

A. Marking for E-26 series in 1206 size: 4 Digits

*The first 3 digits are significant figures of resistance and the 4th digit denoted number of zeros.

Εχ. 1003 100ΚΩ





*For ohmic values below 100 Ω , letter "R" is for decimal point.

Ex.	1R80	1.8Ω

B. Marking for E-24 series in 1206 size: 3 Digits

*The first 2 digits are significant figures of resistance and the 3rd digit denoted number of zeros.



*For ohmic values below 100 Ω , letter "R" is for decimal point.



5. Performance specification

Characteristics	Limits	Test Methods (JIS C 5201-1)
Temperature Coefficient	Refer to item 5.	5.2 Natural resistance change per temp. degree centigrade. R2-R1 x 10 ⁶ (PPM/°C) R1(t2-t1)
		R1: Resistance value at room temperature (T1) R2: Resistance value at room temp. plus 100°c (T2) (Sub-clause 4.8)
Short time overload	Resistance change rate is ± 5% (2% + 0.1Ω) Max. ± 1% (1% + 0.1Ω) Max.	5.5 Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Insulation resistance	1,000 MΩ or more	5.6 Apply 500V DC between protective coating and termination for 1 min, then measure
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	4.7 Clamped in the trough of a 90° metallic V-block and shall be tested at AC potential respectively specified in the table 1. for 60 +10/-0 secs.
Terminal bending	Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max.	6.1.4 Twist of Test Board Y/X = 5/90 mm for 10 seconds





Characteristics	Limits	Test Methods (JIS C 5201-1)		
Solderability	95 % coverage Min.	6.5 Test temperature of solder : 245 ± 3°C Dipping them solder : 2~3 seconds		
	Go up tin rate bigger than half of end pole.	Reflow: (°C) 250 Peak: 260 °C (Max) 235 °C ~ 255 °C Pre Heating Zone 150 150 °C 90 ~ 120 sec Soldering Zone Heating time Max Soldering Time: 2 times Temperature profile for evaluation		
Soldering heat	Resistance change rate is: $\pm (1\%+0.05\Omega)$ Max.	4.18 Dip the resistor into a solder bath having a temperature of 260°C±3°C and hold it for 10±1 seconds.		
		7.4 Resistance change after continuous 5 cycles for duty cycle specified below :		
		Step Temperature	Time	
	Resistance change rate is	1 -55°C ±3°C	30 mins	
Temperature cycling	\pm 5% (1.0% + 0.05Ω) Max. \pm 1% (0.5% + 0.05Ω) Max.	2 Room temp.	10 to 15 mins	
	2 1 70 (0.070 · 0.0032) Wax.	3 +155°C ±2°C	30 mins	
		4 Room temp.	10 to 15 mins	
Load life in humidity	Resistance change rate is $\pm 5\% (3\% + 0.1\Omega)$ Max. $\pm 1\% (1\% + 0.1\Omega)$ Max.	7.9 Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity chamber controlled at 40°C ±2°C and 90 to 95 % relative humidity		
Load Life	Resistance change rate is $\pm 5\% (3.0\% + 0.1\Omega)$ Max. $\pm 1\% (1.0\% + 0.1\Omega)$ Max.	7.10 Permanent resistance change after 1,000 hours operating at RCWV, with duty cycle of (1.5 hours"on", 0.5 hour"off") at 70°C ± 2°C ambient		





Part Number Table

Description	Part Number
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 0R, 1206	MP005619
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 1.2K, 1206	MP005620
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 1.5K, 1206	MP005621
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 1.8K, 1206	MP005622
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 100K, 1206	MP005623
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 100R, 1206	MP005624
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 10K, 1206	MP005625
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 10R, 1206	MP005626
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 120K, 1206	MP005627
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 120R, 1206	MP005628
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 12K, 1206	MP005629
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 150K, 1206	MP005630
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 150R, 1206	MP005631
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 15K, 1206	MP005632
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 15R, 1206	MP005633
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 180K, 1206	MP005634
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 180R, 1206	MP005635
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 18K, 1206	MP005636
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 1K, 1206	MP005637
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 1M, 1206	MP005638
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 2.2K, 1206	MP005639
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 2.4K, 1206	MP005640
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 2.7K, 1206	MP005641
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 20K, 1206	MP005642
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 220K, 1206	MP005643
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 220R, 1206	MP005644
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 22K, 1206	MP005645
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 22R, 1206	MP005646
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 270R, 1206	MP005647
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 27K, 1206	MP005648
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 27R, 1206	MP005649
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 2K, 1206	MP005650
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 3.3K, 1206	MP005651
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 3.9K, 1206	MP005652
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 300K, 1206	MP005653
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 300R, 1206	MP005654
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 330R, 1206	MP005655





Description	Part Number
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 33K, 1206	MP005656
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 33R, 1206	MP005657
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 390R, 1206	MP005658
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 39K, 1206	MP005659
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 39R, 1206	MP005660
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 3K, 1206	MP005661
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 4.7K, 1206	MP005662
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 4.7R, 1206	MP005663
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 430R, 1206	MP005664
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 470K, 1206	MP005665
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 470R, 1206	MP005666
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 47K, 1206	MP005667
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 47R, 1206	MP005668
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 5.1K, 1206	MP005669
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 5.6K, 1206	MP005670
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 510R, 1206	MP005671
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 51R, 1206	MP005672
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 560K, 1206	MP005673
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 560R, 1206	MP005674
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 56K, 1206	MP005675
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 56R, 1206	MP005676
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 6.8K, 1206	MP005677
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 680R, 1206	MP005678
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 68K, 1206	MP005679
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 68R, 1206	MP005680
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 75R, 1206	MP005681
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 8.2K, 1206	MP005682
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 820R, 1206	MP005683
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 82K, 1206	MP005684
Chip Resistor Array, Thick Film, Isolated 4 Elements, 1/16W, 5%, 82R, 1206	MP005685

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

