

SDUC steel boring bar set, offset, positive right

for longitudinal and copy turning using DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC 55° indexable insert.

Version

- precision-manufactured **steel** boring bar set, offset, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. no.	17847 100
ISO name	SDUC R07
Material	Steel
Composition of set	1 piece each 17847 210-214 (A0810J, A1012K, A1216M)
Number of pieces in assortment/set	3 PCS
Suitable for indexable inserts	DC.. 0702..
Machining direction	Right
DIN	8024

EAN-Code

4050293110173