


VAL-U-LOK

TE Internal #: 2-2296207-0

Rectangular Connector Housings, Wire-to-Panel / Wire-to-Wire,
15Newton Insertion Force, 20 Position, 4.2mm [.165in] Centerline[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Connector Housings

Connector System: **Wire-to-Panel, Wire-to-Wire**Insertion Force: **15 Newton**Number of Positions: **20**Centerline (Pitch): **4.2 mm [.165 in]**Row-to-Row Spacing: **4.2 mm [.165 in]****Features****Product Type Features**

Connector System	Wire-to-Panel, Wire-to-Wire
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Insertion Force	15 Newton
Number of Positions	20
Number of Rows	2

Contact Features

Contact Type	Socket
--------------	--------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging), Panel Mount
-------------------------	---

Housing Features

Centerline (Pitch)	4.2 mm [.165 in]
Housing Material	Nylon

Dimensions

Row-to-Row Spacing	4.2 mm [.165 in]
--------------------	------------------

Usage Conditions



Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 2-2029265-0 20P VAL-U-LOK VRTHDR W/PGS GW</p>	 <p>TE Part # 2-1586765-0 20P RCPT VAL-U-LOK GW</p>	 <p>TE Part # 2-2029059-0 20P VAL-U-LOK VRTHDR W/PGS GW</p>	 <p>TE Part # 2-2296205-0 20P RCPT VAL-U-LOK GWT/V0</p>
--	--	--	--



Customers Also Bought



Documents

Product Drawings

[20P PM PLUG VAL-U-LOK PM GWT/V0](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_2-2296207-0_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_2-2296207-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2296207-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English