
Metal Film Fixed Resistors 0.6W, 200 PPM

multicomp PRO



Scope:

This specification for approval relates to Metal Film Fixed Resistors.

Ratings:

Туре	MF	
Rated Power	0.6W at 70°C	
Max. Working Voltage	250V	
Max. Overload Voltage	500V	
Dielectric Withstanding Voltage	500V	
Rated Ambient Temp.	70°C	
Operating Temp. Range	-55°C to +155°C	
Resistance Tolerance	± 1%	
Resistance Range	1Ω to 3.3Ω	

Table. 1

Power Rating:

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70°C. For temperature in excess of 70°C, the load shall be derated as shown in the figure 1.

Voltage Rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial- line frequency and waveform corresponding to the power rating , as determined from the following formula:

$$\mathsf{RCWV} = \sqrt{\mathsf{P} \times \mathsf{R}}$$

Were : RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt)

P = Power Rating (watt)


R = Nominal Resistance (ohm)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value.



Metal Film Fixed Resistors 0.6W, 200 PPM


multicomp PRO



Nominal Resistance:

Effective figures of nominal resistance shall be in accordance with E-96 series, and resistance tolerance shall be shown by table 1.

Construction:



No.	Name	Material
1	Basic Body	Rod Type Ceramics
2	Resistance Film	Metal Film
3	End Cap	Steel (Tin plated iron surface)
4	Lead Wire	Annealed copper wire coated with tin
5	Joint	By Welding
6	Coating	Insulated epoxy resin (Colour: Sky blue)
7	Color Code	Epoxy Resin



Characteristics:


Characteristics	Limits	Test Methods (JIS C 5201-1)
DC. Resistance	Must be within the specified tolerance	The limit of error of measuring apparatus shall not exceed allowable range or 5% of resistance toler- ance
Temperature coefficient	± 200 PPM/°C	Natural resistance change per temp. degree centi- grade $\frac{R_2 \cdot R_1}{\frac{1}{R_1(t_2 \cdot t_1)}} \times 10^6 (\text{PPM/}^\circ\text{C})$ R1: Resistance value at room temperature (t1) R2: Resistance value at room temp. plus 100°C (t2)
Short time overload	Resistance change rate is $\pm (0.5\% + 0.05\Omega)$ Max. with no evidence of mechanical damage	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Dielectric withstanding voltage	No evidence of flashover me- chanical damage, arcing or insulation break down	Resistors shall be clamped in the trough of a 90° metallic V-block and shall be tested at AC potential respectively specified in the table 1. for 60 + 10/ -0 seconds
Pulse overload	Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max. with no evidence of mechanical damage	Resistance change after 10,000 cycles (1 sec. "on" , 25 secs. "off") at 4 times RCWV
Terminal strength	No evidence of mechanical damage	Direct load : Resistance to a 2.5 kgs direct load for 10 secs. in the direction of the longitudinal axis of the terminal leads Twist test : Terminal leads shall be bent through 90 ° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations
Resistance to soldering heat	Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max. with no evidence of mechanical damage	Permanent resistance change when leads immersed to 3.2 to 4.8mm from the body in $350^{\circ}C \pm 10^{\circ}C$ solder for 3 ± 0.5 seconds



Characteristics:

Characteristics	Limits		Test Methods (JIS C 5201-1)		
Solderability	95 % coverage Min.		The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temp. of solder : 245°C ±3°C Dwell time in solder : 2 to 3 seconds		
Resistance to solvent	No deterioration of protective coatings and markings		Specimens shall be immersed in bath of trichroethane completely for 3 mins. with ultrasonic		
	Resistance change rate is \pm (1% + 0.05 Ω) Max. with no evidence of mechanical damage		Resistance change after continuous 5 cycles for duty shown below:		
			Step	Temperature	Time
Temperature cycling			1	-55°C ±3°C	30 mins
- ,			2	Room temp.	10 to 15 mins
			3	+155°C ±2°C	30 mins
			4	Room temp.	10 to 15 mins
Load life in humidity	Resistance value	ΔR/R ±1.5%	7.9 Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity test chamber controlled at 40°C ± 2°C and 90 to 95 % relative humidity		
	Resistance value ΔR/R		7.10 Permanent resistance change after		
Load life	Normal type	±1.5%	1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at 70°C ±2°C ambient		h duty cycle of

Dimension:




Power Rating	D (Max.)	L (Max.)	d ±0.05	H ±3
0.6W-S	2.5mm	6.8mm	0.54mm	28mm



multicomp PRO


Painting Method:

Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within 1/2 of the are angle.



Marking :

Resistors shall be marked with color coding colors shall be in accordance with JIS C 0802



Part Number Table

Description	Part Number	
Resistor, Metal Film, 1R, 0.6W, 1%	MCMF006FJ100KA50	
Resistor, Metal Film, 1R5, 0.6W, 1%	MCMF006FJ150KA50	
Resistor, Metal Film, 2R2, 0.6W, 1%	MCMF006FJ220KA50	
Resistor, Metal Film, 2R7, 0.6W, 1%	MCMF006FJ270KA50	
Resistor, Metal Film, 3R3, 0.6W, 1%	MCMF006FJ330KA50	
Resistor, Metal Film, 4R7, 0.6W, 1%	MCMF006FJ470KA50	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

