

HI70300 - Storage Solution for pH and ORP Electrodes

Printed on 23/09/2019 Page n. 1 / 8 Replaced revision:3 (Dated 16/04/2018)

Safety Data Sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

HI70300 Code

Storage Solution for pH and ORP Electrodes Product name

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use Storage Solution for pH and ORP Electrodes.

1.3. Details of the supplier of the safety data sheet

Name Hanna Instruments S.R.L.

Full address str. Hanna Nr 1

District and Country 457260 loc. Nusfalau (Salaj)

Romania Tel +40 260607700 +40 260607700

e-mail address of the competent person

responsible for the Safety Data Sheet msds@hanna.ro

1.4. Emergency telephone number

For urgent inquiries refer to Emergency Number - International: +1 7035273887 - UK, London: +44 8708200418 -

CHEMTREC 24 hours/365 days

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements).

Hazard classification and indication:

2.2. Label elements

Hazard pictograms:

Signal words:

Hazard statements:

Precautionary statements:

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients

3.2. Mixtures

The product does not contain substances classified as being hazardous to human health or the environment pursuant to the provisions Regulation (EU) 1272/2008 (CLP) (and subsequent amendments and supplements) in such quantities as to require the statement.

SECTION 4. First aid measures

4.1. Description of first aid measures

Not specifically necessary. Observance of good industrial hygiene is recommended.



HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 2 / 8

Page n. 2 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 4. First aid measures .../>>

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures

5.1. Extinguishing media

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE Do not breathe combustion products.

5.3. Advice for firefighters

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Use breathing equipment if fumes or powders are released into the air. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Confine using earth or inert material. Collect as much material as possible and eliminate the rest using jets of water. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage

7.1. Precautions for safe handling

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use.

7.2. Conditions for safe storage, including any incompatibilities

Keep the product in clearly labelled containers. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available



HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 3 / 8

Page n. 3 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

POTASSIUM CHLORID	RIDE
-------------------	------

Predicted no-effect concentration - PNEC		
Normal value in fresh water	0,1	mg/l
Normal value in marine water	0,1	mg/l
Normal value for water, intermittent release	1	mg/l
Normal value of STP microorganisms	10	mg/l
Health - Derived no-effect level - DNEL / DMEL		

Troilliai value el el l	or oor garr	101110					9,.	
Health - Derived no-eff	fect level - D	ONEL / DMEL						
	Effects o	Effects on consumers			Effects on v	vorkers		
Route of exposure	Acute	Acute	Chronic	Chronic	Acute	Acute	Chronic	Chronic
	local	systemic	local	systemic	local	systemic	local	systemic
Oral		455		91				
		mg/kg bw/d		mg/kg bw/d				
Inhalation		1365		273		5320		1064
		mg/m3		mg/m3		mg/m3		mg/m3
Skin		910		182		910		303
		mg/kg bw/d		mg/kg bw/d		mg/kg		mg/kg
						bw/d		bw/d

VND = hazard identified but no DNEL/PNEC available ; NEA = no exposure expected ; NPI = no hazard identified.

8.2. Exposure controls

Comply with the safety measures usually applied when handling chemical substances.

HAND PROTECTION

None required.

SKIN PROTECTION

None required.

EYE PROTECTION

None required.

RESPIRATORY PROTECTION

None required, unless indicated otherwise in the chemical risk assessment.

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

PropertiesValueInformationAppearanceliquid

Colour colourless Odour odourless Odour threshold Not available рΗ 5 - 7 Melting point / freezing point Not available Initial boiling point Not available Boiling range Not available Flash point Not applicable Evaporation rate Not available Flammability (solid, gas) Not available Lower inflammability limit Not available Upper inflammability limit Not available Lower explosive limit Not available Upper explosive limit Not available Vapour pressure 17,5 mmHg Vapour density Not available Relative density 1,027

Solubility soluble in water
Partition coefficient: n-octanol/water Not available
Auto-ignition temperature Not available





HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 4 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 9. Physical and chemical properties/>>

Decomposition temperature
Viscosity
Not available
Explosive properties
Oxidising properties
Not available
not applicable
not applicable

9.2. Other information

Total solids (250°C / 482°F) 22,65 % VOC (Directive 2010/75/EC) : 0 VOC (volatile carbon) : 0

SECTION 10. Stability and reactivity

10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products

Information not available

SECTION 11. Toxicological information

According to currently available data, this product has not yet produced health damages. Anyway, it must be handled according to good industrial practices.

11.1. Information on toxicological effects

Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

LC50 (Inhalation) of the mixture:

LD50 (Oral) of the mixture:

Not classified (no significant component)

Not classified (no significant component)

Not classified (no significant component)

SKIN CORROSION / IRRITATION



HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 5 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 11. Toxicological information .../>>

Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

Information not available

12.2. Persistence and degradability

Information not available

12.3. Bioaccumulative potential

Information not available

12.4. Mobility in soil

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects

Information not available



HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 6 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 13. Disposal considerations

13.1. Waste treatment methods

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Information not relevant

SECTION 15. Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Seveso Category - Directive 2012/18/EC: None Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006 Substances in Candidate List (Art. 59 REACH) On the basis of available data, the product does not contain any SVHC in percentage greater than 0,1%. Substances subject to authorisation (Annex XIV REACH) Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012: Substances subject to the Rotterdam Convention: Substances subject to the Stockholm Convention:

Healthcare controls Information not available

German regulation on the classification of substances hazardous to water (AwSV, vom 18. April 2017)



HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 7 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 15. Regulatory information .../>>

WGK 1: Low hazard to waters

15.2. Chemical safety assessment

A chemical safety assessment has not been performed for the preparation/for the substances indicated in section 3.

SECTION 16. Other information

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

- 1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
- 2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
- 3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
- 4. Regulation (EU) 2015/830 of the European Parliament
- 5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
- 6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
- 7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
- 8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
- 9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
- 10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
- 11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
- 12. Regulation (EU) 2016/1179 (IX Atp. CLP)
- 13. Regulation (EU) 2017/776 (X Atp. CLP)
- 14. Regulation (EU) 2018/669 (XI Atp. CLP)
- 15. Regulation (EU) 2018/1480 (XIII Atp. CLP)
- The Merck Index. 10th Edition
- Handling Chemical Safety
- INRS Fiche Toxicologique (toxicological sheet)
- Patty Industrial Hygiene and Toxicology
- N.I. Sax Dangerous properties of Industrial Materials-7, 1989 Edition
- IFA GESTIS website
- ECHA website
- Database of SDS models for chemicals Ministry of Health and ISS (Istituto Superiore di Sanità) Italy

Note for users:





HI70300 - Storage Solution for pH and ORP Electrodes

Revision nr.4 Dated 19/09/2019 Printed on 23/09/2019 Page n. 8 / 8 Replaced revision:3 (Dated 16/04/2018)

SECTION 16. Other information .../>>

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product. This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

Changes to previous review: The following sections were modified: 01 / 02 / 09 / 15.