

## Micrometer heads

With 1 mm spindle pitch

Mitutoyo

### Application:

For installation in measuring instruments and presetters, as a setting and control element on machine tools, for fine adjustment of cross tables

### Execution:

- With regular gradation
- With simple clamping shank
- Rotating spindle

### Advantage:

- Fast



<b>Art. no.</b>	<b>32017 012</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	152-102
<b>Display</b>	Nonius
<b>Min./max. length measuring range</b>	0-25 mm
<b>Scale value</b>	0.01 mm
<b>Measuring surface diameter</b>	8 mm
<b>Measuring arrangement</b>	Flat
<b>Clamp in shank diameter</b>	12 mm
<b>Clamping shank length</b>	16 mm
<b>Measuring spindle increments</b>	1 mm
<b>Spindle clamping</b>	No
<b>Design</b>	Metric
<b>Calibration Group</b>	DE
<b>Gross Weight</b>	0.260 kg
<b>Product Group</b>	3MA

### EAN

4946368022802