


**Part Number: GC1513**  
**Reed Switch - Standard - Normally Open Contacts**  
**Product Data Sheet**

**PICTURE** **DIMENSIONS**



**us** File # E103299 ✓ RoHS Compliant

Drawings not to scale.  
 All dimensions in mm (inches).


**SPECIFICATION**

Contact Form	Form A (Normally Open)	
Contact Material	Rhodium	
Switching Capacity	Max.	120 W/VA
Switching Voltage	Max.	1500 VAC / DC
Switching Current	Max.	3.0 A
Carrying Current	Max.	5.0 A
Dielectric Strength	Min.	3000 VDC at >75 AT / 1500 VDC at <75 AT
Contact Resistance	Max.	100 mΩ
Insulation Resistance	Min.	10 <sup>11</sup> Ω
Pull - In Sensitivity	60 - 130 AT	
Drop - Out Sensitivity	Min.	30 AT
Operate Time Without Bounce	Max.	3.5 ms
Bounce Time	Max.	0.5 ms
Release Time	Max.	0.20 ms
Resonant Frequency	Typ.	900 Hz
Operating Frequency	Max.	100 Hz
Vibration (10-1000Hz)	35 g	
Shock (11 ms)	50 g	
Capacitance	Typ.	0.8 pF
Operate Temperature Range	Deg.	-40°C + 125°C
Test Coil	Type	1500

**NOTE**

- When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (0.118in.) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.
- We offer a crop and form service for Reed Switches to be customized to your specification.

**ORDERING INFORMATION**



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

**Phone: (1) 973 777 6900**                      **www.comus-intl.com**                      **Fax: (1) 973 777 8405**