

Product type designation

Product description

FO Trailing Cable

Glass fiber-optic cable, preferred length, preassembled
SIMATIC NET FO TRAILING CABLE 50/125, PREASSEMBLED
WITH 2X2 BFOC CONNECTORS, LENGTH 5.0 M



Suitability for use	Flexible cable for use in cable carriers for high mechanical loading, no UL approval
Version of the assembled FO cable	Assembled with four BFOC connectors
Cable designation	AT-W(ZN)Y(ZN)11Y 2G 50/125
Cable length	5 m

Optical data

Damping ratio per length	
<ul style="list-style-type: none"> at 850 nm / maximum at 1300 nm / maximum 	2.7 dB/km 0.7 dB/km
Bandwidth length product	
<ul style="list-style-type: none"> at 850 nm at 1300 nm 	600 GHz·m 1200 GHz·m

Mechanical data

Number of fibers / per FOC core	1
Number of FO cores / per FOC cable	2
Version of the FO conductor fiber	Multi-mode gradient fiber 50/125 μm, OM 2
Design of the FOC core	Hollow core, filled, diameter 1400 μm
Design of the fiber-optic cable	Segmentable
Outer diameter	
<ul style="list-style-type: none"> of the optical fibers of the optical fiber sheath of the FOC core sheath 	50 μm 125 μm 2.9 mm

Symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
Outer diameter / of the cable	10.5 mm
Symmetrical deviation / of the outer diameter of the line	0.5 mm
Material <ul style="list-style-type: none"> • of the fiber-optic cable core • of the optical fiber sheath • of the FOC core sheath • of the fiber-optic cable sheath • of the strain relief 	Quartz glass Quartz glass PVC PUR Aramid fibers
Color <ul style="list-style-type: none"> • of the FOC core sheath • of cable sheath 	Orange/black green
Bending radius <ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	150 mm 200 mm
Number of bending cycles	5000000
Tensile load / during operation / maximum	800 N
Short-term shear force per length	700 N/cm
Continuous lateral force per length	400 N/cm
Weight per length	90 kg/km

Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	-40 ... +80 °C -40 ... +80 °C -40 ... +80 °C -5 ... +50 °C
Burning behavior	Flammable
Chemical resistance <ul style="list-style-type: none"> • to mineral oil • to grease 	acc. to IEC 60811-404 with test oil IRM 902 (acc. to ISO 1817), +100 °C, 168 h, pull speed 250 mm/min. resistant
Radiological resistance / to UV radiation	resistant
Protection class IP	IP20

Product properties, functions, components / general

Product property <ul style="list-style-type: none"> • halogen-free • silicon-free 	No Yes
Product component / Rodent protection	No
Cable length	

- | | |
|--|--------|
| • for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum | 5000 m |
| • for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum | 750 m |
| • for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum | 2000 m |
| • for glass FOC / with PROFIBUS / maximum | 3000 m |

Standards, specifications, approvals

Certificate of suitability

- | | |
|-------------------|-----|
| • RoHS conformity | Yes |
|-------------------|-----|

Further Information / Internet Links

Internet-Link

- | | |
|---|---|
| • to website: Selector SIMATIC NET SELECTION TOOL | http://www.siemens.com/snst |
| • to website: Industrial communication | http://www.siemens.com/simatic-net |
| • to website: Industry Mall | https://mall.industry.siemens.com |
| • to website: Information and Download Center | http://www.siemens.com/automation/net/catalog |
| • to website: Image database | http://automation.siemens.com/bilddb |
| • to website: CAx Download Manager | http://www.siemens.com/cax |
| • to website: Industry Online Support | https://support.industry.siemens.com |

last modified: 16.03.2015