





Industrial jerrycan 10 L, HD-PE natural-coloured, with UN certification



Description:

Industrial jerrycan, 10 litres with screw cap (with original ring), natural-coloured, made of fracture-proof polyethylene (HD-PE)

- with UN certification for transporting hazardous goods
- compact shape - convenient and stackable
- very resistant to acids, alkalis and other chemicals
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- for the labelling (according to GHS regulation and ADR) of canisters filled with fuel, we recommend our hazard identification labels Art.-No. 306100
- separate accessories: Spigot with screw cap DIN 45 art. no. 550600 and filling aid art. no. 819351
- Approval No. 3H1/Y1.7/170/*B/AST-170017
- w = inside diameter of the filling opening = 34 mm
- a = outside thread diameter = DIN 45
- d=depth=192 mm w=width=232 mm h=height=306 mm

Information:

Article

Articlenumber	426301
GTIN	4007228426304
Customs tariff	39233090
Packaging Unit (PU)	6

Colour	natural
Volume in l	10
Weight (kg)	0,36
T x B x H (mm)	192 x 232 x 306

Outer packaging

Content in pieces	6
-------------------	----------

Gross weight unit (kg)	2,16
EAN Verpackungseinheit	4007228958867

Pallet

Number of boxes	16
Number of layers	4
L x B x H (m)	1,20 x 0,80 x 1,37

Carton per layer	4
Gross Weight Palette (kg)	54,56
Artikel pro Palette	96