



AX3000 Dual Band WiFi 6 PoE+ Access Point

TEW-923DAP (v1.0R)

- High performance AX3000 PoE+ access point
- AX3000 Dual Band: 2402Mbps (5GHz) + 573Mbps (2.4GHz) bands
- Two concurrent WiFi bands maximize device networking speeds
- OFDMA and MU-MIMO technology boosts performance in a busy environment
- Access Point and Repeater modes
- Supports up to WPA3 encryption
- 1 x 2.5GBASE-T PoE+ LAN port
- Low-profile blends into most environments
- Includes wall / ceiling mounting plate
- NDAA / TAA compliant (U.S. and Canada only)

TRENDnet's high-performance AX3000 Dual Band WiFi 6 PoE+ Access Point, model TEW-923DAP, features two concurrent WiFi bands to maximize networking speeds with the latest WiFi 6 technology. The two separate high-speed WiFi 6 bands provide speeds up to 2402Mbps on the 5GHz band and 573Mbps on the 2.4GHz band. The access point also supports Access Point (AP) and Repeater modes.

Faster speeds are possible on this WiFi 6 access point with 1024-QAM, OFDMA, and MU-MIMO technologies. MU-MIMO technology processes multiple data streams simultaneously, increasing real-time WiFi performance when multiple devices access the network. The wireless access point features access control, bandwidth control, and band steering. The low-profile housing design blends into most environments, and includes a convenient wall / ceiling mounting plate.





AX3000 WiFi 6

Two concurrent high-speed WiFi 6 bands to maximize device networking speeds: 2402Mbps on 5GHz and 573Mbps on 2.4GHz.



Power over Ethernet (PoE+)

Saves installation time and setup costs with 2.5GbE PoE+ support, delivering power and data over one set of cables.



Built For Busy Environments

MU-MIMO technology processes multiple data streams simultaneously, increasing real-time WiFi performance when multiple devices access the network.

FEATURES



Concurrent Dual Band

AX3000: concurrent 2402Mbps on 5GHz band + 573Mbps on 2.4GHz band



Power over Ethernet (PoE+)

Saves installation time and setup costs with 2.5GbE PoE+ support



WiFi Operation Modes

Supports Access Point (AP) and Repeater modes



MU-MIMO & OFDMA Performance

MU-MIMO technology enables the access point to process multiple data streams simultaneously along with WiFi 6 OFDMA technology to increase real-time WiFi performance



Band Steering

Band steering alleviates network congestion by automatically directing wireless devices from the 2.4GHz band to the 5GHz band



WiFi Traffic Shaping

Manage traffic allocation on the WiFi 6 access point per SSID for each band separately



Encrypted Wireless

Support for wireless encryption of up to WPA3



Multiple SSIDs

Create up to 8 SSIDs per band (16 total)



2.5GBASE-T PoE+ Port

2.5GBASE-T PoE+ LAN port maintains a high-performance connection to the wired network



LED Control

LED control reduces product visibility by disabling the LED indicator



Low Profile

Low-profile housing design blends into most environments



Mounting Plate

Wall / Ceiling mounting plate







SPECIFICATIONS

Standards

- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3x
- IEEE 802.3ab
- IEEE 802.3at
- IEEE 802.3bz
- IEEE 802.1Q
- IEEE 802.11a
- IEEE 802.11b
- IEEE 802.11g
- IEEE 802.11k**
- IEEE 802.11n (up to 300Mbps)*
- IEEE 802.11r**
- IEEE 802.11v
- IEEE 802.11ac (up to 867Mbps)*
- IEEE 802.11ax (up to 2402Mbps on 5GHz, up to 573Mbps on 2.4GHz)*

Hardware Interface

- 1 x 802.3at PoE+ 2.5GBASE-T LAN port (power input)
- Power port (12V DC, 1.5A external power adapter not included)
- LED indicator
- · Reset button

Features

- MU-MIMO
- · Band steering
- 802.1Q VLAN assignment per SSID
- · IPv4 static/DHCP address assignment
- UPnP/Bonjour

Operation Modes

- Access Point
- Repeater

Management/Monitoring

- Web based management (HTTP/HTTPS)
- Command Line Interface (Telnet/SSH)
- SNMP v2c/v3
- · Spanning Tree Protocol (STP)
- Event logging
- · Ping test
- Traceroute
- · Schedule WiFi radio enable/disable
- · Ping watchdog/gateway connection monitor
- · Reboot & scheduled automatic reboot
- Channel utilization scan

Access Control

- Wireless encryption: WPA2/WPA3-RADIUS (Enterprise), WPA2/WPA3-SAE (Personal)
- · MAC filter with scheduling
- · Maximum client limit
- · Client isolation

QoS

· Bandwidth control per SSID

SSID

Up to 8 SSIDs per wireless band (16 total)

Frequency

- 2.4GHz: 2.412 2.472GHz
- 5GHz: 5.180 5.825GHz

Wireless Channels

- 2.4GHz: FCC: 1-11. ETSI: 1-13
- 5GHz: FCC: 36, 40, 44, 48, 52, 56, 60, 64, 100, 104, 408, 112, 116, 120, 124, 128, 132, 136, 140, 149, 153, 157, 161 and 165, ETSI: 36, 40, 44, 48, 52, 56, 60, 64, 100, 104, 108, 112, 116, 120, 124, 128, 132, 136, 140

Modulation

- DBPSK/DQPSK/CCK for DSSS technique
- BPSK/QPSK/16-QAM/64-QAM/256-QAM/ 1024-QAM for OFDM/OFDMA technique

Antenna Gain

- 2.4GHz: 2 x 4.5 dBi internal
- 5GHz: 2 x 5.5 dBi internal

Wireless Output Power

- 802.11b/g/n/ac/ax (2.4GHz): FCC: 18 dBm (max.) / CE: 18 dBm (max.)
- 802.11a/n/ac/ax (5GHz): FCC: 18 dBm (max.) / CE: 18 dBm (max.)

Receiving Sensitivity

- 802.11a: -72 dBm (typical) @ 54Mbps
- 802.11b: -97 dBm (typical) @ 11Mbps
- 802.11g: -75 dBm (typical) @ 54Mbps
- 802.11n (2.4 GHz): -72 dBm (typical) @ 300Mbps
- 802.11n (5 GHz): -70 dBm (typical) @ 300Mbps
- 802.11ac: -60 dBm (typical) @ 867Mbps
- 802.11ax (2.4GHz): -60 dBm (typical) @ 573Mbps
- 802.11ax (5GHz): -52 dBm (typical) @ 2402Mbps

Power

- IEEE 802.3at Type 2 PoE+ PD Class 4
- Input: 100 240V AC, 50/60Hz, Output: 12V DC, 1.5A external power adapter (not included)
- Max. consumption: 17.4W

Operating Temperature

• $0^{\circ} - 40^{\circ} \text{ C} (32^{\circ} - 104^{\circ} \text{ F})$

Operating Humidity

· Max. 90% non-condensing

Certifications

- CE
- FCC

Dimensions

• 160 x 160 x 30mm (6.3 x 6.3 x 1.18 in.)

Weight

• 380g (13.4 oz.)

Warranty:

• 3 year

Package Contents

- TEW-923DAP
- · Quick Installation Guide
- Network cable (0.5m / 1.64 ft.)
- · Mounting plates



*Maximum wireless signal rates are referenced from IEEE 802.11 theoretical specifications. Actual data throughput and coverage will vary depending on interference, network traffic, building materials and other conditions. For maximum performance of up to 867Mbps use with an 867Mbps 802.11ac wireless adapter. For maximum performance of up to 300Mbps, use with a 300Mbps 802.11n wireless adapter. For maximum performance of up to 2402Mbps use with a 2402Mbps 802.11ax 5GHz wireless adapter. For maximum performance of up to 573Mbps use with a 573Mbps 802.11ax 2.4GHz wireless adapter. Multi-User MIMO (MU-MIMO) requires the use of multiple MU-MIMO enabled wireless adapters.

**Feature reserved for use when device is managed by TRENDnet Hive.

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.