


Turnlok[®] Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC

Pass & Seymour

4710, 4700, 4792, 4560, 4550, 4760, 4750, L520, CRL520, L620, L720, L530, CRL530, L630, L730

Quality construction for maximum durability.

hoose from a broad range of capacities in both single and duplex receptacle designs. They feature high-quality, brass contacts for rock-solid electrical connections and long service life. Single-piece, solid brass or steel straps and impact-resistant nylon face and body help them shrug off hard use.



Compact, impact-resistant Clearly marked NEMA configuration, rating nylon face and body are and third party listing on ultrasonically welded together for unrivaled strength. each unit's face. One-piece, high-grade brass contacts offer excellent conductivity and Single-piece, solid brass heat-rise resistance. mounting strap is free of easily loosened rivets found on other brands. 15 Amp mounting strap is steel. Side and external screw-pressure-plate back wire capability. Accepts #14 - #10 AWG. L620-R **Field Uses/Vertical Markets** Health Care Industrial Education Institutional Retail Office Hospitality/Lodging SF1701R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

Features & Benefits



Pass & Seymour


Turnlok[®] Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC

Ordering Information

Catalog Number	Rating A. V.	Description/Color	NEMA Config. No.
Receptad	les Back	& Side Wire	
4710	15 125	Single Receptacle	L5-15R
4700	15 125	Duplex Receptacle	L5-15R
4792	15 125	Combination Straight Blade and Locking	5-15R and L5-15R
4560	15 250	Single Receptacle	L6-15R
4550†	15 250	Duplex Receptacle	L6-15R
4760	15 277*	Single Receptacle	L7-15R
4750	15 277*	Duplex Receptacle	L7-15R
L520-R	20 125	Single Receptacle	L5-20R
CRL520-R	20 125	Single Receptacle, Corrosion-Resistant	L5-20R
L620-R	20 250	Single Receptacle	L6-20R
L720-R	20 277*	Single Receptacle	L7-20R
L530-R	30 125	Single Receptacle	L5-30R
CRL530-R	30 125	Single Receptacle, Corrosion-Resistant	L5-30R
L630-R	30 250	Single Receptacle	L6-30R
L730-R	30 277*	Single Receptacle	L7-30R

*AC only.

[†]Not designed for split circuits.



For more information on these and other P&S products refer to our Product Guide or visit our web site.

Turnlok[®] Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC

Technical Specifications

3rd Party Compliance

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596. CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs. Conforms to NEMA WD-1.

Performance

Electrical		
Dielectric Withstand Voltage	2000V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C max. after 50 cycles at 150% rated current	
Mechanical		
Terminal Accommodation	#14 AWG min. – #10 AWG max.	
Product Identification	Amperage, Voltage, NEMA Configuration molded into face	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact	
Materials		


Standard **Corrosion-Resistant** Front Body Nylon Nylon Back Body Nylon Nylon Mounting Strap Nickel-Plated Brass 15A = Steel, 20 & 30A = Brass Pressure Plate Brass Nickel-Plated Brass Contacts Brass Nickel-Plated Brass **Terminal Clamps** Nickel-Plated Brass Brass **Terminal Screws** Brass Brass Mounting Screws Zinc-Plated Steel Stainless Steel


Warranty

1.19"


1.545

1 Year





.922" #6-32 TAP 1.500" 1.375" 1.375" 1.125"



1.199" 1.322" -1.104" 2.635" 3.281" .0625" .0625"


Dimensions for 4700



Dimensions for 4792



Dimensions for 4550



2.29" .14" Dimensions for

20 Amp Receptacle

SF1701R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour



Complementary Devices & Accessories



TURNLOK® LOCKING DEVICES

 Extra-Hard Use Plugs & Connectors
Heavy-Duty Flanged Inlets & Outlets



GROUND CONTINUITY MONITORING (GCM)

 Extra-Hard Use Straight Blade
Heavy-Duty Turnlok[®]

STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip[®]II



TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok[®] Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS



WALL PLATES

- TradeMaster®
- Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail[™] Devices
- Switches
- Straight Blade Receptacles
- GFCIs
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor[®] Wire Mesh Grips
- Configurable Solutions

L'I legrand[®]

Legrand/Pass & Seymour P.O. Box 4822 Syracuse, NY 13221-4822 800-223-4185 North America Headquarters 60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721 www.legrand.ca

SF1701R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour