

## PSEN cs3.1a /PSEN cs3.1 1unit

541011



RFID safety switch 2 safe SC outputs, connection cable 5 m, one actuation direction, support for SDD, IP6K9K, switching distance 11 mm, Sao = 8 mm, Sar = 20 mm, PU = 1 piece coded switch with actuator.

## Technical details

### General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDB
Transponder coding:	coded
Suitable for series connection:	yes
unit type:	Unit

### Technical data

#### Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	1 W

#### Inputs

Number of inputs:	2
DC voltage at input:	24 V DC

#### Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
Potential isolation S/C O:	No

S/C output short circuit proof:	Yes
Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25 - 70 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Switching distances	
Change op. dist. temp.change:	+0.01mm/°C
Mechanical data	
Bend radius (when laying) K1:	5 x Ø
Type 1 actuator:	PSEN cs3.1
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	5 m cable
Cable lines:	Li9Y11Y 8 x 0.14 mm <sup>2</sup>
Housing material upper part:	PBT
Height dimension:	37 mm
Width dimension:	26 mm
Depth dimension:	18 mm
Net weight:	215 g
Gross weight:	275 g
Transponder	
Operating frequency:	122 kHz - 128 kHz

Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7A, 7C I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365019
EAN-Code:	4046548067224
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002592
Volume:	0

## Optional accessories



540334

PSEN/PDP67 M12-8sm screw terminals



540130

SDD ES ETH



540132

SDD ES PROFIBUS

---