

Stereo zoom microscope KERN OZL-45



#### **LAB LINE**

Stereo zoom microscope with or without halogen illumination, for the laboratory, training centres, quality control or agriculture

#### **Features**

- The KERN OZL-45 stereo zoom microscope series will impress you with its excellent optical characteristics, easy operation and high level of ergonomic working comfort
- The Halogen incident and transmitted illumination included as standard guarantees the very best illumination of your sample
- The high-quality optics, together with a large working surface offers the highest level of comfort for your applications
- The zoom objective offers you continuous magnification from 7,5×-50×
- The KERN OZL-45 series is available as a binocular version
- The pillar stand offers you the highest level of flexibility and the freedom to remove the microscope head and to integrate it into other modular systems, for example into a universal stand

- A large selection of eyepieces, external illumination units as well as auxiliary objectives are available as accessories
- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- Please find detailed information in the following model outfit list

#### Scope of application

 In vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

## Applications/Samples

 Samples with focus on three-dimesnional impression, zoom with variable magnification (depth, thickness), e.g. insects, seeds, circuit boards, components

## Technical data

- Optical system: Greenough optics
- · Brightness adjustable
- Tube 45° inclined
- Magnification ratio: 6,7:1
- Interpupillary distance 55 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 330×270×460 mm
- · Net weight approx. 5 kg

STANDARD										
Ø	00	Ф	Ö	<u> </u>	Q	<b>-</b>				
360°	BINO	HAL	IL	TL	ZOOM	230 V	1 DAY			

Model	Standard configuration						
	Tube	Eyepiece	Field of view	Objective	Stand	Illumination	
KERN			mm	Zoom			
OZL 451	Binocular	HSWF 10×/Ø 23 mm	Ø 33-5	0,75× - 5,0×	Pillar style	10 W Halogen (incident) 10 W Halogen (transmitted)	

# **MICROSCOPES & REFRACTOMETERS 2023**

MICROSCOPES



Stereo zoom microscope KERN OZL-45

Eyepiece	Specifications - Objectives							
	Magnification	Standard	Auxiliary objectives					
		1,0×	0,5×	0,75×	2,0×			
HWF 5×	Total magnification	3,75× - 25×	1,875× - 12,5×	2,813× - 18,75×	7,5× - 50×			
HWF 3^	Field of view mm	Ø 31-4,6	Ø 61,3-9,2	Ø 41,3 - 6,1	Ø 16-2,5			
HOWE 10	Total magnification	7,5×-50×	3,75× - 25×	5,625× - 37,5×	15× - 100×			
HSWF 10×	Field of view mm	Ø 33 - 5	Ø 65 – 10	Ø 44 - 6,7	Ø 16-2,5			
10ME 45	Total magnification	11,25× - 75×	5,625× - 37,5×	8,438× - 56,25×	22,5× - 150×			
HWF 15×	Field of view mm	Ø 24 - 4,2	Ø 48 – 8,5	Ø 32 - 5,6	Ø 12 - 2			
HSWF 20×	Total magnification	15× - 100×	7,5×-50×	11,25× – 75×	30× - 200×			
HOWF ZUX	Field of view mm	Ø 20 - 3,5	Ø 40 – 7	Ø 26,7 - 4,7	Ø 10 – 1,8			
LIME OF	Total magnification	18,75× – 125×	9,375×-62,5×	14,063× - 93,75×	37,5× – 255×			
HWF 25×	Field of view mm	Ø 15,8 - 2,4	Ø 31,5 – 4,8	Ø 24,1 - 3,2	Ø 7,9 – 1,2			
Working distance		113 mm	177 mm	117 mm	35 mm			
Maximum samp	le height	120 mm	60 mm	90 mm	165 mm			

Model outfit		Model KERN	Order number			
		OZL 451				
	HWF 5×/Ø 23,2 mm	00	OZB-A4112			
	HSWF 10×/ø 23 mm	44	OZB-A4118			
Eyepieces (30,0 mm)	HWF 15×/ø 15 mm	00	OZB-A4119			
(55,5)	HSWF 20×/ø 14,5 mm	00	OZB-A4120			
	HWF 25×/ø 11,7 mm	00	OZB-A4121			
	0,5×	0	OZB-A4209			
Auxiliary objectives	0,75×	0	OZB-A4210			
	2,0×	0	OZB-A4206			
Stand	Pillar style, with 12 V/10 W Halogen Illumination (transmitted + incident)	✓				
0. 1.	Frosted glass/Ø 95 mm	✓	OZB-A4805			
Stage plate	Black-white/Ø 95 mm	✓	OZB-A4806			
Illumination	10 W spare bulb (transmitted + incident)	✓	OZB-A4804			
Mechanical stage (Pre-assembling on request)	Stage size W×D 180×155 mm, Travel 75×55 mm, for transmitted and incident illumination	0	OZB-A4605			
External illumination	Please find the information about external illumination units in the catalogue on page 83 and on the internet					
		✓ = Included with delivery		O = Ontion		

## **MICROSCOPES & REFRACTOMETERS 2023**

KERN PICTOGRAMS





360° rotatable microscope head



Monocular Microscope For the inspection with one eye



**Binocular Microscope** For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



**LED** illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination **for compound microscopes**With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light

00

Infinity system

Infinity corrected optical system



Zoom magnification

For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WIFI data interface:

For transmitting of the picture to a mobile display device



**HDMI** digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurements from the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

**ABBREVIATIONS** 

C-Mount Adapter for the connection of a camera to a trinocular microscope

**FPS** Frames per second

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses) H(S)WF

LWD Long Working Distance N.A. **Numerical Aperture** SLR camera Single-Lens Reflex camera

**SWF** Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

BATT

**Battery operation** 

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable Prepared for a rechargeable battery

operation

**Plug-in power supply** 230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.