

Clamping jaw with positioning pins, pneumatic operation

ATORN®

Application

Clamping jaw system with positioning pins render laborious and time-consuming clamping devices superfluous, a practical, fast and simple way to lock the position of workpieces in a matter of seconds.

Version

- Fast and precise clamping of a wide variety of workpieces.
- Changeover in seconds for various machining operations
- Loose surfaces become superfluous, as does time-consuming cleaning.
- Stable and robust construction, also suitable for high clamping forces.
- Compressed air application via valves on each face.
- Closed on all sides once installed. This makes it low-maintenance.
- Recommended air pressure: 5.5 bar
- High-quality tool steel, hardened, ground and treated with a special oxidation process.

Advantage

- One press of the blow-out gun and all pins are driven out



Art. no.	26111 320
Jaws width	125 mm

EAN-Code

4050293625387