

Stereomicroscope KERN OSE-42





Side view

EDUCATIONAL LINE

Stereo microscope with robust, ergonomic design, ideal for workshops, schools and training

Features

- With its integrated handle as well as its stable arm curved stand, the KERN OSE OSE-42 has been specially developed for schools and workshops
- The incident and transmitted illumination unit included as standard can be optionally enabled for the very best illumination of your sample. Mobile use is also no problem due to the integrated battery compartment.
- Despite its low price it has very good optical characteristics, which enable you to have sharp images over a large field of view
- An turnable objective with predefined magnifications is available to make your working procedures quicker and more efficient

- The eyepieces are fixed in the eyepiece tube, to stop them getting damaged or lost
- A special feature of this adaptable and yet robust microscope series is the stable mechanism of the microscope stand which can be adjusted precisely. It will also impress you with its functionality and ergonomic design
- A large selection of eyepieces as well as various additional external illumination units are available as accessories

Scope of application

 Training, in vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

Applications/Samples

 Samples with focus on three-dimensional impression (depth, thickness), e.g. insects, seeds, circuit boards, components

Technical data

- Optical system: Greenough optics
- · Brightness adjustable
- Tube 45° inclined
- Interpupillary distance 55 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 200×180×300 mm
- Net weight approx. 2 kg

STANDARD)					
00	Ð	Ö	<u> </u>		_#	
RINO	LED	- 11	TI	RATT	23U V	1 DAY

Model Standard configuration						
	Tube	Eyepiece	Field of view	Objective	Stand	Illumination
KERN			mm			
OSE 421	Binocular	WF 10×/Ø 20 mm	Ø 20	2×/4×	Arm curved	1 W LED (incident); 1 W LED (transmitted)

MICROSCOPES & REFRACTOMETERS 2023





Stereomicroscope KERN OSE-42

Eyepiece	Specifications - Objectives				
	Magnification	2×	4×		
WF 5×	Total magnification	10×	20×		
WF 5*	Field of view mm	Ø 10	Ø 5		
WE 40	Total magnification	20×	40×		
WF 10×	Field of view mm	ø 10	Ø 5		
WE 45	Total magnification	30×	60×		
WF 15×	Field of view mm	ø 7,5	ø 3,7		
WE 20	Total magnification	40×	80×		
WF 20×	Field of view mm	Ø 6,5	Ø 3,2		
Working distan	ce	57 mm	57 mm		

Model outfit		Model KERN	Order number			
		OSE 421				
	WF 5×/Ø 16,2 mm	00	OZB-A4101			
	WF 10×/Ø 20 mm	44	OZB-A4102			
Eyepieces (30,5 mm)	WF 15×/ø 15 mm	00	OZB-A4103			
(,,	WF 20×/Ø 10 mm	00	OZB-A4104			
	WF 10×/ø 20 mm (reticule 0,1 mm)	0	OZB-A4151			
Stand	Arm curved, with 1 W LED illumination (transmitted + incident)	✓				
04	Frosted glass/ø 59,5 mm	✓	OZB-A4815			
Stage plate	Black-white/Ø 59,5 mm	✓	OZB-A4816			
External illumination	Please find the information about external illumination ur	nits in the catalogue on page 83 and on	the internet			

MICROSCOPES & REFRACTOMETERS 2023

KERN PICTOGRAMS





360° rotatable microscope head



Monocular Microscope For the inspection with one eye



Binocular Microscope For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination **for compound microscopes**With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light

00

Infinity system

Infinity corrected optical system



Zoom magnification

For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WIFI data interface:

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurements from the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

ABBREVIATIONS

C-Mount Adapter for the connection of a camera to a trinocular microscope

FPS Frames per second

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses) H(S)WF

LWD Long Working Distance N.A. **Numerical Aperture** SLR camera Single-Lens Reflex camera

SWF Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

BATT

Battery operation

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable Prepared for a rechargeable battery

operation

Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.