

Pneumatic-hydraulic blind rivet nut placement tool


PH 2 model



Version:

- Die-cast aluminium pneumatic cylinder
- Aluminium rotating hydraulic head
- Hardened and hard chrome-plated piston

Art. no.	53195 040
Model	PH 2
Suitable for min./max. rivet diameter	3-5 mm
Rivet setting force	8800 N
Max. working stroke	15 mm
Min./max. operating pressure	0-6 bar
Weight	1.3 kg



EAN-Code

4007081170017