

## Subland stepped drill bit type N HSS, fine quality grade

For 90° countersunk screws

**ORION**<sup>®</sup>

### Application:

For through holes in accordance with DIN EN 20273 and screw head countersinking 90°.

### Execution:

- Drill and countersink step with independent chip grooves and drill heels; regrinding does not affect the profile

### Advantage:

- precise alignment of drill diameter and countersink diameter, lower process costs
- universal use, therefore tool costs are reduced to a minimum and user flexibility is increased



<b>Art. no.</b>	<b>11100 008</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11100008
<b>Cutting material</b>	HSS
<b>Surface</b>	Vaporised
<b>Type</b>	N
<b>Angle of the tip</b>	118 Degree
<b>Coolant supply</b>	External
<b>Tool holding device</b>	HA parallel shank
<b>Suitable for screw thread</b>	M8
<b>Pilot hole diameter</b>	8.4 mm
<b>Spot-facer diameter</b>	15 mm
<b>Pilot hole length</b>	19 mm
<b>Chip flute length</b>	114 mm
<b>Length</b>	169 mm
<b>Shank diameter</b>	15 mm
<b>f steel 1000</b>	0.23 mm/r
<b>DIN</b>	8374
<b>Gross Weight</b>	0.200 kg
<b>Product Group</b>	1AR

### EAN

4039247026364