

## Die stock set, electric

For cutting the male threads of tapered Whitworth pipe thread ISO 7-1



### Application:

For electrically cutting the male threads of tapered Whitworth pipe thread ISO 7-1 during the repair and installation of extremely difficult-to-access threads.

### Version:

- Amigo type with 1200 W motor for R1/8 - 1 1/4, electrical hand die stock with universal motor 230 V, 50/60 Hz, double insulation to VDE (CEE), clockwise and anti-clockwise rotation with support bracket for both rotational directions and with 4 cutting heads for R1/8 - 1 1/4, in steel case with carry handle

### Advantage:

- Compact, robust and suitable for use on construction sites, can be used anywhere immediately, even without a vice, narrow design for tight spots
- Stable, compact and maintenance-free gear with robust and powerful 1200 W universal motor with 30% performance increase thanks to automatic carbon brush adjustment on change of rotational direction, peak draw up to 1800 W. High cutting speed of 35-27 rpm. Safety tip switch
- Motor weighing just 3.5 kg, not top heavy (hence also suitable for one-handed use), perfect and secure seating of quick-change cutting heads
- Compact design, high cutting material quality and precise processing of the cutting head guarantees easy cutting and thread cutting



<b>Art. no.</b>	<b>13735 110</b>
<b>Min./max. thread-cutting area, imperial</b>	1/2-1 1/4 in