

Manual scissor-type lifting carriage

Load-bearing capacity 500 kg

fetra
Transportgeräte

Execution:

- Frame and forks in a stable, torsion-free section steel construction
- Strong tubular push handle
- Hydraulic pump with chrome-plated pistons and overload valve
- Operation via foot pedal
- Lowering valve activated via hand lever
- 2 castors, wheels, polyurethane tyres
- 150 x 40 mm and 2 fork rollers
- Nylon 70 x 65 mm, castors with locking device.

Advantage:

- Good stability, can be moved even when the load is lifted.



Art. no.	50262 453
Brand	FETRA
Manufacturer Part Number	6820
Load-carrying capacity	500 kg
Length	1550 mm
Width	526 mm
Fork length	1115 mm
Fork arm width	153 mm
Fork roller width	65 mm
Fork roller diameter	70 mm
Fork, external distance	526 mm
Min. lift height	85 mm
Lift height	830 mm
Material of fork castor	Nylon
Material of wheel	Polyurethane
Wheel width	40 mm
Wheel diameter	150 mm
Total stop optional	No
Gross Weight	107.000 kg
Product Group	5AE

EAN

4017976068206