

Permanent magnetic clamping block

Application:

For magnetic clamping of round and rectangular workpieces.

Execution:

- Three magnetic contact surfaces
- Top features a cross-over V-block and two lateral areas
- Parallelism tolerance: 0.015 mm
- Right-angle tolerance: 0.025 mm

Advantage:

- Magnetic hold can be continuously adjusted using the rotary switch

Art. no.	51136 500
Length x width x height	100 x 100 x 100 mm
Min./max. workpiece diameter	2-20 mm
Gross Weight	6.441 kg
Product Group	592

