

## Index Plungers • with hexagon collar and locking, stainless steel A4

### 22120.1192



#### Product Description

Index plungers are used for indexing bores.  
The stainless steel A4 version ensures maximum corrosion resistance.

#### Material

##### Body

- Stainless steel 1.4401

##### Locking pin

- Stainless steel 1.4401 nickel-plated

##### Knob

- Stainless steel 1.4401

##### Lock nut


- Stainless steel 1.4401

#### More information

#### Notes

Knob not removable.  
Lock nuts have to be purchased separately.

#### Drawing





#### Order information

Dimensions							Spring load <sup>1)</sup>		🌡️	🏋️	Art. No.
d <sub>1</sub>	d <sub>2</sub>	l <sub>2</sub> min.	d <sub>3</sub>	l <sub>1</sub>	l <sub>3</sub>	l <sub>4</sub>	F <sub>1</sub> ~	F <sub>2</sub> ~	max.	[g]	
-0.02 -0.05											
[mm]											
[N]											
[°C]											
with knob of stainless steel – picture 2											
12	M20 x 1,5	15	32	71.5	33	10	9	32	100	229	22120.1192

<sup>1)</sup> statistical average value

#### Accessories

	Dimensions d <sub>2</sub> [mm]	Wrench size [mm]	 [g]	Art. No.
Lock nuts ISO 8675 (DIN 439), Stainless steel 1.4401				
	M20 x 1,5	30	33.0	22120.1520

## Compliance

### RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 10.06.2022

### Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure  
<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals