


GENERAL PURPOSE APPLICATION.
SWITCHING APPLICATION .

FEATURES


- For Complementary With NPN Type BC846W/847W/848W.

MAXIMUM RATING (Ta=25)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Collector-Base Voltage	BC856W	V_{CBO}	-80	V
	BC857W		-50	
	BC858W		-30	
Collector-Emitter Voltage	BC856W	V_{CEO}	-65	V
	BC857W		-45	
	BC858W		-30	
Emitter-Base Voltage	BC856W	V_{EBO}	-5	V
	BC857W		-5	
	BC858W		-5	
Collector Current		I_C	-100	mA
Emitter Current		I_E	100	mA
Collector Power Dissipation		P_C	100	mW
Junction Temperature		T_j	150	
Storage Temperature Range		T_{stg}	-55 150	



Marking



MARK SPEC

TYPE	BC856W-A	BC856W-B	BC857W-A	BC857W-B	BC857W-C	BC858W-A	BC858W-B	BC858W-C
MARK	3A	3B	3E	3F	3G	3J	3K	3L

BC856W/7W/8W

ELECTRICAL CHARACTERISTICS (Ta=25 °C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current		I_{CBO}	$V_{CB}=-30V, I_E=0$	-	-	-15	nA
DC Current Gain (Note)	BC856W	h_{FE}	$V_{CE}=-5V, I_C=-2mA$	125	-	475	
	BC857W			125	-	800	
	BC858W			125	-	800	
Collector-Emitter Saturation Voltage		$V_{CE(sat)} 1$	$I_C=-10mA, I_B=-0.5mA$	-	-0.09	-0.3	V
		$V_{CE(sat)} 2$	$I_C=-100mA, I_B=-5mA$	-	-0.25	-0.65	
Base-Emitter Saturation Voltage		$V_{BE(sat)} 1$	$I_C=-10mA, I_B=-0.5mA$	-	-0.7	-	V
		$V_{BE(sat)} 2$	$I_C=-100mA, I_B=-5mA$	-	-0.9	-	
Base-Emitter Voltage		$V_{BE(ON1)}$	$V_{CE}=-5V, I_C=-2mA$	-0.6	-0.65	-0.75	V
Base-Emitter Voltage		$V_{BE(ON2)}$	$V_{CE}=-5V, I_C=-10mA$	-	-	-0.82	V
Transition Frequency		f_T	$V_{CE}=-5V, I_C=-10mA, f=100MHz$	-	150	-	MHz
Collector Output Capacitance		C_{ob}	$V_{CB}=-10V, I_E=0, f=1MHz$	-	4.5	-	pF
Noise Figure		NF	$V_{CE}=-6V, I_C=-0.2mA$ $R_g=2k\Omega, f=1kHz$	-	2.0	10	dB

NOTE : According to the value of h_{FE} the BC856, BC857, BC858 are classified as follows.

CLASSIFICATION		A	B	C
h_{FE}	BC856W	125 250	220 475	-
	BC857W	125 250	220 475	420 800
	BC858W	125 250	220 475	420 800

BC856W/7W/8W

